

DESIGN ENVELOPE 4312 TWIN SINGLE PHASE | 0208-003.0 | submittal

File No: 100.4858 Date: OCTOBER 27, 2014 Supersedes: NEW Date: NEW

Job:	_ Representative:	
	Order No:	_ Date:
Engineer:	_ Submitted by:	_ Date:
Contractor:	Approved by:	Date:

PUMP DESIGN DATA

No. of pumps:	Tag:	
Capacity:USgpm (L/s)	Head:ft (m)	
Liquid:	Viscosity:	
Temperature:°F (°C)	Specific gravity:	
Suction: 2" (50mm)	Discharge: 2" (50mm)	

MOTOR DESIGN DATA

нр: 3	rрм: 1750	Frame size:	
Enclosure:	_ Volts: 208	Freq: 60 Hz	
Phase: 3	Efficiency: NE	Efficiency: NEMA premium	

MAXIMUM PUMP OPERATING CONDITIONS

ANSI 125

175 psig at 150°F (12 bars at 65°C) 140 psig at 250°F (10 bars at 121°C)

• Tolerance of ±0.125" (±3 mm) should be used

• For exact installation, data please write factory for certified dimensions

MECHANICAL SEAL DESIGN DATA

See file no. 43.50 for standard mechanical seal details as indicated below


Armstrong seal reference number

□ A1 (c) □ Others: ____

CONTROLS DATA

Power supply:	Volts: 200-240VAC Freq: 50/60Hz Phase: 1	
Sensorless control:		
Minimum system pressure to be maintained:	ft (m)*	
Protocol (standard):	□ Modbus rtu □ BACnet [™] ms/tp	
	\Box Johnson [®] N2 \Box Siemens [®] FLN	
Protocol (optional):	□ LonWorks [®]	
Enclosure:	□ Indoor - UL TYPE 12 □ Outdoor - UL TYPE 4x with weather shield	
	□ Outdoor – UL TYPE 4X less weather shield	
Disconnect switch:		
Duty/standby		
pre-wired bridge:		
EMI/RFI control:	1-phase IVS102 units do not meet the EN61800-3 directive	
Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% Ac line reactor) Supporting IEEE 519-1992 requirements**	
Cooling:	Fan-cooled through back channel	
Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)	
Analog ı/o:	Two current or voltage inputs, one current output	
Digital ı/o:	Six programmable inputs (two can be configured as outputs)	
Pulse inputs:	Two programmable	
Relay outputs:	Two programmable	
Communication port:	1-rs485, 1-usb	

* If minimum maintained system pressure is not known: Default to 40% of design head **The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation. 2



DIMENSION DATA


	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)
Frame size:	182TC	182TC
Size:	2×2×8	2×2×8
HP:	3	3
RPM:	1750	1750
AB:	29.23(743)	35.27(896)
B1:	8.19(208)	8.19(208)
B2:	8.66(220)	8.66(220)
C1:	13.91(353)	13.91(353)
C2:	14.38(365)	14.38(365)
D1:	8.27(210)	8.27(210)
D2:	9.06(230)	9.06(230)
E:	6.84(174)	7.50(191)
F:	15.94(405)	19.50(495)
P:	10.38(264)	9.56(243)
SD:	15.75(400)	15.75(400)
т:	5.12(130)	5.12(130)
XY:	26.54(674)	26.42(671)
Weight:	465(210.9)	545(247.2)


Dimensions - inch (mm)

Weight – Ibs (kg)

:

Performance curves are for reference only. Confirm current performance data with Armstrong ACE Online selection software.





TORONTO

+416 755 2291

BUFFALO

+716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM