

DESIGN ENVELOPE 4382 DUALARM | 0608-005.0 | SUBMITTAL

File No: 100.4646

Date: OCTOBER 30, 2015

Supersedes: 100.4633

Date: AUGUST 14, 2015


Job:			Repre	sentative:			
			Order	No:	Date:		
Engineer: Subr			Subm	itted by:	Date:		
Contractor: Appr			Appro	oved by:	Date:		
PUMP DESIGN D	АТА			CONTROLS DATA			
No. of pumps:		Tag:		: Sensorless Control:	Standard		
Capacity:	_USgpm (L/s)	Head:	ft (m)	Minimum system pressure to be maintained:	ft (m)*		
Liquid: Temperature:				Protocol (standard): ☐ Modbus RTU ☐ BACnet™ MS☐ Johnson® N2 ☐ Siemens® F			
Suction: 6" (150mm)				Protocol (optional):	\square LonWorks $^{\circledR}$		
OSHPD Seismic Certification OSP-0422-10 UL STD 778 & CSA STD C22.2 NO.108 certified				Enclosure:	☐ Indoor - UL TYPE 12 ☐ Outdoor - UL TYPE 4X with		
MOTOR DESIGN	DATA			Fused disconnect switch:			
HP: RPM:	_ Frame size: _	Enclosure	e:	Duty/standby			
Volts:	_ Hertz: 60 Hz	z Phase: 3		pre-wired bridge:			
Efficiency: NEMA pre	emium 12.12			EMI/RFI CONTROL:	Integrated filter designed to meet EN61800-3		
MAXIMUM PUMP OPERATING CONDITIONS				Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**		
ANSI 125	nars at 65°C)			Cooling:	Fan-cooled through back channel		
175 psig at 150°F (12 bars at 65°C) 140 psig at 250°F (10 bars at 121°C)				Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)		
ANSI 250				Analog ı/o:	Two current or voltage inputs,		
250 psig at 150°F (17 bars at 65°C)				Disital (o	one current output Six programmable inputs (two can		
250 psig at 250°F (17 bars at 121°C)					be configured as outputs)		
a Talayanaa af to soo" (to sous) da a title a a ti				Pulse inputs:	Two programmable		
 Tolerance of ±0.125" (±3 mm) should be used For exact installation, data please write factory for 				Relay outputs:	Two programmable		
certified dimensions				Communication port:	1-RS485, 1-USB		
MECHANICAL SE	AL DATA			**The IVS 102 drive is a low harmonic o	sure is not known: Default to 40% of design head drive via built-in DC line reactors. This does not		
Seal Type: 2A	Stationa	ary Seat: Silicon car	bide	guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong			
Secondary Seal: EPDM Rotating Hardware: Stainless steel				will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation			

FLUID TYPE	ALL GLYCOLS > 30% WT CONC		ALL OTHER NON-POTABLE FLUIDS		POTABLE (DRINKING) WATER	
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating Face	Silicon carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat Elastomer	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (o-ring)
Material Code	SCsc L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

and the costs for such mitigation.

Spring: Stainless steel

2



Performance curves are for reference only.

 $Confirm\ current\ performance\ data\ with\ Armstrong\ {\tt ACE}\ Online\ selection\ software.$

ARMSTRONG FLUID TECHNOLOGY

ESTABLISHED 1934

DIMENSION DATA

	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)
Frame size:	184	184
Size:	6×6×8	6×6×8
HP:	5	5
RPM:	1500	1500
AB:	22.27(566)	22.27(566)
B1:	9.75(248)	9.75(248)
B2:	9.75(248)	9.75(248)
C1:	16.90(429)	16.90(429)
C2:	17.63(448)	17.63(448)
D1:	16.81(427)	16.81(427)
D2:	16.81(427)	16.81(427)
E:	7.50(190)	7.50(190)
F:	13.65(347)	13.65(347)
P:	10.38(264)	9.50(241)
SD:	33.94(862)	33.94(862)
T:	7.875(200)	7.875(200)
XY:	19.67(500)	20.42(519)
Weight:	618(280.3)	694(314.8)

Dimensions - inch (mm) Weight - lbs (kg)

TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER


+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696



ARMSTRONGFLUIDTECHNOLOGY.COM