

DESIGN ENVELOPE 4382 DUALARM

0811-007.5 | SUBMITTAL

File No: 104.5523

Date: JULY 8, 2019

Supersedes: 104.5523

Date: AUGUST 1, 2018

Job:	Representative:			
	Order No:		Date:	
Engineer: Submit Contractor: Approx		ed by:		
		ed by:		
PUMP DESIGN DATA	:	CONTROLS DATA		
No. of pumps: Tag:		Protocol (standard):	☐ BACnet [™] MS/TP	
	•		☐ BACnet™ TCP/IP	
Total system design flow:USg	:		☐ Modbus RTU	
Head:ft(m) Capacity split	:	Enclosure:	☐ Indoor – UL TYPE 12	
Flow per pump head:USg	:		☐ Outdoor – UL TYPE 4X with	
Parallel flow:USg	pm(L/s)		Weather Shield	
Liquid: Viscosity:			☐ Outdoor - UL TYPE 4X less Weather Shield	
Temperature: °F (°C) Specific gravity:	:	Fused disconnect switch:		
Suction: 8" (200mm) Discharge: 8" (200m	nm)		Integrated filter designed to	
OSHPD Seismic Certification OSP-0422-10		EMIJ KFI COITTIOI.	meet EN61800-3	
UL STD 778 & CSA STD C22.2 NO.108 certified Test report is supplied with each pump		Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% Ac line reactor) Supporting IEEE 519-1992 requirements**	
MOTOR DESIGN DATA		Cooling:	Fan-cooled through back channel	
HP: RPM: Frame size: Enclosure:	Volts:	_	-10°C to +45°C up to 1000 meters above	
Hertz: 60 Hz Phase: 3 Efficiency: NEMA premium	:		sea level (+14°F to +113°F, 3300 ft)	
		Analog ı/o:	Two current or voltage inputs,	
MAXIMUM PUMP OPERATING CONDITIONS	. :		one speed output	
		Digital ı/o:	Two inputs, two outputs	
ANSI 125 - (CONSTRUCTION: BF)		Pulse inputs:	Two programmable	
175 psig at 150°F (12 bar at 65°C) 140 psig at 250°F (10 bar at 121°C)		Relay outputs: Two programmable		
		Communication port:	1-RS485	
FLOW READOUT ACCURACY		guaranty performance to any sys	ive via built-in DC line reactors. This does not tem wide harmonic specification or the costs to . If supplied with the system electrical details,	

MECHANICAL SEAL DATA

The Design Envelope model selected will provide flow reading

on the controls local keypad & digitally for the BMS. The model

readout will be factory tested to ensure ±5% accuracy.

Seal Type: 2A Stationary Seat: Silicon carbide Secondary Seal: EPDM Rotating Hardware: Stainless steel Spring: Stainless steel Spring: Stainless steel

FLUID TYPE	ALL GLYCOLS > 30% WT CONC		ALL OTHER NON-POTABLE FLUIDS		POTABLE (DRINKING) WATER	
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating Face	Silicon carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat Elastomer	EPDM (L-cup)	EPDM (o-ring)	EPDM (L-cup)	EPDM (O-ring)	EPDM (L-cup)	EPDM (o-ring)
Material Code	SCSC L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

Armstrong will run a computer simulation of the system wide harmonics. If

harmonic mitigation and the costs for such mitigation.

system harmonic levels are exceeded Armstrong can also recommend additional

2

OPTIONS

SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

PARALLEL SENSORLESS (STANDARD)



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

*Only available if sensorless bundle is enabled

□ PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

□ ZONE OPTIMIZATION BUNDLE



Controls pumps to ensure multiple zones are satisfied for heating or cooling

 2 sensor control - Controls pumps in a 2-zone application to ensure both zones are always satisfied for heating or cooling

□ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Cooling

Duty point	gpm (L/s) at	ft (m)
Minimum syste	m pressure to be maint	ained
	ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum syste	m pressure to be maint	ained
	ft (m)	

OPTIONAL SERVICES

ON-SITE PUMP COMMISSIONING



Where purchased and applicable, onsite commissioning by an Armstrong representative will include setting up communication with the Pump (not wiring to BAS), adjusting parameters to match on-site conditions, register the pumps for enhanced warranty and connect the pumps to the router as part of the activation of Pump Manager.

PUMP MANAGER




As a Performance Management Service, Pump Manager is an online automated fault detection and diagnostic service for sustained performance and enhanced reliability. It includes advanced trending, alerts of variance in performance and automated reports.

Available in yearly increments. Includes an option for a price discount on the Extended Warranty Service.

^{*}Only available if sensorless bundle is enabled

^{*}The Service requires an active internet connection.

3



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.

INDOOR OUTDOOR SD D2 Ď1 D1 _E1 Ε B1 В2 _ E2_ В1 В2 WEATHER ØΡ ØΡ SHIELD ΑВ

C1

C2

DIMENSION DATA

	INDOOR	OUTDOOR
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC)
Frame size:	254	254
Size:	8×8×11	8×8×11
HP:	7.5	7.5
RPM:	1500	1500
AB:	24.95(634)	24.95(634)
B1:	10.50(267)	10.50(267)
B2:	11.00(279)	11.00(279)
C1:	20.10(511)	20.10(511)
C2:	20.23(514)	20.23(514)
D1:	21.46(545)	21.46(545)
D2:	26.30(668)	26.30(668)
E:	9.94(252)	9.94(252)
F:	17.96(456)	17.96(456)
P:	14.19(360)	14.19(360)
SD:	46.94(1192)	46.94(1192)
T:	8.80(224)	8.80(224)
XY:	27.26(692)	27.26(692)
Weight:	1604(727.6)	1684(763.9)

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of ± 0.125 " (± 3 mm) should be used
- For exact installation, data please write factory for certified dimensions

TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A. 14120-6594 +1 716 693 8813

BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL HALESOWEN, WEST MIDLANDS UNITED KINGDOM B62 8DJ +44 (0) 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM
M11 2ET
+44 (0) 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA 560 003 +91 (0) 80 4906 3555

SHANGHAI

UNIT 903, 888 NORTH SICHUAN RD. HONGKOU DISTRICT, SHANGHAI CHINA 200085 +86 (0) 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

