

VERTICAL TURBINE DIESEL FIRE PUMP | 6x10H VTF WITH 6x12 CAST IRON HEAD | SUBMITTAL

File No: F51.602
Date: APRIL 10, 2025
Supersedes: F51.602
Date: JULY 15, 2013

Job: _____ Representative: _____

Order no.: _____ Date: _____

Engineer: _____ Submitted by: _____ Date: _____

Contractor: _____ Approved by: _____ Date: _____

Model: 6 x 10H VTF **Discharge head:** 6 x 12 A

RPM: 1770 Water lube

500 GPM: _____ T.D.H

- FM UL NFPA-20 only
- Approval Construction
- Engine model: _____
- Ragd model: _____
- Shaft model: _____
- Controller model: _____

NOTES


- Dimension based on randolph gear drive. May vary when driver adaptor is required.
- Dimensions are in inches unless otherwise indicated.
- Engine to base mounting and cooling loop to be field installed and plumbed.
- Engine oil & anti freeze/coolant may not be included.
- Gear shipped filled with oil. Check level before installation.
- Refer dwg. no. _____ for Engine dimensions.
- Not to be used for construction unless certified.

PRESS RATE	DISCHARGE FLANGE INCH (mm)					
	DA	DC	DD	DF	DG	DK
125 #	11.00 (279)	9.50 (241)	10.25 (260)	6.00 (152)	0.88 (22)	1.00 (25)



NO OF STG'S	DISCHARGE SIZE	RATING	RAGD	AG*	B	C	H*	I*	L	AA
	INCH (mm)		HP	INCH (mm)						
5	6 (152)	125	40	22.25 (565)	63.44 (1611)	1.00 (25)	8.50 (216)	17.00 (432)	—	—
6	6 (152)	125	60	22.25 (565)	71.94 (1827)	1.00 (25)	8.50 (216)	17.00 (432)	—	—
7	6 (152)	125	60-80	22.25 (565)	80.44 (2043)	1.00 (25)	8.50 (216)	17.00 (432)	—	—

* Dimension based on randolph gear drive. May vary when driver adaptor is required.



TORONTO
+1 416 755 2291

BUFFALO
+1 716 693 8813

DROITWICH SPA
+44 8444 145 145

MANCHESTER
+44 8444 145 145

BANGALORE
+91 80 4906 3555

SHANGHAI
+86 21 5237 0909

BEIJING
+86 21 5237 0909

SÃO PAULO
+55 11 4785 1330

LYON
+33 4 20 10 26 21

DUBAI
+971 4 887 6775

JIMBOLIA
+40 256 360 030

FRANKFURT
+49 6173 999 77 55