

VERTICAL TURBINE ELECTRIC FIRE PUMP | 10×15H VTF WITH 10×20 FABRICATED STEEL HEAD | SUBMITTAL

File No: F51.526
Date: APRIL 28, 2025
Supersedes: F51.526
Date: AUGUST 15, 2005

Job: _____ Representative: _____

Order no.: _____ Date: _____

Engineer: _____ Submitted by: _____ Date: _____

Contractor: _____ Approved by: _____ Date: _____

Model: 10 × 15H VTF

Discharge head: 10 × 20 F

rpm: 1770 Water lube

2000 gpm: _____ T.D.H


☐ FM ☐ UL ☐ NFPA-20 only ☐ Approval ☐ Construction

Motor: _____ HP: _____

Volt: _____ pH: _____

Hz: _____

☐ Controller model: _____




PRESS RATE	DISCHARGE FLANGE inch (mm)					
	DA	DC	DD	DF	DG	DK
300 #	17.50 (445)	15.25 (387)	14.00 (356)	10.00 (254)	1.13 (29)	1.88 (49)

NO OF STG'S	DISCHARGE SIZE	RATING	DIMENSION inch (mm)		
	inch (mm)		AG*	B	C
5	10.00 (254)	300	65.25 (1657)	97.25 (2470)	1.94 (49)

NOTES

- Dimensions are in inches unless otherwise indicated.
- When motor is oil lubricated, oil is not furnished. See operation manual for manufacturer's recommendations.
- Not to be used for construction unless certified.
- * Dimension based on motor height of a standard WP-I Hollow shaft motor. Subject to change depending on motor mfg. and/or the use of a motor adaptor.



TORONTO
+1 416 755 2291

BUFFALO
+1 716 693 8813

DROITWICH SPA
+44 8444 145 145

MANCHESTER
+44 8444 145 145

BANGALORE
+91 80 6510 3555

SHANGHAI
+86 21 5237 0909

BEIJING
+86 21 5237 0909

SÃO PAULO
+55 11 4785 1330

LYON
+33 4 20 10 26 21

DUBAI
+971 4 887 6775

JIMBOLIA
+40 256 360 030

FRANKFURT
+49 6173 999 77 55