

VERTICAL TURBINE ELECTRIC FIRE PUMP | 12×18H VTF WITH 12×24.5 FABRICATED STEEL HEAD | SUBMITTAL

File No: F51.544
Date: APRIL 28, 2025
Supersedes: F51.544
Date: AUGUST 15, 2005

Job: _____ Representative: _____

Order no.: _____ Date: _____

Engineer: _____ Submitted by: _____ Date: _____

Contractor: _____ Approved by: _____ Date: _____

Model: 12 × 18H VTF

Discharge head: 12 × 24.5 F

rpm: 1770 Water lube

4000 gpm: _____ T.D.H


☐ FM ☐ UL ☐ NFPA-20 only ☐ Approval ☐ Construction

Motor: _____ HP: _____

Volt: _____ pH: _____

Hz: _____

☐ Controller model: _____




PRESS RATE	DISCHARGE FLANGE inch (mm)					
	DA	DC	DD	DF	DG	DK
300 #	20.50 (521)	17.75 (451)	17.00 (432)	12.00 (304)	1.25 (32)	2.00 (51)

NO OF STG'S	DISCHARGE SIZE	RATING	DIMENSION inch (mm)		
	inch (mm)		AG*	B	C
3	12.00 (305)	300	65.25 (1657)	66.50 (1689)	2.25 (57)

NOTES

- Dimensions are in inches unless otherwise indicated.
- When motor is oil lubricated, oil is not furnished. See operation manual for manufacturer's recommendations.
- Not to be used for construction unless certified.
- * Dimension based on motor height of a standard WP-I Hollow shaft motor. Subject to change depending on motor mfg. and/or the use of a motor adaptor.



TORONTO
+1 416 755 2291

BUFFALO
+1 716 693 8813

DROITWICH SPA
+44 8444 145 145

MANCHESTER
+44 8444 145 145

BANGALORE
+91 80 6510 3555

SHANGHAI
+86 21 5237 0909

BEIJING
+86 21 5237 0909

SÃO PAULO
+55 11 4785 1330

LYON
+33 4 20 10 26 21

DUBAI
+971 4 887 6775

JIMBOLIA
+40 256 360 030

FRANKFURT
+49 6173 999 77 55