

END SUCTION ELECTRIC FIRE PUMP | 50 HZ | SELECTION CHARTS

File No: F40.205
Date: FEBRUARY 20, 2024
Supersedes: F40.205
Date: DECEMBER 29, 2021

PUMP	FLOW USgpm (L/s)	SPEED rpm	PRESSURE RANGE PSI (kPa)		
			UL	ULC	FM
4×3×8.5 FM	250 (16)	2945	45 (310) – 92 (634)	45 (310) – 92 (634)	45 (310) – 92 (634)
	300 (19)	2945	44 (303) – 91 (636)	44 (303) – 91 (636)	44 (303) – 91 (636)
	400 (25)	2945	49 (338) – 88 (607)	49 (338) – 88 (607)	49 (338) – 88 (607)
	450 (28)	2945	60 (414) – 85 (594)	60 (414) – 85 (594)	60 (414) – 85 (594)
4×3×13 FM	300 (19)	2945	114 (786) – 212 (1462)	—	114 (786) – 212 (1462)
	400 (25)	2945	109 (752) – 211 (1455)	—	109 (752) – 211 (1455)
	450 (28)	2945	106 (731) – 210 (1420)	—	106 (731) – 206 (1420)
	500 (32)	2945	101 (696) – 209 (1441)	—	101 (696) – 207 (1427)
	750 (47)	2945	—	—	154 (1062) – 190 (1310)
4×3×13 NF	300 (19)	2945	105 (723) – 188 (1296)	—	—
	400 (25)	2945	99 (682) – 182 (1254)	—	—
	450 (28)	2945	94 (648) – 178 (1227)	—	—
	500 (32)	2945	102 (703) – 171 (1179)	—	—
5×4×11.5 FM	500 (32)	2945	107 (738) – 158 (1089)	107 (738) – 158 (1089)	107 (738) – 158 (1089)
	750 (47)	2945	102 (703) – 154 (1061)	102 (703) – 154 (1061)	102 (703) – 154 (1061)
	1000 (63)	2945	98 (676) – 146 (1006)	98 (676) – 146 (1006)	98 (676) – 147 (1013)
8×5×11.5 FM	750 (47)	2945	96 (662) – 145 (1000)	96 (662) – 145 (1000)	96 (662) – 145 (1000)
	1000 (63)	2945	92 (634) – 143 (986)	92 (634) – 143 (986)	92 (634) – 143 (986)
	1250 (79)	2945	87 (600) – 140 (965)	87 (600) – 140 (965)	86 (593) – 140 (965)
	1500 (95)	2945	111 (765) – 133 (917)	111 (765) – 133 (917)	112 (772) – 133 (917)
6×5×13 FM	400 (25)	2945	120 (827) – 175 (1207)	120 (827) – 175 (1207)	120 (827) – 175 (1207)
	450 (28)	2945	120 (827) – 174.5 (1203)	120 (827) – 174.5 (1203)	120 (827) – 174 (1200)
	500 (32)	2945	120 (827) – 174 (1200)	120 (827) – 174 (1200)	120 (827) – 174 (1200)
	750 (47)	2945	119 (820) – 172 (1186)	119 (820) – 172 (1186)	119 (820) – 172 (1186)
	1000 (63)	2945	116 (800) – 168 (1158)	116 (800) – 168 (1158)	116 (800) – 168 (1158)
	1250 (79)	2945	110 (758) – 162 (1117)	110 (758) – 162 (1117)	110 (758) – 162 (1117)
8×6×13 FM	1000 (63)	2945	116 (800) – 159 (1096)	116 (800) – 159 (1096)	116 (800) – 159 (1096)
	1250 (79)	2945	113.5 (783) – 156 (1076)	113.5 (783) – 156 (1076)	114 (786) – 156 (1076)
	1500 (95)	2945	110 (758) – 152 (1048)	110 (758) – 152 (1048)	110 (758) – 152 (1048)
	1750 (111)	2945	—	—	106 (731) – 147 (1014)

TORONTO

23 BERTRAND AVENUE,
TORONTO, ONTARIO,
CANADA, M1L 2P3
+1 416 755 2291

BUFFALO

93 EAST AVENUE, NORTH
TONAWANDA, NEW YORK,
USA, 14120-6594
+1 716 693 8813

DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS
BUSINESS PARK, DROITWICH SPA,
WORCESTERSHIRE,
UNITED KINGDOM, WR9 0LW
+44 121 550 5333

MANCHESTER

WOLVERTON STREET, MANCHESTER
UNITED KINGDOM, M11 2ET
+44 161 223 2223

BANGALORE

#18, LEWIS WORKSPACE, 3RD FLOOR,
OFF MILLERS - NANDIDURGA ROAD,
JAYAMAHAL CBD, BENSON TOWN,
BANGALORE, INDIA 560 046
+91 80 4906 3555

SHANGHAI

UNIT 903, 888 NORTH SICHUAN RD.
HONGKOU DISTRICT, SHANGHAI
CHINA, 200085
+86 21 5237 0909

BEIJING

ROOM 1612, NANYIN BUILDING NO.2
NORTH EAST THRID RING ROAD
CHAOYANG DISTRICT, BEIJING,
CHINA 100027
+86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES
AGOSTINHO, 1370 GALPÃO 6 EMBU
DAS ARTES, SAO PAULO, BRAZIL
+55 11 4785 1330

LYON

93 RUE DE LA VILLETTE
LYON, 69003 FRANCE
+33 4 20 10 26 21

DUBAI

JAFZA VIEW 19, OFFICE 402
P.O. BOX 18226 JAFZA,
DUBAI - UNITED ARAB EMIRATES
+971 4 887 6775

JIMBOLIA

STR CALEA MOTILOR NR. 2C
JIMBOLIA 305400, JUD.TIMIS
ROMANIA
+40 256 360 030

FRANKFURT

WESTERBACHSTRASSE 32,
D-61476 KRONBERG IM TAUNUS
GERMANY
+49 6173 999 77 55

ARMSTRONG FLUID TECHNOLOGY®
ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM