

Certificate of Compliance

This certificate is issued for the following:

Centrifugal Fire Pumps (Axial Split-Case Type)

> Model 5x4x17F (see ratings below)

Prepared for:

S. A. Armstrong Limited 23 Bertrand Avenue Scarborough, Ontario Canada M1L 2P3

FM Approvals Class: 1311

Approval Identification: 3057403

Approval Granted: October 11, 2016

To verify the product continues to be Approved please refer to www.approvalguide.com.

Said Approval is subject to satisfactory field performance, continuing Surveillance Audits, and strict conformity to the constructions as shown in the Approval Guide, an online resource of FM Approvals.



Member of the FM Global Group

B. 4

David B. Fuller AVP, Manager of Fire Protection FM Approvals 1151 Boston-Providence Turnpike Norwood, MA 02062 USA



Certificate of Compliance

	Rated	Rated	Rated Net Head at		Rated		Discharge	
	Capacity,	Capacity,	Rated Capacity,	Rated Net Head at	Speed,	Suction Inlet,	Outlet,	
Product	(gal/min)	(dm³/min)	psi	Rated Capacity, kPa	r/min	dia., in.	dia., in.	Stage(s)
5x4x17F	500	1895	45-90	310-620	1480	5	4	1
5x4x17F	500	1895	96-134	660-925	1780	5	4	1
5x4x17F	500	1895	100-194	690-1340	2100	5	4	1
5x4x17F	500	1895	109-243	750-1675	2350	5	4	1
5x4x17F	500	1895	134-279	925-1925	2600	5	4	1
5x4x17F	500	1895	174-251	1200-1730	2945	5	4	1
5x4x17F	500	1895	181-261	1250-1800	3000	5	4	1
5x4x17F	750	2840	85-123	585-850	1780	5	4	1
5x4x17F	750	2840	88-185	605-1275	2100	5	4	1
5x4x17F	750	2840	100-235	690-1620	2350	5	4	1
5x4x17F	750	2840	126-271	870-1870	2600	5	4	1
5x4x17F	750	2840	171-248	1180-1710	2985	5	4	1
5x4x17F	750	2840	172-252	1185-1735	3000	5	4	1



Member of the FM Global Group