

Product	Item Update Description
Accessories	Resolved - Inaccurate voltage listed in submittal output document versus quote line selection (Incident #149509)
Expansion	Removed - Specific GLA Models from selection option [UK and Europe Markets] (Incident #145982)
Fire System	Added - Fire Controller Enclosure Rating option list
	Added - Orifice option for Tornatech flow meter type. (Incident #149475)
	Resolved - Error displayed when requesting Expedite for Consult Factory workflow during Fire Systems selection [UK Market]
	Resolved - Inaccurate line drawing displayed versus ANSI flange rating selected [India Market] (Incident #147855)
	Resolved - Place order issue for NFPA DE Fire [Brazil Market]
	Resolved - In certain selection scenarios, low control suction valve was automatically selected within the quote (Incident #150197)
	Updated - Enclosed Fire Pak System Lead time updates (Incident #149219)
	Updated - NFPA Fire System pricing [Brazil Market]
	Updated - Updated battery cable supplied components for with Kirloskar Engines
iFMS	Resolved - DE iFMS error displayed when selecting ed both "DirtAir Separator" and "Expansion Tank"
Order Submission	Added - Expedite queue dashboard available within Home screen
	Added - When Consult Factory is requested, "Place Order" is not available
	Removed - Improve Lead Time option no longer available in Expedite option screen
	Resolved - Check Stock function not working [Brazil Market]
	Updated - Consult Factory request workflow now includes notification to requesting user
	Updated - Consult Factory set as lead time for output quote documents when Consult Factory request is included (Incident #140678)
Selection	Updated - Lead times for various Boosters, Commercial Pumps. Pressurization Units and Controls [UK Market] (Incident #148087)
Parts	Resolved - For certain impeller requirements, option not available to trim below 200mm (Incident #149219)
Pumps	Removed - "Vertical Inline DualArm" option from results grid [India Market]
	Resolved - Armstrong Integrated Designer displayed flow showing accurate flow per rotating assembly versus total flow
	Resolved - Incorrect 125hp motor line on 4300 - 8x8x13
	Resolved - Lead time inaccurate when VFD option not selected with pump and motor [Canda Market] (Incident #148617)
	Resolved - Output submittal reflects Tango & Dual Arm Standby (Incident #145460)
	Resolved - During Constant Speed selection, under specific duty points, model 4700 not listed in grid results [IEC Markets]
	Updated - 4030 pump coupling option (NEMA, Asia Pacific, UK Markets)
	Updated - Curve and motor for specific model 4300 and 4030/4280
	Updated - Lead Time changed to 18 weeks when selecting TCZ frame size. [US, Canada, Latin America Markets] (Incident #150022)
	Updated - Lead Time for S ECM and H ECM for 5 and 6 Series (Incident #146621)
	Updated - Price adjust for Customer Choice motor option [US Market] (Incident #151393)
	Updated - Pump size 20x20x19 BD and OCD dimensions for ANSI-125 , PN-16 , ANSI-250 and PN-25 (Incident #147955)
	Validated - Design Envelope model 4332 – 1015B-022.0 curve error displayed for selected duty point. No error found
Service	Resolved - Finish button not displayed under certain scenarios when configuring SMART Recommissioning (Incident #145982)
	Resolved - Item# 427163-041 not allowing trim to 7.5" size (Incident #149121)
Shell & Tube	Added - Custom option for RTB within manual selection (Incident #150601)
	Resolved - Shell and Tube Heat Exchanger inaccurate output unit specification listed under specific scenarios (Incident #129026)
	Resolved - Shell & Tube configurator output submittal shows units Imperial when Metric was selected within configurator (Incident #104549)
UDP	Added - Price field for User Define Products when Parts is selected in Product field