

Product	Summary
Pumps	Resolved - Output Submittal does not match selected Suction Guide psi selection (Incident #63762)
	Resolved - E2 Pump duty points changed not reflected in UI
	Validated - CS 4700 pump ("VMS-60:05-2C") error displayed when click Get Results
	Updated - 145 kw motor frame size changed from 280S to 280SX [IEC Market] (Incident #73768)
	Resolved - Motor size is not updating on Post select Screen for 4700 - QVMS-03:36A , 4700-QVMS-150:05-2A - Manual Selection [IEC Market]
	Validated - During specific 4332 selection scenarios a motor discrepancy was created. Validated no issue (Incident #132360)
	Validated - Error - Head in meters mentioned at full capability at 100% design flow. Validated no issues (Incident #84885)
	Updated - Pacdor drawing for 4700QVMS [China-India Market] (Incident #137107)
	Updated - Load Profile submittal report for PRS
	Resolved - Seismic Clip option aligned with 4200H pumps only
	Removed - 4380 3212H 00.55 Design Envelope model removed from auto selection option [IEC Market] (Incident #141798)
	Updated - "Elastomeric Flexible coupling" instead of "Flexible Coupling" in option drop down (Incident #141338)
	Resolved - NCP request not required when selecting TDS above 2000+ PPM for DEPM IVS pumps (Incident #141811)
	Resolved - In certain multi-pump selections, remote disconnects and fuses inaccurate quantity was allocated [NEMA Market] (Incident #142493)
	Resolved - 4700 VMS BOMs are showing triple quantities (Incident #142665)
	Resolved - Under certain pump selection, error displayed when adding Suction Guide from Accessories selection (Incident #142420)
	Removed - 4700QVMS dimension table in submittal [India, Middle East, Asia Pacific Rim, China Markets]
	Resolved - Inaccurate fluid type listed in submittal when Ethylene solution is selected for Constant speed VMS pump (Incident #143558)
	Resolved - %BEPQ inaccurate value listed in submittal's
	Resolved - Error displayed when selecting email output during post select within pump configurator
	Updated - Lead Time inaccurate when selecting 4030 pump series with a 480/3/60 power supply [USA Market] (Incident #143956)
	Updated - 4300 - 1219-037.0kW and 4300 - 2037-110.0kW pumps set to ASHRAE 90.1 compliance [IEC Markets]
	Resolved - Error displayed when adding Suction Guide during Load profile schanges within Armstrong Integrated Designer configurator
	Resolved - Change of hp not available during selecting stand-by pump hp to match available pump hp [NEMA Market] (Incident#144582)
	Removed - Variable speed '4300 - 8x8x8'
	Resolved - Inaccurate Hmax RPM reflected on Submittal (Incident #144796)
	Updated - Inaccurate Lead Time reflected in specific 4302 pump configurations (Incident #144996)
	Resolved - Under certain scenarios, error displayed when selecting Place Order from Place Order detail confirmation screen

Product	Summary
Boosters	Updated - After selection, removed "(control panel contact only)" verbiage [IEC Market] (Incident #116939)
	Resolved - AV Kit option selected, on DE6800G, not showing size [UK Market] (Incident #142509)
	Resolved - In limited scenarios when configuring a Booster, selected flange option inaccurately displayed on output submittal. (Incident #142574)
	Updated - Remove QVMS dimension table from the submittal and correct the drawing format for DEBooster 6800Q model
	Updated - 6800Q model accurate line drawings are displayed and included in output report
	Added - DE 6800Q Pacdor drawings (Incident #136060)
Service	Validated - No Error found - Displayed 500 Error for Service and Parts in specific scenario
	Added - Insulated NDE Bearing made default option for 90KW or greater motor size and optional for less than 90KW [IEC Market] (Incident #137981)
	Resolved - Commercial pump replacement parts set Trim diameter to mm instead of current "in" measures (Incident #138238)
	Resolved - Certain scenarios the Service and Parts option is displaying an error (Incident #142668)
	Validated - Error displayed when configuring replacement motor parts for 4312 -1.5x1.5x3, 184TC - Selection is not valid
	Resolved - During certain scenarios when quote includes both IPS and non-IPS products, error is displayed when clicking "Continue" during Service and Parts configuration of IPS Manager/IPS Manager
Packaged Systems	Resolved - ETO Packaged Systems - Getting error while selecting Secondary Pump. [UK Market]
	Validated - Error displayed post selection for ETO Packaged systems [Asia Pacific Rim Market]
Selection	Resolved - UI Exception error displayed under specific scenarios when Place Order is clicked
	Resolved - Pricing inconsistency for iFMS [Canada and USA Market]
	Updated - Circulator output document inconsistent measurement unit [Latin America Market]
Fire	Resolved - Disable Kirloskar Engine selection option [USA and Latin America Market]
	Updated - ADEPT DE Fire Pump curve and submittal (Incident #137855)
	Updated - LPS and LPL are removed from NFPA Fire Systems, NFPADE fire system and Loose fire accessories. (Incident #140484)
	DCR-2024-013 - Resolved - PLD Engines Section2 - Curve ID does not match submittal for 8x6x15NF @ 2350 rpm [NEMA Market]
	Updated - Battery option submittals Indian Market and non-India Market, respectively. (Incident #140996)
	Updated - 350GPM selection removed from the Rated Flow dropdown in the NFPA Fire Systems, Replacement/Standalone Listed Fire Pump and Driver, and Replacement/Standalone Listed Bareshaft Fire Pump selection modules (Incident #141319)
	Resolved - Remote Alarm Panel option details included on output report (Incident #143049)
	Resolved - Error displayed when selecting 12x12x18F with CFP15E-F10 model [NEMA Market]
	Resolved - Post select price is inaccurate in certain scenarios when selecting FM Bareshaft pumps [UK Market]
	Resolved - Not able to add replacement Fire pump VIL 4x3x9 pump with 380/3/60 to quote (Incident #144803)
	Resolved - Certain DE Fire Pump inaccurate details listed in submittal document (Incident #137855)
	Resolved - Error displayed when selecting various NFPA Fire pump models from result grid
	Resolved - No Results displayed when selecting 300USgpm@7bar ES Electric (Incident #97059)

Product	Summary
Fire Systems	Added - Display "External Comments" field on output Submittal documents
Control Systems	Updated - Please add "Modbus TCP/IP" to the Communications Protocol drop-down list for all IPS and SE-F products (Incident #142162)
	Resolved - Post Select price and quote line pricing not matching
	Resolved - 4x3x9NF_VIL Fire Pump motor frame inaccurate item number for all hp in 50hz selection
	Resolved - During selection of IPC EE-W10(Suitable for 3 nos chillers) for dedicated pump configuration, not able to enter rated tonnage/chiller under "Capacity per chiller (Tons)' option (Incident #144588)
Shell & tube	Resolved - Unable to print submittal for certain Shell and Tube models [NEMA Market] (Incident #144569)
DAS	Resolved - DASH-12-R inaccurately displays NCP required (Incident #144931)