

Product	Item Update Description
ADEPT Select	Resolved - ADEPT Select unable to download submittal report for schedule (Incident #148568)
	Added - New graphic landing page for ADEPT Select
Air Separators	Resolved - Error displayed when configuring Vortex Air Separator selection [Brazil Market]
Boosters	Adept issue regarding the configured Booster order
Circulators	Updated - Lead time for H-H68 1.5hp to be set to 5 weeks (Incident #148162)
Control Systems	Resolved - Pricing inaccuracies within EE-W and SE-A Optimization products (Incident #145900)
	Updated - 6 zones is the maximum number of zones available for SE-F10.2 (Incident #146773)
Expansion	Added - Specific Expansion Tanks not available (Incident #145365)
Expansion Systems	Added - Country of Installation option for DAS, VAS, Expansion, Tank Heaters
Fire Systems	Updated - Electric Fire controller "Topicalization" option is now set to "D15" (Incident #146192)
	Resolved - NCP Status not updated after NCP approved for Replacement Listed Fire Pump and Driver
	Resolved - Getting attention required error for Replacement Listed Bareshaft Fire pump and Replacement Listed Fire pump and driver [Asia Pacific and Middle East Markets]
	Resolved - VIL Jockey Pump electric kit for Firepak not displayed within selectin option (Incident #146920)
	Resolved - Error displayed - when importing and validating a existing quote then selecting to generate report
	Updated - Driver details during selection includes accurate motor
	Resolved - Error printing schedule quote during FM selection using Fire Systems (Incident #147796)
	Resolved - Certain Fire Pump line drawings not available
	Updated - Various DE Fire pump curve images
	Resolved - Incorrect pumps displayed under specific duty conditions [India Market] (Incident #145816)
	Resolved - When NCP is approved, under certain scenarios, pricing is not accurate [UK Market] (Incident #148906)
	Added - 5x4x10PF DE VIL Fire Pump
	Added - 5x4x10 PF CS VIL Fire Pump
	Added - LPC MPA pumps panel manufacture options
	Resolved - Error displayed when option to print schedule with file attached
Order Submission	Resolved - when selecting to print the Order Summary report, an error is displayed [USA Market] (Incident #148039)
Pumps	Resolved - Load profile error when clicking Apply
	Added - Turn Down Ratio options
	Resolved - Unable to add to schedule 4380 1205-002.0 pump @2hp and 575V (Incident #144033)
	Resolved - Under certain selection options, can not select 30hp pump (Incident#144582)
	Resolved - Update Lead Time on specific 4200H pumps with Shaft Grounding Ring (Incident #144928)
	Added - DE 4200H Envelopes for specific pump models (Incident #145588)
	Resolved - Lead Time for specific S & H Circulators not accurate (Incident #145327)
	Updated - Various pump models display inaccurate Lead Times [India Market] (Incident #145813)
	Added - Enhancements to Armstrong Integrated Designer selection options
	Resolved - Incorrect units displayed for Temperature and Pressure based on Regional login (Incident #143871)
	Resolved - unable to select specific variable speed pumps with outlined speed corner points
	Updated - MEI value for 4280 150-250
	Resolved - Specific 4300 8x8x15 Pump curve displayed inaccurately (Incident #145908)
	Added - Initiate NCP Required when 4600pump - 75kW to 315kW, 2 pole motor - selection requested (Incident #146007)
	Resolved - The constant speed curve is not shown correctly for a variable speed selection.
Added - Drip Pan has been added back to selection option (Incident #146612)	

Product	Item Update Description
Pumps	Resolved - Line drawing not displayed for Tango 4332 0407-050.0 [NEMA Market]
	Updated - Lead time for specific pump products
	Resolved - Under certain scenario, unable to print submittal, error is displayed (Incident #148719)
	Resolved - Line drawing not displayed for specific pump models (Incident #147505)
	Resolved - Incorrect redundancy percent listed in pump output submittal for specific scenarios of importing quote file for the Tango 4x4x7.5
	Added - Tango 4x4x7.5 pump series available for auto selection
Selection	Resolved - Product drawings missing for specific configurations (Incident #120852)
	Resolved - in some scenarios the output Quote report price not matching in both columns.
Service	Updated - Update Smart Startup configuration screen to include pump quantity (Incident #119632)
	Validated - Smart Start-up quantity matches selected pump quantity
	Updated - Pricing outline for specific pump replacement motor parts (Incident #145402)
	Updated - When selecting SE-F units, default option now includes Armstrong Services (Incident #141788)
	Updated - Control Panel parts listing for DE Booster (Incident #146666)
	Resolved - Submit button not available to add Services and Parts options when quote includes selection from Armstrong Integrated Designer (Incident #147776)
	Resolved - Motor Size within the Operating Parameters selection showing inaccurate unit measurements [Brazil Market]
	Resolved - Not able to configure selected Smart Recommissioning option selection [Brazil Market]
Service Parts	Resolved - Error displayed when performing selections within "Commercial Pump Replacement Parts" (Incident #145720)
Accessories	Resolved - Pump Size column, in results pane, not correctly sorting (Incident #65217)
	Resolved - During selection, incorrect Suction Guide may be selected or Error displayed (Incident #144216)
Shell & tube	Resolved - Error displayed when Manua selection through Model Type as Replacement Tube Bundle [NEMA Market] (DCR 2025-003)
Sustainability	Updated - TM65 report data