

		3	3	I	2			1		
		ZONE	REV.		REVIS	IONS		ATE	APPROVED	
			KEV.		ELEASE, SEE E.O. #	103688		3/10	JM	,
								FILE NO.: DATE:	62.5 Jun. 01, 2	
								SUPERSE DATE:		New New ^F
	NOTE	ES:								
			<u>.</u>				_			
				ised on facto idard consult					e require	d. –
	2 - All dimensions are in inches [mm].									
	3 - Tolerances are +/- 1/4" [6.35] unless otherwise specified.									
	4 - Drawings are for layout purposes only.								E	
	 5 - Drawing 2505-000 is applicable for Pumps with suction size up to 3", 20hp @ 3600rpm, and nominal impeller diameters of 10". For larger sizes consult factory for new drawing. 									
	6 - Dir	nensio	n in parei	nthesis applie	es for pun	nps 15-2	0hp.			
	for	⁻ optior		l with standa ic type or eq d loose).			der coni	nections	suitable	
	Μ	laximu	um Syster	n Pressure:	□ 175 PS	I □2	50 PSI			C
) TE 7				NECTION	ORIENT	ATION				
	SI	JCTIO RIGI		- STD. AS SH	OWN [I LEFT I	HAND			
	D	ISCHA RIGI		- STD. AS SH	OWN [I LEFT I	HAND			С
	-4X SLOT: 1/2''X4'' / RECOM	ANCHO	r bolt							
										P
			I		1 1					
				NLESS OTHERWISE SPECIFIED: NIMENSIONS ARE IN INCHES VEIGHT IN POUNDS	DRAWN .	VAME DATE JMC 5/13/10	AR	MSTR	DNG 此	
			F A	OLERANCES: RACTIONAL±1/4 .NGULAR: MACH±0.5° BEND±0.5°	ONEONED	DG 5/25/10 EH 5/25/10	TITLE: 653	5IVS -	TRIPLEX	A
ARY AND CONFIDENTIAL			T Ti	WO PLACE DECIMAL ± 0.25 HREE PLACE DECIMAL ± 0.250 MENSIONING AND TOLERANCING PER:		BB 5/25/10 JM 5/25/10		DW		
THE SOLE PROPERTY OF DNG. ANY ON IN PART OR AS A WHO WRITTEN PERMISSION OF	DLE		M.	ASME Y14.5-1994	COMMENTS:	I	SIZE DWG	. NO.	F	REV
WRITTEN PERMISSION OF DNG IS PROHIBITED.	NEXT A	ASSY	USED ON	NISH	DO NOT	SCALE	C	2505-0	000	
		APPLICATIO	DN D	ESIGN AUTHORITY: ${f S}$.	A. ARMSTR	RONG	SCALE: NTS	WEIGHT:	SHEET 1 (OF 1

2	