





anaging a commercial building involves wrestling with new challenges every day, particularly where building temperatures are involved.


The energy needed to run your HVAC systems represents an enormous percentage of your overall operating costs, and the challenge of balancing cost control against the comfort of your tenants can certainly make life interesting.

With some pump designs even a simple seal replacement can cause a downtime of six to seven hours. If your HVAC system doesn't have built-in redundancy, building temperatures will be affected, and your tenants will notice.

If external service providers are required, any maintenance work that takes place outside regular hours can be expensive. You could end up overspending on your maintenance budget, and still have unhappy tenants.

With increased expectations for financial performance and tenant satisfaction, commercial buildings need HVAC systems that combine highefficiency with constant availability.

CONSTANT AVAILABILITY But upgrading to a redundant system may not be as straightforward as it sounds. In many instances building designs don't allow adequate space in the mechanical room for a separate standby pumping unit. And even if there is floor space available. once you factor in the costs for a concrete base, pipe, additional fittings and installation labour, a standby pump can be prohibitively expensive.



To address these issues Armstrong offers an advanced solution that gives you the security of a 100% redundant pump in a compact design that will fit almost any installation.

The Armstrong Design **Envelope Twin Vertical** In-Line pump draws on a proven, industry-leading design that makes it the most costeffective solution for commercial HVAC systems and the perfect choice for your project.

THE ASSURANCE: **BUILT-IN**


If your pump application is highly critical, the Armstrong Design Envelope dualArm offers continuous operation during repair.



SAVINGS

FLOOR SPACE SAVINGS

Because the two rotating assemblies are integrated into one casing, a Twin pump requires only 25% of the floor space needed for two end suction base-mounted pumps. You can install the redundancy you need without expanding the mechanical room, and a smaller mechanical room means more square feet of rentable space within your building.





	MODEL	FOOTPRINT (SQ.FT.)	RATIO TO END- SUCTION PUMPS
ONE TWIN	4312 5нр моток	6.4	0.26
TWO END SUCTION PUMPS	5HP MOTOR	25	1.0

EVERY


PURCHASE & INSTALLATION SAVINGS

TWIN PUMP

END SUCTION

View your savings and ROI using real data from your installation. Ask your Armstrong representative.

Compared to industry-standard solutions the Armstrong Design Envelope Twin pump saves over 60% of the costs related to installation.



IDENTICAL APPLICATION

One 4312 Twin pumping unit

Two pump end suction unit system

1.00

INSTALLATION COST*

3.96

*Costs are normalized so no units are shown.

Everything included


- Elegant space-saving design
- All-in-one pump and VFD solution
- Perfectly matched pumpmotor-control combination
- No mounting of VFD to wall
- No re-alignment of shaft and coupling
- No flexible piping connectors
- No inertia base or grouting

Contents required

- Flex connectors
- Inertia base
- Remote sensor
- Extra set of pump trim

Labour requirements

- Grouting
- Shaft realignment
- Wiring to VFD
- Mounting and wiring of remote sensor



DESIGN SAVINGS

The small footprint of the Twin vertical in-line pump means you can include it in your drawings without redesigning the mechanical room to make space. Design Envelope selection lets you choose a pumping solution based on your HVAC requirements, and not worry about having to update your selection because of changes to the project.

REDUCED TENANT COMPLAINTS

Constant uptime supported by built-in redundancy means the Armstrong Design Envelope Twin pump is always available to meet the demand for heating or cooling.

MAINTENANCE SAVINGS

The Armstrong Vertical In-Line design allows easy access to the mechanical seal, so routine maintenance can be completed in less than 30 minutes. The 100% redundancy means you can schedule repairs at convenient times, and avoid emergency service rates.

UP TO 70%

DESIGN ENVELOPE

Armstrong's Design Envelope pumps integrate a perfectly matched Vertical In-Line pump, motor and intelligent variable speed controller to create a complete pumping solution for HVAC systems. Design Envelope maximizes pumping efficiency by adjusting pump speed in response to system demand. Variable speed technology combined with sensorless control can reduce your energy costs by up to 70%.

FOR DETAILS ON

- Design Envelope Selections
- Demand-based variable speed operation, and
- Sensorless technology
 please see the Design Envelope
 brochure (FILE NO. 100.11)



KEYFEATURES

VERTICAL IN-LINE DESIGN

Reduces costs for

component purchas-

es and installation. Because the pump Provides increased hangs in the HVAC system piping, there is no requirement for a concrete pad, grouting or flex-**HVAC** system more connectors.

SENSORLESS

TECHNOLOGY

overall efficiency,

matching pump

operation to the

demands of the

accurately than

industry-standard remote sensors.

AVAILABLE FITTED PLATE

Installs in the casing to allow removal of the entire rotating assembly for service. With the fitted plate in place, the backup pump operates normally until the duty pump is serviced and returned.

VERTICAL ORIENTATION

No requirement for realignment as part of a mechanical seal change.

TWIN PUMP APPLICATION RANGE*

TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A. 14120-6594 +1 716 693 8813

BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL HALESOWEN, WEST MIDLANDS UNITED KINGDOM B62 8DJ +44 (0) 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM
M11 2ET
+44 (0) 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA 560 003 +91 (0) 80 4906 3555

SHANGHAI


NO. 1619 HU HANG ROAD, XI DU TOWNSHIP FENG XIAN DISTRICT, SHANGHAI P.R.C. 201401 +86 21 3756 6696


SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4781 5500

ARMSTRONG FLUID TECHNOLOGY

ESTABLISHED 1934





4312 SPLIT-COUPLED DESIGN ENVELOPE

INDOORS

OUTDOORS

Integrated to 40hp

Integrated to 40hp


4392 CLOSE-COUPLED DESIGN ENVELOPE

INDOORS

Integrated to 7.5hp

OUTDOORS

Integrated to 7.5hp



Armstrong Design Envelope pumps are available for outdoor applications in Series 4312 and 4392.

*Single phase available to 7.5hp / 5.5kW

Contact us at:

+416 755 2291

armstrongfluidtechnology.com/DE

View your savings and ROI using real data from your installation. Ask your Armstrong representative.



