



Mobile Ultra High-Pressure Wash Unit

Integrated mechanical, hydraulic and electrical safety controls in a versatile portable unit.

Features

Water supply tank - 50-100 US Gallon (190-380L)


High Pressure Plunger Pump
10 US GPM (38 Lpm) @ 32000 PSI (220MPa) flow rate

Discharge manifold

Sugino spray cleaning heads and washing nozzle attachments

SUGINO

Electrical Power is supported by a diesel generator set sized for pump and auxiliaries

John Deere
248hp (185kW)
Diesel engine  **JOHN DEERE**

Pump & Engine are directly coupled (no gearbox required)

Common Trailer Skid supports the engine, pump, tank, and auxiliaries

Safety & Control Components:

Rupture Disk to protect against overpressure

High-Pressure Filter to protect the pump and nozzle

Leak Nozzle Line to handle seal leakage safely

Cylinder Valve (manual) to control water delivery

Applications

Units are available for demonstration at your site upon request

01
Drain Cleaning

02
Rail Culvert Cleaning

03
Cable Duct Desilting

04
Many more applications

Measured Efficiency | Proven Reliability | Advanced Performance