

HSC Fire Pumps & Packaged Systems

FILE NO: DATE: SUPERSEDES: DATE:

F43.11 Sep. 25, 2011 F43.11 May 26, 2008

Series 4600F - Truly Superior

The Series 4600F, drawing on over 100 years of pump design expertise and leadership, is the state of the art in Horizontal Split Case pumps. It meets or exceeds the requirements of NFPA and testing laboratories involved in fire protection such as UL, ULC & FM.

The family of pumps capitalize on the "Tilted Parting" concept to minimize turbulence at the eye of the impeller

by its straight laminar approach, thus maximizing efficiency. The family was designed with commonality of parts, low installation cost, and ease of maintenance objectives.

The pumps' compact sizes are ideally suited for space saving packages and retrofit applications.



Recirculation

• External Water Seal Recirculation Lines

2 Coupling

• UL Listed close-coupled coupling

3 Stuffing Box Housing

- Self contained Combination Bearing & Seal Housing
- Permits packing change-out without having to be removed

4 Drip Containment

Fitted with drain connection

5 Casing Wear Ring

- Replaceable Case Wear Rings
- Locked to prevent rotation or axial displacement
- Impeller Wear Ring available as an option

6 Pump Casing

• Designed to withstand the high pressure requirement typical in fire protection

Impeller

- Hydraulically balanced double suction
- Dynamically balanced
- Minimum axial thrust
- High efficiency throughout operating range

Shaft Sealing with Packing

- Three-piece Split Gland standard
- Packing replaceable without disturbing wetted parts
- Stuffing Box Extension designed for easy access

Shaft Sleeves

- Replaceable bronze sleeves
- Protects shaft throughout Stuffing Box

Bearings


- Easy removal with bearing nut
- Sealed, permanently greased bearings
- Low Friction Lost Bearing
- Maintenance free


Bearing Housing

• Removable without removing top casing

Shaft

- Minimum deflection for long bearing life
- Minimum vibrations
- Identical shaft and parts for left and right-hand drives





Tilted Parting Design Casing

- Permits laminar approach to eye of Impeller
- Lower NPSH required
- Lower pump profile
- Minimum pump footprint
- Removeable rotating element without disturbing piping
- Low foot-mounted Casing to reduce vibrations

HSC Fire Pumps & Packaged Systems

Horizontal Fire Systems

With years of experience in fire protection industry, Armstrong can supply fire pump systems with all necessary accessories ready for site installation.

GUARANTEED ADVANTAGES


- Simplifies piping design
- Single source unit responsibility
- A complete package that will meet NFPA-20 requirements

FIRE PUMP - ELECTRIC DRIVEN

- 1. Pump/motor
- 2. Fire pump controller (with optional transfer switch)
- 3. Suction and discharge gauges
- 4. Air release valve
- 5. Casing relief valve (not shown)
- 6. Jockey pump
- 7. Common base

FIRE PUMP - DIESEL ENGINE DRIVEN

- 1. Pump/engine assembled with
 - Cooling system
 - Fuel system
 - Battery system
 - Exhaust system
- 2. Fire pump controller
- 3. Suction and discharge gauges
- 4. Air release valve



- 6. Jockey pump
- 7. Common base

ACCESSORIES - ADDITIONAL (ELECTRIC OR DIESEL)

- 8. Suction OS&Y gate valve
- 9. Discharge butterfly valve
- 10. Check valve
- 11. Test tee

ACCESSORIES - SPECIAL FOR DIESEL OR VFD

Rated Head (kPa)

1500

1250

1000

500

275


- 12. Main relief valve
- 13. Enclosed cone (not shown)

Fire Pump Coverage Chart

Electrical 60 Hz

Rated Capacity (L/min) 1890 2850 3800 4750 5700 7600 9500 11400 1800 rpm Rated Head (psi) 3600 rpi 200 150 100 50 750 1000 1250 1500 2000 2500 3000 Rated Capacity (USGPM)

Electrical 50 Hz



Features common to electric and diesel

Accessories - special for diesel or VFD

Accessories - (electric or diesel)

Note: Higher ranges may be available for diesel driven applications.

Typical Specifications

Horizontal Fire Pump - Electric Motor Driven*

Supply and install as indicated on plans one (1) fire pump system consisting of:

1. FIRE PUMP

One Armstrong, Series 4600F, Size	double suction
horizontal split case fire pump listed by [Underwriters Laboratories of
Canada (ULC)], [Underwriters Laboratori	es Inc. (UL)] and/or [approved
by Factory Mutual (FM)] having a capacit	y ofusgpm
for a pressure boost of	psig. Suction pressure
PSIG.	

Pump casing shall be of cast iron, axially split with a 15° angle that will minimize npsh requirements and dimensions. Lower half shall contain suction and discharge nozzles. Suction and discharge connections shall be on the same elevation. Top half and rotating element shall be removable without disturbing the piping. Casing shall be fitted with replaceable bronze wearing rings. Impeller shall be bronze, double suction, enclosed type fully balanced and keyed to an alloy steel shaft. Shaft shall to be fitted with replaceable bronze sleeves. Shaft shall be mounted in two dust tight deep grooves, sealed, and permanently greased ball bearings.

Bearings shall be mounted in cartridge type housing so that they shall be replaceable without opening pump casing. Bearings shall be easily removable by rotating bearing removal nut. No special tools or bearing puller are to be necessary.

Each stuffing box shall be fitted with a three piece bronze gland. Stuffing box shall be fitted with a stuffing box extension to facilitate the packing rings removal. Packing rings shall be removable without disturbing wetted parts or the pump bearings. Water seal recirculation lines made from non-corroding material shall be piped to pump volute.

2. ELECTRIC MOTOR

The fire pump shall be d	irectly coupled t	through flexible o	oupling to a
horizontal electric moto	r with a maximu	m нр of	at
RPM,	VOLT ,	PHASE	CYCLE.
Motor shall be ul Listed	for fire pump se	rvice, open drip p	oroof, standard
efficiency with 1.15 servi	ce factor.		

3. MINIMUM FITTINGS

The pump shall be supplied with the following accessories:

- One (1) combination suction gauge 3½" dial type with ¼" cock and lever handle.
- One (1) discharge gauge, $3\frac{1}{2}$ " dial type, with $\frac{1}{4}$ " cock and lever handle.
- One (1) air release valve.
- One (1) casing pressure relief valve.

4. OTHER ACCESSORIES

Pump shall be fitted with one (1) eccentric suction reducer and one (1) concentric discharge increaser, as required (by mechanical contractor) to fit NFPA 20 recommended piping sizes.

One (1) outside test header shall be supplied with one (1) set of $___ x 2\frac{1}{2}$ " hose valves with caps and chains.

5. FIRE PUMP CONTROLLER

The fire pump c	ontroller shall be specifically a	pproved for fire pump
service by [ULC]	, [UL] and/or [FM]. The controll	er shall be of the
combined manu	ıal and automatic stop,	starting method,
Model	as manufactured by	All equipment shall be
enclosed in an a	approved drip proof enclosure.	The control equipment shall
be completely a	ssembled, wired and tested at	point of manufacture prior
to shipment.		
	shall have an interrupting capa ng of kAmps R	,
Water pressure working pressur	switch shall be suitable for	PSI

5A. FIRE PUMP CONTROLLER AND AUTOMATIC TRANSFER SWITCH COMBINATION

The automatic transfe	r switch controller c	ombination shall be approved
by [UL], [ULC] and/or [ғм], Model	as manufactured
by	The automatic tra	nsfer switch and the pump
controller shall each b	e mounted in separa	ate enclosures, mechanically
attached to form one	unit and provide for	protected interlock wiring.

The automatic transfer switch shall be capable of automatic power transfer from normal to alternate______ [generator] / [second utility] emergency power source in case of normal supply failure and automatically re-transfer after restoration of normal power conditions.

6. JOCKEY PUMP

The jockey pump shall	be manufactured l	by	Model
for a	capacity of	usgpm an	d a pressure
boost of	_ psig. The jockey	pump shall be dri	iven by an [oper
drip proof] [totally enclosed fan cooled] electric motor ofHP,			
RPM	VOLT	PHASE	CYCLE

7. JOCKEY PUMP CONTROLLER

The jockey pump shall be controlled by an automatic jockey pump controller model_____ as manufactured by _____ with full voltage starter.

8. MOUNTING AND TESTING

The fire pump shall be suitable for a maximum working pressure of ______. The fire pump shall be hydrostatically tested at twice the maximum working pressure for at least 5 minutes. The fire pump shall be performance tested at rated speed. The fire pump shall furnish not less than 150% of rated capacity at a pressure not less than 65% of rated head. The shut-off total head of the fire pump should not exceed 140% of total rated head. A certified test curve, indicating the flow, head, power and efficiency shall be supplied for the field acceptance test. The fire pump and electric motor shall be base mounted and aligned at the pump manufacturer's factory. Final alignment shall be made after installation on site

S. A. ARMSTRONG LIMITED

23 Bertrand Avenue Toronto, Ontario Canada, M1L 2P3 T 416-755-2291 F 416-759-9101

ARMSTRONG PUMPS INC.

93 East Avenue North Tonawanda, New York U.S.A., 14120-6594 T 716-693-8813 F 716-693-8970

ARMSTRONG INTEGRATED LIMITED

Wenlock Way Manchester United Kingdom, M12 5JL T +44 (0) 8444 145 145 F +44 (0) 8444 145 146





^{*} Please refer to Armstrong Fire Pump Catalogue for Diesel Driven Typical Specifications.