

FILE NO: 90.55 DATE: Aug. SUPERSEDES: New Aug. 13, 2004

DATE: New

IPS Controller 9100

SUBMITTAL

JOB:	REPRESENTATIVE:	REPRESENTATIVE:	
ENGINEER:CONTRACTOR:	ADDDOL/ED DV	DATE:	

SYSTEM LAYOU CONFIGURATION	
Number of pumps being controlled	(Specify 1 to 6)
Number of remote Differential Pressure signals (zones)	(Specify 1 to 18)

IPS CONTROLLER 9100 VARIANT			
	Input Zone Capability	Output Pump Control Capability	Select Standby or Parallel Operation of Pumps (VFDs)
IPS Controller 9101	up to 6 Zones	up to 6 pumps	☐ IPS9101 Standby ☐ IPS9101 Parallel
IPS Controller 9102	up to 12 Zones	up to 6 pumps	☐ IPS9102 Standby ☐ IPS9102 Parallel
IPS Controller 9103	up to 18 Zones	up to 6 pumps	☐ IPS9103 Standby ☐ IPS9103 Parallel



STANDARD FUNCTIONALITY and CONSTRUCTION

- A large-sized (10.4") touchscreen operator interface
- On-screen menu driven operator interface
- Manual or automatic system control (H-O-A selection)
- Remote or local start/stop mode of operation
- Field and factory password security
- · Alarm and event logging of 2000 events
- · Data trending with display screen
- PID control loop, adjustable
- UL Listed and CSA Approved
- Internal circuit breaker protection
- Automatic or manual pump alternation
- End-of-curve pump run out protection
- Best Efficiency Point (BEP) staging
- Wire-to-water efficiency monitoring and staging
- 3 standard alarms: (1) drive, motor overload or pump failure, (2) system fault, (3) zone signal fault
- Separate operating status display of pump status, pump speed(s) and drive status
- Digital inputs for pump differential pressure switches
- Output for remote alarm/horn signal
- Input for silencer of remote alarm/horn
- Separate input screen for DP, flow, temperature and kW sensors
- Separate input screens for differential pressure sensor setpoint and operating range (psi or feet)
- · Logic outputs for VFD automatic by-pass control
- Separate status screen of remote zone signals, zone faults, zone setpoint, and active control zone
- Embedded logic to prevent hunting, pump flow surge and motor overloading
- Multi-color schematic active display of mechanical room hydronic circuit indicating operating status
- Manual control screen for fixed speed, by-pass or selected variable speed settings
- · Secure front cabinet door with lock and key
- · Diagnostic test of CPU, RAM and Flash memory

Armstrong Pumps Inc. 93 East Avenue

North Tonawanda, New York U.S.A. 14120-6594 Tel: (716) 693-8813 Fax: (716) 693-8970

S.A. Armstrong Limited 23 Bertrand Avenue Toronto, Ontario Canada, M1L 2P3

Tel: (416) 755-2291 Fax: (416) 759-9101



DIMENSIONS and WEIGHTS				
Model	Width	Height	Depth	Weight
IPS Controller 9101	24 (610)	24 (610)	8 (203)	95 (43)
IPS Controller 9102		24 (010)	0 (203)	105 (48)
IPS Controller 9103	24 (610)	36 (914)	8 (203)	115 (52)

Note: Dimensions are in inches (mm). Weights are in lbs. (kg).

POWER SUPPLY			
	Volts	Frequency	Phase
	115 Vac	60 Hz 50 Hz	single
	230 Vac		
	240 Vac		

ENCLOSURE		
DETAILS		
□ NEMA 1		
□ NEMA 2		
□ NEMA 4		
□ NEMA 12		
☐ EEMAC 2		

OPTIONS and ACCESSORIES

- ☐ A serial communications port for communication with a Building Automation System (standard communication options included with basic system are Modbus, LonWorks, Trend, Johnson Controls Metasys N2 and pLAN
- ☐ Serial communications port to receive full information from the variable speed drives (VFD's) (Modbus)
- Optional communications gateways for BACnet and Webgate (TCP/IP)
- ☐ Armstrong shall enter the project specific field enter parameters
- ☐ Telephone communications modem and port
- ☐ Flash memory card expandable to 6 MB

Armstrong Pumps Limited

Peartree Road, Stanway Colchester, Essex United Kingdom, CO3 0LP Tel: +44 (0) 1206 579491 Fax: +44 (0) 1206 760532

Armstrong Darling

9001 De L'Innovation, Suite 200 Montreal (Anjou), Quebec Canada, H1J 2X9 Tel: (514) 352-2424 Fax: (514) 352-2425

