

REVISIONS ZONE DESCRIPTION DATE APPROVED REDRAWN WITH CHANGES, SEE E.O. 103786# 10/18/10





6

NOTES:

- 1 Dimensions are based on factory choice standard components.
 For other than standard consult factory, as a new drawing may be required.
- 2 All dimensions are in inches [mm].
- 3 Tolerances are +/- 1/4" [6.35] unless otherwise specified.
- 4 Drawings are for layout purposes only.

Maximum System Pressure: □175 PSI □ 250 PSI

INLET ORIENTATION

☐ LEFT HAND - STD. AS SHOWN (CONSULT DRAWING #2546-100 FOR RIGHT HAND ORIENTATION.)

DIMENSIONS					
DUALPAK	А	В	С	D	
6901-3x3x6	46.41 [1178.72]	31.99 [812.42]	9.25 [234.95]	32.38 [822.45]	
6902-3x3x8	47.41 [1204.12]	34.80 [883.86]	9.50 [241.30]	32.88 [835.03]	
6903-3x3x6	46.41 [1178.72]	31.99 [812.42]	9.25 [234.95]	32.38 [822.45]	
6904-3x3x8	47.41 [1204.12]	34.80 [883.86]	9.50 [241.30]	32.88 [835.03]	

SCALE: 1:12 WEIGHT:

SHEET 1 OF 1

			UNLESS OTHERWISE SPECIFIED:		NAME	DATE		ARMSTRONG (
			DIMENSIONS ARE IN INCHES WEIGHT IN POUNDS	DRAWN	JMC	5/13/10		AKNIS I KUNU	
			TOLERANCES:	CHECKED	PR	10/18/10	TITLE:		_ /
			FRACTIONAL±1/4 ANGULAR: MACH±0.5° BEND±0.5°	Q.A.	JM	10/18/10)1/2/3/4IVS DUA	IDAV
PROPRIETARY AND CONFIDENTIAL			TWO PLACE DECIMAL ± 0.25 THREE PLACE DECIMAL ± 0.250	MFG APPR.	KB	10/18/10	070		
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF			DIMENSIONING AND TOLERANCING PER:	ENG APPR.	JC	10/18/10		LEFT HAND DW	В
S.A. ARMSTRONG. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF S.A. ARMSTRONG IS PROHIBITED.				COMMENTS:					
			MATERIAL				SIZE	DWG. NO.	REV
			FINISH					2546-000	│
	NEXT ASSY	USED ON	LIINISTI	DO N	OT SC	ALE		2546-000	

DESIGN AUTHORITY: S.A. ARMSTRONG

UNLESS OTHERWISE SPECIFIED:

APPLICATION

1	DUALARM PUMP, MOTOR, AND DRIVE	4	BASE & PANEL SUPPORT
2	CHECK VALVE	5	SUCTION PRESSURE GAUGE
3	DUAL PUMP CONTROLLER	6	DISCHARGE PRESSURE GAUGE

DO NOT SCALE

THIRD ANGLE PROJECTION

4