

BRAZED PLATE HEAT EXCHANGER | MODEL ABD030 DOUBLE WALL | SUBMITTAL

File no: 113.579
Date: MAY 28, 2025
Supersedes: NEW
Date: NEW

Job: _____ Representative: _____

Order No: _____ Date: _____

Engineer: _____ Submitted by: _____ Date: _____

Contractor: _____ Approved by: _____ Date: _____

QUANTITY	TAG NO.	MODEL NO.	COMMENTS

ABD - BRAZED PLATE HEAT EXCHANGERS DOUBLE WALL

Armstrong's ABD brazed plate heat exchangers are designed to facilitate heat transfer between two media of different temperatures. ABD produces high heat transfer rates that allow for a compact, corrosion resistant and robust design.

DESCRIPTION

Number of plates (N):	
Design Pressure	435 psi (30 bar)
Max Temperature	392°F / 200°C
Plate Material	316 SS
Braze Material	Copper
Connection Material	316 SS

TYPICAL SPECIFICATION

Furnish and install on the plans and described herein, an Armstrong ABD030-_____ brazed plate heat exchanger. Each heat exchanger must be designed to have the capacity and pressure/temperature rating as detailed in the schedule. The heat exchanger must utilize 316L stainless steel plates and copper braze to separate the two fluids while transferring heat and preventing corrosion.

To prevent cross contamination of the two media the heat exchanger shall be of double wall design. The media shall be separated by two plates with an air gap between them providing a positive leak path with detection grooves.

Each heat exchanger shall be Armstrong ABD030-_____ or approved equal.


CONNECTIONS

	Size - inch	Location	Rating
Fluid 1 Inlet	0.75	A2	MNPT
Fluid 1 Outlet	0.75	A1	MNPT
Fluid 2 Inlet	0.75	B1	MNPT
Fluid 2 Outlet	0.75	B2	MNPT

DIMENSIONS

DIMENSIONS in inch (mm)						VOLUME	WEIGHT
A	B	C	D	E	L	gals(ltrs)	lbs(kgs)
7.95 (202)	6.14 (156)	3.62 (92)	1.81 (46)	0.79 (20)	0.315 + (0.095 × N) (8.0 + (2.4 × N))	(0.007 × N) gals (0.027 × (N-1)) liters	1.39 + (0.229 × N) lbs 0.63 + (0.104× N) kgs

NOTE:
* N = Total number of plates per unit



TORONTO
+1 416 755 2291

BUFFALO
+1 716 693 8813

DROITWICH SPA
+44 8444 145 145

MANCHESTER
+44 8444 145 145

BANGALORE
+91 80 6510 3555

SHANGHAI
+86 21 5237 0909

BEIJING
+86 21 5237 0909

SÃO PAULO
+55 11 4785 1330

LYON
+33 4 20 10 26 21

DUBAI
+971 4 887 6775

JIMBOLIA
+40 256 360 030

FRANKFURT
+49 6173 999 77 55