


DESIGN ENVELOPE 4302 DUALARM | 1515-001.5 | submittal

File No: 100.4422IN Date: AUGUST 14, 2015 Supersedes: 100.4422IN Date: JUNE 15, 2015

Jop:		Representative:			
		Order No:	Date:		
Engineer: Contractor:		Submitted by:	Date: _		
		Approved by:	Date: _		
PUMP DESIGN DATA		CONTROLS DATA			
No. of pumps: Tag:		Sensorless Control:	Standard		
Capacity: m ³ /h(USgpm) Head: Liquid: Viscos		Minimum system pressure to be maintained:		m (ft)*	
Temperature:°C (°F) Specif	-	Protocol (standard):	□ Modbus rtu □ b, □ Johnson® N2 □ S		
Suction: 150mm (6") Discha		Protocol (optional):	\Box LonWorks [®]		
		Enclosure:	: □ Indoor - 1P55 □ Outdoor - 1P66		
MOTOR DESIGN DATA		Fused disconnect switch:			
kW: RPM: Enclosure: Volts: Hertz: 50 Hz Phase: 3 Efficiency: IE2 IE3 EFF2 Frame size: MAXIMUM PUMP OPERATING CONDITIONS PN 16 16 bars at 149°C (232 psig at 300°F) 7 bars at 150°C (100 psig at 300°F) PN 25 25 bars at 149°C (375 psig at 300°F)		Duty/standby pre-wired bridge:			
		EMI/RFI control:	: Integrated filter designed to meet EN61800-3		
		Harmonic suppression:	: Dual Dc-link reactors (Equivalent: 5% Ac line reactor) Supporting IEEE 519-1992 requirements**		
		Cooling: Fan-cooled through back channe		ack channel	
		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)		
		Analog ı/o:	Two current or voltag	le inputs,	
21 bars at 150°C (260 psig at 300°F)		Digital ı/o:	Six programmable in can be configured as		
 Tolerance of ±3 mm (±0.125") should be used For exact installation, data please write factory for 		Pulse inputs:	Two programmable		
certified dimensions	·	Relay outputs:	Two programmable		
		Communication port:	1-rs485, 1-usb		
MECHANICAL SEAL DESIGN DATA See file no. 43.50 for standard mechanical seal details as indicated below		*If minimum maintained system pressure is not known: Default to 40% of design head **The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.			
Armstrong seal reference number					
□ c1 (a) □ Others:					



	INDOOR
	IP55
Frame size:	90L
Size:	1515-001.5
kW:	1.5
RPM:	1500
AB:	540(21.34)
B1:	188(07.40)
B2:	188(07.40)
C1:	346(13.62)
C2:	364(14.33)
D1:	427(16.81)
D2:	427(16.81)
E:	133(05.23)
F:	150(05.90)
Ρ:	190(07.57)
SD:	851(33.50)
т:	197(07.84)
XY:	552(21.73)
Weight:	232.24(512)
Dimensions – n Weight – kg (lb	

Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.

TORONTO +1 416 755 2291

BUFFALO +1 716 693 8813

BIRMINGHAM +44 (0) 8444 145 145


MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555


ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934



[]

INDOOR

:



ARMSTRONGFLUIDTECHNOLOGY.COM

SHANGHAI +86 21 3756 6696