

DPM-100 - Differential Pressure Manometer

SUBMITTAL

JOB: _____	REPRESENTATIVE: _____
_____	_____
ENGINEER: _____	ORDER NO: _____ DATE: _____
CONTRACTOR: _____	SUBMITTED BY: _____ DATE: _____
_____	APPROVED BY: _____ DATE: _____

Quantity	TAG No.	Model No.	Comments

The Differential Pressure Manometer (DPM) is a rugged, digital instrument used to measure the pressure drop or pressure gain across hydronic system components. The DPM-100 has a 0-100 psi measurement range for precise adjustment of circuit balancing valves, and to monitor circulator performance. The unit measures gauge or differential pressure and can store up to 40 readings for later recall. The operator can select from a variety of Imperial and metric measurement units to suit the hydronic system design data. Valuable safety features include visible and audible instrument over-range warning alarms and backlit display for work in poorly illuminated areas. The lightweight, compact DPM design is easy to use in the tight, overhead spaces commonly encountered when balancing or troubleshooting hydronic systems.

TECHNICAL DATA	
Service	Compatible, non-combustible gases & liquids
Wetted Materials	Type 316L Stainless Steel
Accuracy	±0.5% of full scale from 15°C - 25°C (60°F - 78°F); ±1% of full scale from 0°C - 15°C and 25°C - 40°C (32°F - 60°F and 78°F - 104°F)
Measurement Range	DPM-100 0 - 6.9 bar (0 - 100 psi)
Maximum Pressure	DPM-100 13.0 bar (200 psi)
Selectable Pressure Units	psi, in. H ₂ O, in. Hg, mm Hg, kPa, bar and mbar
Operating Temperature Range	0°C to 93°C (32°F to 200°F)
Storage Temperature	-20°C to 80°C (-4°F to 176°F)
Pressure Hysteresis	±0.1% of full scale
Connections	Two 1/8" female NPT
Adapters	Two 1/4" male SAE adapters included
Display	10.6 mm (0.42") 4-1/2 digit LCD with units indicators
Power Source	9 V alkaline battery (included)
Battery Life	Up to 100 hours (less when LCD backlight used)
Agency Approvals	CE



CARRYING CASE includes:

- Made of durable resin material
- Impact-resistant foam packing
- Flexible hoses (one red and one blue) complete with fittings:
 - 1/4" female SAE flare straight fitting (connects to 1/4" SAE adapters on meter)
 - 1/4" female SAE 45° elbow fitting (connects to measuring probes)
- Two pressure measuring probes with adapter fittings
- Two Armstrong ARMflo venturi-style CBV balancing slide rule

DIMENSIONS and WEIGHTS				
Model	Height	Width	Depth	Weight
DPM-100	150 (5-7/8)	70 (2-3/4)	20 (7/8)	0.4 (0.90)
Carrying Case plus hoses & fittings	343 (13-1/2)	432 (17)	114 (4-1/2)	2.6 (5.85)

Note: All dimensions are in mm (inches) and weights are in kg (lbs).

S. A. Armstrong Limited
23 Bertrand Avenue
Toronto, Ontario
Canada, M1L 2P3
T: (416) 755-2291
F (Main): (416) 759-9101

Armstrong Pumps Inc.
93 East Avenue
North Tonawanda, New York
U.S.A. 14120-6594
T: (716) 693-8813
F: (716) 693-8970

Armstrong Integrated Systems Limited
Mucklow Hill
Halesowen, West Midlands
United Kingdom, B62 8DJ
T: +44 (0) 121 550 5333
F: +44 (0) 121 550 1679

