

# **DESIGN ENVELOPE** 4372 TANGO | 3×3×5 (80–125) |

0305-005.0 | SUBMITTAL

File No: 102.5129

Date: MARCH 25, 2021

Supersedes: 102.5129

Date: APRIL 18, 2018

Date:

Date: \_\_

Date: \_\_\_

Job:		Repres	sentative:	
		Order	No:	
Engineer: Sub		Submi	mitted by:	
Contractor:		Appro	ved by:	
PUMP DESIGN DATA		:	DEPM MOT	
No. of pumps:	Tag:	_ :		
Total system design flow:				
Head:ft(m)	Capacity split	% :	Moto	
Flow per pump head:	USgpm(L,	/s) :		
Parallel flow:	USgpm(L,	/s) :		
Liquid:	Viscosity:	_ :		
Temperature: °F (°C)	Specific gravity:	_ :	Protoco	
Suction: 3" (80 mm)	Discharge: 3" (80 mm)			
UL STD 778 & CSA STD C22.2 NO	0.108 certified	:	Contr	
Test report is supplied with each	n pump	:	Fused discor	
MATERIALS OF CONSTRU	ICTION	:	EM	
☐ ANSI 125			Harmonic	
CONSTRUCTION: LPDESF		:	панноніс	
E-coated ductile iron A536	Gr 65-45-12, stainless fitte	ed :		
☐ ANSI 250		:	Ambient t	
construction: HPDESF E-coated ductile iron A536	Gr 120 - 90 - 2. stainless fitt	ed		
		:		
MAXIMUM PUMP OPERA	TING CONDITIONS	:		
ANSI 125  175 psig at 150°F (12 bar at 6)	-°C)	:		
100 psig at 250°F (7 bar at 12			Rommur	
☐ ANSI 250		•	** If supplied with th	
300 psig at 150°F (20 bar at 6	-	:	of the system wide	
250 psig at 250°F (17 bar at 1	21°C)	•	a.so recommend t	

## MECHANICAL SEAL DESIGN DATA : FLOW READO

**Seal type:** 2A **Stationary seat:** Silicone carbide

Secondary seal: EPDM Spring: Stainless steel

Rotating hardware: Stainless steel

## DEPM MOTOR AND CONTROL DATA

**HP:** 5

**RPM:** 3000

Motor enclosure: TEFC

Volts: \_\_\_\_\_

Phase: 3 Efficiency: IE5

**Orientation:** Standard

Protocol (standard): ☐ BACnet™ MS/TP ☐ BACnet™ TCP/IP

☐ Modbus RTU

Control enclosure: ☐ Indoor – UL TYPE 12

☐ Outdoor - UL TYPE 4X

Fused disconnect switch: Consult factory

EMI/RFI control: Integrated filter designed to meet

EN61800-3

Harmonic suppression: Equivalent: 5% Ac line reactor - Sup-

porting IEEE 519-1992 requirements\*\*

Cooling: Fan-cooled, surface cooling

Ambient temperature: -10°C to +45°C up to 1000 meters above

sea level (+14°F to +113°F, 3300 ft)

Analog I/o: Two inputs, one output. Output can

be configured for voltage or current

Digital I/o: Two inputs, two outputs. Outputs can

be configured as inputs

Relay outputs: Two programmable

Communication port: 1-RS485

\* If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

### FLOW READOUT ACCURACY

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMs. The model readout will be factory tested to ensure  $\pm 5\%$  accuracy.

FLUID TYPE	ALL GLYCOLS > 30% WT CONC		ALL OTHER NON-POTABLE FLUIDS		POTABLE (DRINKING) WATER	
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating face	Silicone carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat elastomer	EPDM (L-cup)	EPDM (o-ring)	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (0-ring)
Material code	SCsc L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

2

## **OPTIONS**

## SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

 If minimum maintained system pressure is not known: Default to 40% of design head

## ☐ PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

## ☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

## PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

## □ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

#### Coolina

Cooling		
Duty point	gpm (L/s) at	ft (m)
Minimum syster	n pressure to be maint	ained
	ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum syster	m pressure to be maint	ained
	ft (m)	

## **OPTIONAL SERVICES**

## **ON-SITE PUMP COMMISSIONING**



## **PUMP MANAGER**



Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- \* Requires an internet connection to be provided by building
- \* Includes an extended warranty for parts and labour (wearable parts excluded)


<sup>\*</sup>Only available if sensorless bundle is enabled

<sup>\*</sup>Available in single pump operation only

 $<sup>^\</sup>star Only$  available if sensorless bundle is enabled

<sup>\*</sup>Available in single pump operation only


3




Performance curves are for reference only.


Confirm current performance data with Armstrong ADEPT Quote or ADEPT Select selection software.


## INDOOR











## **DIMENSION DATA**

INDOOR	OUTDOOR	
(UL TYPE 12/TEFC)	(UL TYPE 4X/TEFC)	
3×3×5	3×3×5	
5	5	
3000	3000	
18.33 (466)	20.54 (522)	
6.00 (152)	6.00 (152)	
6.00 (152)	6.00 (152)	
11.20 (284)	11.20 (284)	
11.20 (284)	11.20 (284)	
-	5.00 (127)	
6.82 (173)	6.82 (173)	
8.20 (208)	8.62 (219)	
7.35 (187)	7.35 (187)	
14.17 (360)	14.17 (360)	
5.24 (133)	5.24 (133)	
197 (89.3)	197 (89.3)	
	3×3×5 5 3000 18.33 (466) 6.00 (152) 6.00 (152) 11.20 (284) 11.20 (284) - 6.82 (173) 8.20 (208) 7.35 (187) 14.17 (360) 5.24 (133)	

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of  $\pm 0.125$ " ( $\pm 3$  mm) should be used
- For exact installation, data please write factory for certified dimensions

#### TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

#### BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

#### DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS BUSINESS PARK DROITWICH SPA, WORCESTERSHIRE UNITED KINGDOM, WR9 OLW +44 8444 145 145

#### MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

#### BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

## SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

#### SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

### LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

#### DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

## MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

## JIMBOLIA

STR CALEA MOTILOR NR. 2C JIMBOLIA 305400, JUD.TIMIS ROMANIA +40 256 360 030

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934