

# DESIGN ENVELOPE 4372 TANGO 1.5×1.5×5 (32-125) 1505-001.5 SUBMITTAL

File No: 102.5188 Date: NOVEMBER 08, 2021 Supersedes: NEW Date: NEW

| Jop:        | Representative: |         |  |
|-------------|-----------------|---------|--|
|             | Order No:       | _Date:  |  |
| Engineer:   | Submitted by:   | _Date:  |  |
| Contractor: | Approved by:    | _ Date: |  |

#### PUMP DESIGN DATA

| No. of pumps:                              | Тад:                          |
|--|-------------------------------|
| Total system design flow:                  | USgpm(L/s)                    |
| Head:ft(m)                                 | Capacity split%               |
| Flow per pump head:                        | USgpm(L/s)                    |
| Parallel flow:                             | USgpm(L/s)                    |
| Liquid:                                    | Viscosity:                    |
| Temperature: °F (°C)                       | Specific gravity:             |
| Suction: 1.5" (40 mm)                      | Discharge: 1.5" (40 mm)       |
| UL STD 778 & CSA STD C22.2 NC              | 0.108 certified               |
| Test report is supplied with each          | n pump                        |
| MATERIALS OF CONSTRU                       | JCTION                        |
| 🗆 ANSI 125                                 |                               |
| CONSTRUCTION: LPDESF                       |                               |
| E-coated ductile iron A536                 | Gr 65-45-12, stainless fitted |
| CONSTRUCTION: HPDESF                       |                               |
| E-coated ductile iron A536                 | Gr 120-90-2, stainless fitted |
| MAXIMUM PUMP OPERA                         | TING CONDITIONS               |
| 🗆 ANSI 125                                 |                               |
| 175 psig at 150°F (12 bar at 6             | •                             |
| 100 psig at 250°F (7 bar at 12             | 21°C)                         |
| ANSI 250<br>300 psig at 150°F (20 bar at 1 | ۲۹<br>۲۰<br>۲۰                |
| 250 psig at 250°F (17 bar at 1             |                               |
|  | •                             |
| MECHANICAL SEAL DESI                       | GN DATA :                     |

## Seal type: 2AStationary seat: Silicone carbideSecondary seal: EPDMSpring: Stainless steelRotating hardware: Stainless steel

#### DEPM MOTOR AND CONTROL DATA

| HP:                      | 1.5  |
|--------------------------|--|
| RPM:                     | 3300   |
| Motor enclosure:         |  |
| Volts / Phase:           | 🗆 200-240V/1ph 🛛 380-480V/3ph                            |
|                          | For 200-240V/3ph or 575V/3ph,                            |
|                          | see File #:102.5169                                      |
| Efficiency:              | IE5  |
| Orientation:             | Standard   |
| Protocol (standard):     | □ BACnet <sup>™</sup> MS/TP □ BACnet <sup>™</sup> TCP/IP |
|                          | □ Modbus rtu   |
| Control enclosure:       | 🗆 Indoor – UL TYPE 12                                    |
|                          | 🗆 Outdoor – UL TYPE 12,                                  |
|                          | tested to TYPE 4X  |
| Fused disconnect switch: | See File 100.8131  |
| EMI/RFI control:         | Integrated filter designed to meet                       |
|                          | en61800-3  |
| Harmonic suppression:    | Equivalent: 5% Ac line reactor - Sup-                    |
|                          | porting IEEE 519-1992 requirements**                     |
| Cooling:                 | Fan-cooled, surface cooling                              |
| Ambient temperature:     | -10°c to +40°c up to 1000 meters above                   |
|                          | sea level (+14°F to +104°F, 3300 ft)                     |
| Analog ı/o:              | Two inputs, one output. Output can                       |
|                          | be configured for voltage or current                     |
| Digital ı/o:             | Two inputs, two outputs. Outputs can                     |
|                          | be configured as inputs                                  |
| Relay outputs:           | Two programmable   |
| Communication port:      | 1-RS485  |

\*\* If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

#### FLOW READOUT ACCURACY

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMS. The model readout will be factory tested to ensure  $\pm 5\%$  accuracy.

| FLUID TYPE     | ALL GLYCOLS >      | 30% WT CONC       | ALL OTHER NO        | N-POTABLE FLUIDS       | POTABLE (DRII      | NKING) WATER      |
|----------------|--------------------|-------------------|---------------------|------------------------|--------------------|-------------------|
| Temperature    | up to 200°F / 93°C | over 200°F / 93°C | up to 200°F / 93°C  | over 200°F / 93°C      | up to 200°F / 93°C | over 200°F / 93°C |
| Rotating face  | Silicone           | carbide           | Resin bonded carbon | Antimony loaded carbon | Resin bond         | led carbon        |
| Seat elastomer | EPDM (L-CUP)       | EPDM (O-ring)     | EPDM (L-CUP)        | ердм (o-ring)          | EPDM (L-cup)       | EPDM (O-ring)     |
| Material code  | SCsc l epss 2A     | SCsc 0 epss 2A    | C-SC L EPSS 2A      | ACsc 0 epss 2A         | C-SC L EPSS 2A     | C-sc o epss 2A    |

Design Envelope 4372 Tango

2

#### OPTIONS

#### SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained

ft (m)

 If minimum maintained system pressure is not known: Default to 40% of design head

#### PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

#### ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate

ow rate gpm (L/s)

\*Only available if sensorless bundle is enabled \*Available in single pump operation only

#### PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Cooling

Duty point \_\_\_\_\_ gpm (L/s) at \_\_\_\_\_ ft (m) Minimum system pressure to be maintained \_\_\_\_\_\_ ft (m)

#### Heating

Duty point \_\_\_\_\_ gpm (L/s) at \_\_\_\_\_ ft (m) Minimum system pressure to be maintained ft (m)

\*Available in single pump operation only

### **OPTIONAL SERVICES**

#### **ON-SITE PUMP COMMISSIONING**



#### PUMP MANAGER




Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- \* Requires an internet connection to be provided by building
- \* Includes an extended warranty for parts and labour (wearable parts excluded)

\*Only available if sensorless bundle is enabled



**DIMENSION DATA** 

|         | INDOOR<br>(UL TYPE 12/TEFC) | OUTDOOR<br>(UL TYPE 12,<br>TESTED TO TYPE 4X |
|---------|-----------------------------|--|
| Size:   | 1.5×1.5×5                   | 1.5×1.5×5                                    |
| HP:     | 1.5                         | 1.5  |
| RPM:    | 3300                        | 3300   |
| Frame:  | 71                          | 71   |
| AB:     | 14.51 (464)                 | 15.64 (520)                                  |
| B1:     | 5.86 (149)                  | 5.86 (149)                                   |
| B2:     | 5.86 (149)                  | 5.86 (149)                                   |
| C1:     | 11.00 (279)                 | 11.00 (279)                                  |
| C2:     | -                           | 2.80 (71)                                    |
| CI:     | -                           | 2.80 (71)                                    |
| D:      | 5.14 (102)                  | 5.14 (102)                                   |
| E:      | 5.99 (152)                  | 6.40 (163)                                   |
| s:      | 7.02 (178)                  | 7.02 (178)                                   |
| SD:     | 11.02 (280)                 | 11.02 (280)                                  |
| т:      | 3.50 (89)                   | 3.50 (89)                                    |
| Weight: | 114 (51.7)                  | 114 (51.7)                                   |
|         |                             |  |


Dimensions - inch (mm) Weight – Ibs (kg)


• Tolerance of ±0.125" (±3 mm) should be used

• For exact installation, data please write factory for certified dimensions


Performance curves are for reference only. Confirm current performance data with Armstrong ADEPT Quote or ADEPT Select selection software.


#### INDOOR





#### OUTDOOR





3

#### TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

#### BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

#### DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS BUSINESS PARK DROITWICH SPA, WORCESTERSHIRE UNITED KINGDOM, WR9 OLW +44 8444 145 145

#### MANCHESTER

WOLVERTON STREET MANCHESTER UNITED KINGDOM, M11 2ET +44 8444 145 145

#### BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

#### SHANGHAI

unit 903, 888 north sichuan rd. hongkou district, shanghai china, 200085 +86 21 5237 0909

#### SÃO PAULO

rua josé semião rodrigues agostinho, 1370 galpão 6 embu das artes sao paulo, brazil +55 11 4785 1330

#### LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

#### DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

#### MANNHEIM

DYNAMOSTRASSE 13 68165 mannheim germany +49 621 3999 9858

#### JIMBOLIA

STR CALEA MOTILOR NR. 2C JIMBOLIA 305400, JUD.TIMIS ROMANIA +40 256 360 030

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM