

# **DESIGN ENVELOPE** 4372 TANGO | 2×2×5 (50–125) |

Representative: \_\_

0205H-001.5 | SUBMITTAL

MECHANICAL SEAL DESIGN DATA

Stationary seat: Silicone carbide

**Spring:** Stainless steel

Seal type: 2A

Secondary seal: EPDM

Rotating hardware: Stainless steel

Job:

File No: 102.5193 Date: NOVEMBER 08, 2021 Supersedes: NEW Date: NEW

	Order No:	Date:
Engineer:	_ Submitted by:	Date:
Contractor:	Approved by:	Date:
PUMP DESIGN DATA	DEPM MOTOR ANI	D CONTROL DATA
No. of pumps: Tag:		<b>HP:</b> 1.5
Total system design flow:USgpm Head:ft(m) Capacity splitUSgpm Flow per pump head:USgpm Parallel flow:USgpm		RPM: 3000 sure: TEFC ase: □ 200-240V/1ph □ 380-480V/3p For 200-240V/3ph or 575V/3ph, see File #:102.5106
Liquid: °F (°C) Specific gravity: Suction: 2" (50 mm) Discharge: 2" (50 mm)	Efficie Orienta	ncy: IE5 tion: Standard ard): □ BACnet™ MS/TP □ BACnet™ TCF □ Modbus RTU
UL STD 778 & CSA STD C22.2 NO.108 certified  Test report is supplied with each pump	Control enclos	Sure: Indoor – UL TYPE 12  Outdoor – UL TYPE 12, tested to TYPE 4X
MATERIALS OF CONSTRUCTION  ANSI 125  CONSTRUCTION: LPDESF	EMI/RFI con Harmonic suppress	itch: See File 100.8131 Itrol: Integrated filter designed to meet EN61800-3 sion: Equivalent: 5% AC line reactor - Sup-
E-coated ductile iron A536 Gr 65-45-12, stainless for ANSI 250  CONSTRUCTION: HPDESF  E-coated ductile iron A536 Gr 120-90-2, stainless	Coo Ambient temperat	porting IEEE 519-1992 requirements*  ling: Fan-cooled, surface cooling  ture: -10°C to +40°C up to 1000 meters abo  sea level (+14°F to +104°F, 3300 ft)
MAXIMUM PUMP OPERATING CONDITIONS	Analog	y i/o: Two inputs, one output. Output can be configured for voltage or current
□ <b>ANSI 125</b> 175 psig at 150°F (12 bar at 65°C)	Digital	I I/o: Two inputs, two outputs. Outputs ca be configured as inputs
100 psig at 250°F (7 bar at 121°C)  ANSI 250	Relay outp Communication p	outs: Two programmable port: 1-RS485
300 psig at 150°F (20 bar at 65°C) 250 psig at 250°F (17 bar at 121°C)	of the system wide harmonic	lectrical details, Armstrong will run a computer simulat cs. If system harmonic levels are exceeded Armstrong c narmonic mitigation and the costs for such mitigation.

### TΑ

 $MS/TP \square BACnet^{TM} TCP/IP$ 

## FLOW READOUT ACCURACY

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMS. The model readout will be factory tested to ensure ±5% accuracy.

FLUID TYPE	ALL GLYCOLS >	30% WT CONC	ALL OTHER NO	N-POTABLE FLUIDS	POTABLE (DRI	NKING) WATER
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating face	Silicone	carbide	Resin bonded carbon	Antimony loaded carbon	Resin bond	led carbon
Seat elastomer	EPDM (L-cup)	EPDM (o-ring)	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (O-ring)
Material code	SCsc L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

2

# **OPTIONS**

# SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

# □ PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

## ☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

# □ PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum	flow rate	gpm	(L/	/s

# □ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

### Cooling

Cooling		
Duty point	gpm (L/s) at	ft (m)
Minimum system	pressure to be maint	ained
-	_ ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum system	pressure to be maint	ained
	_ft (m)	

## **OPTIONAL SERVICES**

### **ON-SITE PUMP COMMISSIONING**



# PUMP MANAGER



Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- \* Requires an internet connection to be provided by building
- \* Includes an extended warranty for parts and labour (wearable parts excluded)


<sup>\*</sup>Only available if sensorless bundle is enabled

<sup>\*</sup>Available in single pump operation only

<sup>\*</sup>Only available if sensorless bundle is enabled

<sup>\*</sup>Available in single pump operation only

3




Performance curves are for reference only.


Confirm current performance data with Armstrong ADEPT Quote or ADEPT Select selection software.


# INDOOR

# B1 B2 C2









# **DIMENSION DATA**

	INDOOR (UL TYPE 12/TEFC)	OUTDOOR (UL TYPE 12,
		TESTED TO TYPE 4X)
Size:	2×2×5	2×2×5
HP:	1.5	1.5
RPM:	3000	3000
Frame:	71	71
AB:	14.48 (368)	15.61 (397)
B1:	5.50 (140)	5.50 (140)
B2:	5.50 (140)	5.50 (140)
C1:	11.80 (300)	11.80 (300)
C2:	11.80 (300)	11.80 (300)
CI:	-	2.80 (71)
D:	6.30 (160)	6.30 (160)
E:	5.99 (152)	6.40 (163)
s:	7.83 (199)	7.83 (199)
SD:	13.02 (331)	13.02 (331)
T:	4.30 (109)	4.30 (109)
Weight:	124 (56.2)	124 (56.2)

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of  $\pm 0.125$ " ( $\pm 3$  mm) should be used
- For exact installation, data please write factory for certified dimensions

### TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

### BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

### DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS BUSINESS PARK DROITWICH SPA, WORCESTERSHIRE UNITED KINGDOM, WR9 OLW +44 8444 145 145

### MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

### BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

### SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

### SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

### LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

### DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

### MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

### JIMBOLIA

STR CALEA MOTILOR NR. 2C JIMBOLIA 305400, JUD.TIMIS ROMANIA +40 256 360 030

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934