

DESIGN ENVELOPE DEPM IVS 4300 VIL

0307-025.0 | SUBMITTAL

Armstrong seal reference number

☐ c1 (a) ☐ Others: ____

File No: 100.5183

Date: FEBRUARY 08, 2024

Supersedes: NEW

Date: NEW

I				
Job:		Representative:		
	C	Order No:	Date:	
Engineer:		ubmitted by:	Date:	
Contractor:		approved by:	Date:	
PUMP DESIGN DATA		DEPMH MOTOR AN	ID CONTROLS DATA	
No. of pumps:	Tag:	:	: 25	
Capacity:USgpm (L/s)		Volts	: TEFC	
Liquid:		Filase		
Temperature: °F (°C)		_	-	
Suction: 3" (75mm)	Discharge: 3" (75mm)	_	: □ L1 (default) □ L2 □ L3 □ L4 : □ BACnet™ MS/TP □ BACnet™ TCP/IP	
UL STD 778 & CSA STD C22.2 NO.1	108 certified	: Trotocor (Standard)	☐ Modbus RTU	
Test report is supplied with each pump		Enclosure	: ☐ Indoor – UL TYPE 12	
	•	•	☐ Outdoor – UL TYPE 4X with Weather Shield	
MATERIALS OF CONSTRUCT	TION	•	□ Option for Indoor units	
		Fused disconnect switch:	: ப : Integrated filter designed to meet	
□ ANSI 125		. Limit Ki i Control.	EN61800-3	
CONSTRUCTION: SF		Harmonic suppression:	Dual pc-link reactors (Equivalent: 5% AC	
E-coated cast iron, 316 stainless steel fitted			line reactor) Supporting IEEE 519-1992	
☐ Upgrade impeller to duplex stainless steel fitted (DF)			requirements**	
☐ ANSI 250			Fan-cooled through back channel 10°C to +45°C up to 1000 meters above	
CONSTRUCTION: DSF		: Ambient temperature.	sea level (+14°F to +113°F, 3300 ft)	
E-coated ductile iron, 316 stainless steel fitted		Analog 1/0:	: Two current or voltage inputs,	
☐ Upgrade impeller to duplex stainless steel fitted (DDF)		•	one speed output	
			Two inputs, two outputs	
MAXIMUM PUMP OPERATING CONDITIONS			Pulse inputs: Two programmable Relay outputs: Two programmable	
☐ ANSI 125		Communication port:		
175 psig at 150°F (12 bar at 65°C))			
100 psig at 300°F (7 bar at 150°C)		**The IVS drive is a low harmor	nic drive via built-in pc line reactors. This does not	
		guaranty performance to any	y system wide harmonic specification or the costs to meet	
□ ANSI 250		•	a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation	
375 psig at 150°F (26 bar at 65°C) 260 psig at 300°F (21 bar at 150°C)		•		
200 psig at 300 F (21 Dar at 150)	C)	and the costs for such mitiga	tion.	
MECHANICAL SEAL DESIGN	DATA			
		: : FLOW READOUT AC	CURACY	
See file no. 43.50 for standard mechanical seal details as		: : The Design Fovelone m	nodel selected will provide flow reading	
indicated below		: =	and Collection for the second Dome	

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMS and Pump Manager. The model readout will be factory tested to ensure ±5% accuracy.

2

OPTIONS

SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

☐ PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

*Only available if sensorless bundle is enabled

□ PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

□ ZONE OPTIMIZATION BUNDLE



Controls pumps to ensure multiple zones are satisfied for heating or cooling

 2 sensor control - Controls pumps in a 2-zone application to ensure both zones are always satisfied for heating or cooling

□ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Cooling

Duty point	gpm (L/s) at	ft (m)		
Minimum system pressure to be maintained				
	ft (m)			
Heating				
Duty point	gpm (L/s) at	ft (m)		
Minimum system pressure to be maintained				
	ft (m)			

OPTIONAL SERVICES

ON-SITE PUMP COMMISSIONING



Where purchased and applicable, onsite commissioning by an Armstrong representative will include setting up communication with the Pump (not wiring to BAS), adjusting parameters to match on-site conditions, register the pumps for enhanced warranty and connect the pumps to the router as part of the activation of Pump Manager.

PUMP MANAGER




As a Performance Management Service, Pump Manager is an online automated fault detection and diagnostic service for sustained performance and enhanced reliability. It includes advanced trending, alerts of variance in performance and automated reports.

Available in yearly increments. Includes an option for a price discount on the Extended Warranty Service.

^{*}Only available if sensorless bundle is enabled

^{*}The Service requires an active internet connection.


PERFORMANCE CURVES




Performance curves are for reference only.


Confirm current performance data with Armstrong ADEPT Quote or ADEPT Select selection software.


INDOOR





OUTDOOR






DIMENSION DATA

	INDOOR (UL TYPE 12/TEFC)	OUTDOOR (UL TYPE 4X/TEFC)
Size:	3×3×7.5	3×3×7.5
HP:	25	25
AB:	44.02 (1118)	48.03 (1220)
D:	10.00 (254)	10.00 (254)
E:	17.87 (454)	17.87 (454)
F:	30.00 (762)	30.00 (762)
P:	11.42 (290)	11.42 (290)
s:	12.01 (305)	12.01 (305)
SD:	22.00 (559)	22.00 (559)
T:	6.70 (170)	6.70 (170)
XY:	48.46 (1231)	48.46 (1231)
Weight:	496 (224.9)	499 (226.3)

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of ±0.125" (±3 mm) should be used
- For exact installation, data please write factory for certified dimensions

CONTROL ORIENTATIONS



TORONTO

23 BERTRAND AVENUE, TORONTO, ONTARIO, CANADA, M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE, NORTH TONAWANDA, NEW YORK, USA, 14120-6594 +1 716 693 8813

DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS BUSINESS PARK, DROITWICH SPA, WORCESTERSHIRE, UNITED KINGDOM, WR9 OLW +44 121 550 5333

MANCHESTER

WOLVERTON STREET, MANCHESTER UNITED KINGDOM, M11 2ET +44 161 223 2223

BANGALORE

#18, LEWIS WORKSPACE, 3⁸⁰ FLOOR, OFF MILLERS - NANDIDURGA ROAD, JAYAMAHAL CBD, BENSON TOWN, BANGALORE, INDIA 560 046 +91 80 4906 3555

SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

BEIJING

ROOM 1612, NANYIN BUILDING NO.2 NORTH EAST THRID RING ROAD CHAOYANG DISTRICT, BEIJING, CHINA 100027 +86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES, SAO PAULO, BRAZIL +55 11 4785 1330

LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

JIMBOLIA

STR CALEA MOTILOR NR. 2C JIMBOLIA 305400, JUD.TIMIS ROMANIA +40 256 360 030

FRANKFURT

WESTERBACHSTRASSE 32, D-61476 KRONBERG IM TAUNUS GERMANY +49 6173 999 77 55

ARMSTRONG FLUID TECHNOLOGY® ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM