


## DESIGN ENVELOPE 4302 DUALARM | 1015-00.75 | submittal

File No: 100.4412IN Date: AUGUST 14, 2015 Supersedes: 100.4412IN Date: JUNE 15, 2015

Job:		Representative:	
		Order No:	Date:
Engineer:		Submitted by:	Date:
		Approved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	
No. of pumps:	Тад:	Sensorless Control:	Standard
Capacity: m³/h(USgpm) Liquid:		Minimum system pressure to be maintained:	m (ft)*
Temperature:°C (°F)	Specific gravity:	Protocol (standard):	□ Modbus rtu □ bacnet™ ms/tp □ Johnson® N2 □ Siemens® fln
Suction: 100mm (4")	Discharge: 100mm (4")	Protocol (optional):	□ LonWorks <sup>®</sup>
MOTOR DESIGN DATA		Enclosure:	□ Indoor - 1P55 □ Outdoor - 1P66
	<b>F</b> 1	Fused disconnect switch:	
kW: RPM: Enclosure:   Volts: Hertz: 50 Hz Phase: 3   Efficiency:   IE2 IE3   EFF2 Frame size:   MAXIMUM PUMP OPERATING CONDITIONS PN 16   16 bars at 149°C (232 psig at 300°F)   7 bars at 150°C (100 psig at 300°F)   PN 25   25 bars at 149°C (275 psig at 300°F)   21 bars at 150°C (260 psig at 300°F)   Televence of Leaver (Leaver) about the used		Duty/standby pre-wired bridge:	
			Integrated filter designed to meet EN61800-3
		Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
		Cooling:	Fan-cooled through back channel
		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
		Analog ı/o:	Two current or voltage inputs, one current output
		Digital ı∕o:	Six programmable inputs (two can be configured as outputs)
<ul> <li>Tolerance of ±3 mm (±0.125") should be used</li> <li>For exact installation, data please write factory for certified dimensions</li> </ul>		Pulse inputs:	Two programmable
		Relay outputs:	Two programmable
		Communication port:	1-RS485, 1-USB
<b>MECHANICAL SEAL DESIGN DATA</b> See file no. 43.50 for standard mechanical seal details as indicated below		*If minimum maintained system pressure is not known: Default to 40% of design head **The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.	
Armstrong seal reference number			
□ c1 (a) □ Others:			



Design Envelope 4302 dualArm




INDOOR IP55		
Frame size:	80	
Size:	1015-00.75	
kW:	0.75	
RPM:	1500	
AB:	490(19.38)	
B1:	173(06.81)	
B2:	173(06.81)	
C1:	308(12.12)	
C2:	321(12.63)	
D1:	352(13.94)	
D2:	352(13.94)	
E:	123(04.84)	
F:	148(05.82)	
P:	170(06.78)	
SD:	676(26.61)	
т:	147(05.87)	
XY:	502(19.85)	
Weight:	170.55(375)	
Dimensions – mm (inch) Weight – kg (lbs)		

Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.

INDOOR



TORONTO +1 416 755 2291

BUFFALO +1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER


+44 (0) 8444 145 145

BANGALORE

SHANGHAI

+91 (0) 80 4906 3555

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934



ARMSTRONGFLUIDTECHNOLOGY.COM

+86 21 3756 6696