

# DESIGN ENVELOPE 4302 DUALARM | 1015-001.5 | SUBMITTAL

Armstrong seal reference number

☐ Others:

□ c1 (a)

File No: 100.44161N **Date:** AUGUST 14, 2015 Supersedes: 100.4416IN **Date:** JUNE 15, 2015


Job:		Representative:	
		Order No:	Date:
Engineer:		Submitted by:	Date:
Contractor:		Approved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	
No. of pumps:	Tag:	Sensorless Control:	Standard
Capacity: m³/h(USgpm) Liquid:		Minimum system pressure to be maintained:	m (ft)*
Temperature:°C (°F)	Specific gravity:	Protocol (standard):	☐ Modbus RTU ☐ BACnet™ MS/TP☐ Johnson® N2 ☐ Siemens® FLN
Suction: 100mm (4")	Discharge: 100mm (4")	Protocol (optional):	$\square$ LonWorks $^{\circledR}$
		Enclosure:	☐ Indoor - IP55 ☐ Outdoor - IP66
MOTOR DESIGN DATA		: Fused disconnect switch:	
kW: RPM:	Enclosure:	: Duty/standby	
Volts: Hertz: 50 Hz Phase: 3		pre-wired bridge:	
Efficiency:   IE2   IE3   IEFF2   Frame size:  MAXIMUM PUMP OPERATING CONDITIONS		EMI/RFI control:	Integrated filter designed to meet EN61800-3
		Harmonic suppression:	Dual Dc-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
PN 16		Cooling:	Fan-cooled through back channel
16 bars at 149°C (232 psig at 300°F) 7 bars at 150°C (100 psig at 300°F)		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
<b>PN 25</b> 25 bars at 149°C (375 psig at 300°F) 21 bars at 150°C (260 psig at 300°F)		Analog ı/o:	Two current or voltage inputs, one current output
		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
<ul> <li>Tolerance of ±3 mm (±0.125") should be used</li> <li>For exact installation, data please write factory for certified dimensions</li> </ul>		Pulso inputs	Two programmable
		:	Two programmable
		Communication port:	
		. Communication port:	1 K3405, 1-030
MECHANICAL SEAL DESIG	ON DATA	•	ure is not known: Default to 40% of design head
See file no. 43.50 for standard mechanical seal details as indicated below		guaranty performance to any syster	drive via built-in DC line reactors. This does not m wide harmonic specification or the costs to supplied with the system electrical details,

Armstrong will run a computer simulation of the system wide harmonics. If system

harmonic levels are exceeded Armstrong can also recommend additional harmonic

mitigation and the costs for such mitigation.

2



Performance curves are for reference only.


Confirm current performance data with Armstrong ACE Online selection software.

#### **DIMENSION DATA**

	INDOOR		
	IP55		
Frame size:	90L		
Size:	1015-001.5		
kW:	1.5		
RPM:	1800		
AB:	533(21.07)		
B1:	173(06.81)		
B2:	173(06.81)		
C1:	308(12.12)		
C2:	321(12.63)		
D1:	352(13.94)		
D2:	352(13.94)		
E:	133(05.23)		
F:	150(05.90)		
P:	190(07.57)		
SD:	676(26.61)		
T:	147(05.87)		
XY:	545(21.54)		
Weight:	186.88(411)		
Dimensions - mm (inch)			

Dimensions - mm (inch) Weight - kg (lbs)

## INDOOR



#### **TORONTO** +1 416 755 2291

# BUFFALO

+1 716 693 8813

## BIRMINGHAM

+44 (0) 8444 145 145

## MANCHESTER

+44 (0) 8444 145 145

#### BANGALORE

+91 (0) 80 4906 3555

### SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM