

DESIGN ENVELOPE 4302 DUALARM

1515-007.5 | **SUBMITTAL**

Armstrong seal reference number

☐ Others:

□ c1 (a)

File No: 100.44252IN

Date: AUGUST 14, 2015

Supersedes: 100.44252IN

Date: JUNE 15, 2015


Job:		Representative:	
		Order No:	Date:
Engineer:		Submitted by:	Date:
Contractor:		Approved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	
No. of pumps:	Tag:	Sensorless Control:	Standard
Capacity: m³/h(USgpm) Liquid:		Minimum system pressure to be maintained:	m (ft)*
Temperature:°C (°F)	Specific gravity:	Protocol (standard):	☐ Modbus RTU ☐ BACnet™ MS/TP☐ Johnson® N2 ☐ Siemens® FLN
Suction: 150mm (6")	Discharge: 150mm (6")	Protocol (optional):	\square LonWorks $^{\circledR}$
		Enclosure:	□ Indoor - IP55 □ Outdoor - IP66
MOTOR DESIGN DATA		Fused disconnect switch:	
kW: RPM: Enclosure:		: Duty/standby	
Volts: Hertz: 50 Hz Phase: 3		pre-wired bridge:	
Efficiency: ☐ IE2 ☐ IE3 ☐ EFF2 Frame size:		EMI/RFI control:	Integrated filter designed to meet EN61800-3
MAXIMUM PUMP OPERAT	ING CONDITIONS	Harmonic suppression:	Dual Dc-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
PN 16		Cooling:	Fan-cooled through back channel
16 bars at 149°C (232 psig at 300°F) 7 bars at 150°C (100 psig at 300°F)		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
PN 25 25 bars at 149°C (375 psig at 300°F)		Analog ı/o:	Two current or voltage inputs,
21 bars at 150°c (260 psig at 300	°F)	Dicital you	one current output
a Talayanaa af ta mara (ta gar'') ahayild ha yaad		Digital 1/0:	Six programmable inputs (two can be configured as outputs)
 Tolerance of ±3 mm (±0.125") should be used For exact installation, data please write factory for certified dimensions 		Pulse inputs:	Two programmable
		Relay outputs:	Two programmable
		Communication port:	1-RS485, 1-USB
MECHANICAL SEAL DESIG	ON DATA	*If minimum maintained system press	ure is not known: Default to 40% of design head
See file no. 43.50 for standard mechanical seal details as indicated below		guaranty performance to any syster	drive via built-in oc line reactors. This does not m wide harmonic specification or the costs to supplied with the system electrical details,

Armstrong will run a computer simulation of the system wide harmonics. If system

harmonic levels are exceeded Armstrong can also recommend additional harmonic

mitigation and the costs for such mitigation.

2



Performance curves are for reference only.


Confirm current performance data with Armstrong ACE Online selection software.

DIMENSION DATA

	INDOOR
	IP55
Frame size:	1325
	1515-007.5
kW:	
RPM:	3000
AB:	678(26.78)
В1:	188(07.40)
B2:	188(07.40)
C1:	346(13.62)
C2:	364(14.33)
D1:	427(16.81)
D2:	427(16.81)
E:	175(06.97)
F:	212(08.34)
P:	280(11.02)
SD:	851(33.50)
T:	197(07.84)
XY:	690(27.25)
Weight:	306.62(675)
Dimensions - n	nm (inch)

Weight - kg (lbs)

INDOOR



AB XY

TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM