

# DESIGN ENVELOPE 4302 DUALARM | 1515-011.0 | SUBMITTAL

Armstrong seal reference number

☐ Others:

□ c1 (a)

File No: 100.4426IN **Date:** AUGUST 14, 2015 Supersedes: 100.4426IN **Date:** JUNE 15, 2015


| Job:  |                       | Representative:   |   |
|---|-----------------------|---|---|
|   |                       | Order No:   | Date:   |
| Engineer:   |                       | Submitted by:   | Date:   |
| Contractor:   |                       | Approved by:  | Date:   |
| PUMP DESIGN DATA  |                       | CONTROLS DATA   |   |
| No. of pumps:   | Tag:                  | Sensorless Control:   | Standard  |
| Capacity: m³/h(USgpm) Liquid:   |                       | Minimum system pressure to be maintained:                                   | m (ft)*   |
| Temperature:°C (°F)   | Specific gravity:     | Protocol (standard):  | ☐ Modbus RTU ☐ BACnet <sup>™</sup> MS/T☐ Johnson® N2 ☐ Siemens® FLN   |
| Suction: 150mm (6")   | Discharge: 150mm (6") | Protocol (optional):  | $\square$ LonWorks $^{\mathbb{R}}$  |
|   |                       | Enclosure:  | ☐ Indoor - IP55<br>☐ Outdoor - IP66   |
| MOTOR DESIGN DATA   |                       | Fused disconnect switch:  |   |
| kW:   | Enclosure:            | Duty/standby  |   |
| Volts: Hertz: 5   | 50 Hz Phase: 3        | pre-wired bridge:   |   |
| Efficiency: ☐ IE2 ☐ IE3 ☐ EFF2 Frame size:  |                       | EMI/RFI control:  | Integrated filter designed to meet EN61800-3  |
| MAXIMUM PUMP OPERAT   | FING CONDITIONS       | Harmonic suppression:   | Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**  |
| PN 16   |                       | Cooling:  | Fan-cooled through back channel   |
| 16 bars at 149°C (232 psig at 300 7 bars at 150°C (100 psig at 300°   |                       | Ambient temperature:  | -10°C to +45°C up to 1000<br>meters above sea level<br>(-14°F to +113°F, 3300 ft)   |
| PN 25<br>25 bars at 149°C (375 psig at 300°F)   |                       | Analog 1/0:   | Two current or voltage inputs, one current output   |
| 21 bars at 150°C (260 psig at 300   | °F)                   | Digital ı/o:  | Six programmable inputs (two can be configured as outputs)  |
| <ul> <li>Tolerance of ±3 mm (±0.125") should be used</li> <li>For exact installation, data please write factory for certified dimensions</li> </ul> |                       | Pulse innuts  | -   |
|   |                       |   | Pulse inputs: Two programmable  Relay outputs: Two programmable   |
|   |                       | : Communication port:   |   |
| MECHANICAL SEAL DESIG   | GN DATA               |   | ure is not known: Default to 40% of design hea  |
| See file no. 43.50 for standard mechanical seal details as indicated below  |                       | **The IVS 102 drive is a low harmonic of guaranty performance to any system | drive via built-in pc line reactors. This does not<br>m wide harmonic specification or the costs to<br>supplied with the system electrical details, |

Armstrong will run a computer simulation of the system wide harmonics. If system

harmonic levels are exceeded Armstrong can also recommend additional harmonic

mitigation and the costs for such mitigation.

2




Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.

### **DIMENSION DATA**

|   | INDOOR<br>IP55 |  |
|---|----------------|--|
|   | ,,             |  |
| Frame size:                                 | 160M           |  |
| Size:                                       | 1515-011.0     |  |
| kW:   | 11             |  |
| RPM:  | 3000           |  |
| AB:   | 852(33.54)     |  |
| B1:   | 188(07.40)     |  |
| B2:   | 188(07.40)     |  |
| C1:   | 346(13.62)     |  |
| C2:   | 364(14.33)     |  |
| D1:   | 427(16.81)     |  |
| D2:   | 427(16.81)     |  |
| E:  | 208(08.27)     |  |
| F:  | 430(16.92)     |  |
| P:  | 315(12.40)     |  |
| SD:   | 851(33.50)     |  |
| T:  | 197(07.84)     |  |
| XY:   | 740(29.13)     |  |
| Weight:                                     | 421.38(928)    |  |
| Dimensions – mm (inch)<br>Weight – kg (lbs) |                |  |

# INDOOR



# AB XY

#### TORONTO

+1 416 755 2291

#### BUFFALO

+1 716 693 8813

# BIRMINGHAM

+44 (0) 8444 145 145

# MANCHESTER

+44 (0) 8444 145 145

#### BANGALORE

+91 (0) 80 4906 3555

# SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM