

DESIGN ENVELOPE 4302 DUALARM |

1020-003.0 | SUBMITTAL

Armstrong seal reference number

☐ Others:

□ c1 (a)

File No: 100.44462IN

Date: AUGUST 14, 2015

Supersedes: 100.44462IN

Date: JUNE 15, 2015


Job:		Representative:	
		Order No:	Date:
Engineer:		Submitted by:	Date:
Contractor:		Approved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	
No. of pumps:	Tag:	Sensorless Control:	Standard
Capacity: m³/h(USgpm) Liquid:		Minimum system pressure to be maintained:	m (ft)*
Temperature:°C (°F)	Specific gravity:	Protocol (standard):	☐ Modbus RTU ☐ BACnet™ MS/TP☐ Johnson® N2 ☐ Siemens® FLN
Suction: 100mm (4")	Discharge: 100mm (4")	Protocol (optional):	\square LonWorks $^{\circledR}$
		Enclosure:	☐ Indoor - IP55 ☐ Outdoor - IP66
MOTOR DESIGN DATA		: Fused disconnect switch:	
kW: RPM:	Enclosure:	: Duty/standby	
Volts: Hertz: 50 Hz Phase: 3		pre-wired bridge:	
Efficiency: ☐ IE2 ☐ IE3 ☐ EFF2 Frame size: MAXIMUM PUMP OPERATING CONDITIONS		EMI/RFI control:	Integrated filter designed to meet EN61800-3
		Harmonic suppression:	Dual Dc-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
PN 16		Cooling:	Fan-cooled through back channel
16 bars at 149°C (232 psig at 300°F) 7 bars at 150°C (100 psig at 300°F)		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
PN 25 25 bars at 149°C (375 psig at 300°F) 21 bars at 150°C (260 psig at 300°F)		Analog ı/o:	Two current or voltage inputs, one current output
		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
 Tolerance of ±3 mm (±0.125") should be used For exact installation, data please write factory for certified dimensions 		Pulso inputs	Two programmable
		:	Two programmable
		Communication port:	
		. Communication port:	1 K3405, 1-030
MECHANICAL SEAL DESIG	ON DATA	•	ure is not known: Default to 40% of design head
See file no. 43.50 for standard mechanical seal details as indicated below		guaranty performance to any system	drive via built-in DC line reactors. This does not m wide harmonic specification or the costs to supplied with the system electrical details,

Armstrong will run a computer simulation of the system wide harmonics. If system

harmonic levels are exceeded Armstrong can also recommend additional harmonic

mitigation and the costs for such mitigation.

2



Performance curves are for reference only.


Confirm current performance data with Armstrong ACE Online selection software.

DIMENSION DATA

	INDOOR	
	IP55	
Frame size:	100L	
Size:	1020-003.0	
kW:	3	
RPM:	1800	
AB:	567(22.32)	
B1:	222(08.74)	
B2:	222(08.74)	
C1:	383(15.16)	
C2:	397(15.62)	
D1:	377(14.84)	
D2:	377(14.84)	
E:	138(05.43)	
F:	167(06.66)	
P:	200(07.96)	
SD:	702(27.63)	
T:	160(06.38)	
XY:	579(22.88)	
Weight:	244.94(540)	
Dimensions - n	nm (inch)	

Weight - kg (lbs)

INDOOR



TORONTO +1 416 755 2291

+1 410 /55 229

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM