

# DESIGN ENVELOPE 4380 VIL | 0206-007.5 | SUBMITTAL

File No: 100.4312

Date: JANUARY 14, 2016

Supersedes: 100.4312

Date: AUGUST 14, 2015

Job:	epresentative:			
	Order No:	Date:		
Engineer:	Submitted by:	Date:		
Contractor:	Approved by:	Date:		
PUMP DESIGN DATA	CONTROLS DATA			
No. of pumps: Tag:	: Sensorless control:	Standard		
Capacity:USgpm (L/s) Head:ft (m	to be maintained:	ft (m)*		
Viscosity:	: Orientation:	□ L1 (default) □ L2 □ L3 □ L4		
Temperature:°F (°C) Specific gravity: Suction: 2" (50mm) Discharge: 2" (50mm)	,	☐ Modbus RTU ☐ BACnet™ MS/TP☐ Johnson® N2 ☐ Siemens® FLN		
DISCHAIGE: 2 (3011111) DISCHAIGE: 2 (3011111) DISCHAIGE: 2 (3011111)	Protocol (optional):	☐ LonWorks®		
JL STD 778 & CSA STD C22.2 NO.108 certified	Enclosure:	☐ Indoor – UL TYPE 12 ☐ Outdoor – UL TYPE 4X with weather shield		
MOTOR DESIGN DATA		☐ Outdoor - UL TYPE 4X less weather shield		
np: rpm:Frame size: Enclosure:	Fused disconnect switch:			
Volts: Hertz: 60 Hz Phase: 3	ЕМІ/RFI control:	Integrated filter designed to meet EN61800-3		
Efficiency: NEMA premium 12.12  MAXIMUM PUMP OPERATING CONDITION:		Dual DC-link reactors (equivalent: 5% AC line reactor) supporting IEEE 519-1992 requirements**		
		Fan-cooled through back channel		
<b>ANSI 125</b> 175 psig at 150°F (12 bars at 65°C)	Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)		
140 psig at 250°F (10 bars at 121°C)	Analog ı/o:	Two current or voltage inputs, one current output		
<b>ANSI 250</b> 300 psig at 150°F (20 bars at 65°C)	Digital ı/o:	Six programmable inputs (two can be configured as outputs)		
250 psig at 250°F (17 bars at 121°C)	Pulse inputs:	Two programmable		
• Tolerance of ±0.125" (±3 mm) should be used	Relay outputs:	Two programmable		
<ul> <li>For exact installation, data please write factory for</li> </ul>	: Communication port:	1-RS485, 1-USB		

<sup>\*</sup>If minimum maintained system pressure is not known: Default to 40% of design head

\*\*The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not
guaranty performance to any system wide harmonic specification or the costs to meet
a system wide specification. If supplied with the system electrical details, Armstrong
will run a computer simulation of the system wide harmonics. If system harmonic
levels are exceeded Armstrong can also recommend additional harmonic mitigation
and the costs for such mitigation.

FLUID TYPE	ALL GLYCOLS > 30% WT CONC		ALL OTHER NON-POTABLE FLUIDS		POTABLE (DRINKING) WATER	
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating face	Silicone carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat elastomer	EPDM (L-cup)	EPDM (O-ring)	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (O-ring)
Material code	SCsc L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

certified dimensions

Seal type: 2A


Secondary seal: EPDM

Spring: Stainless steel

**MECHANICAL SEAL DATA** 

Stationary seat: Silicone carbide

Rotating hardware: Stainless steel





Performance curves are for reference only.  $Confirm\ current\ performance\ data\ with\ Armstrong\ ACE\ Online\ selection\ software.$ 


## **DIMENSION DATA**


	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)		
Frame size: 184		213		
Size:	2×2×6	2×2×6		
HP:	7.5	7.5		
RPM:	3600	3600		
AB:	24.22(615)	30.76(781)		
в:	4.47(114)	4.47(114)		
c:	4.47(114)	4.47(114)		
D: E: P: F:	7.00(178)	7.00(178)		
	14.21(361)	18.36(466)		
	10.38(264)	11.13(283)		
	22.20(564)	26.36(669)		
s:	8.00(203)	8.00(203)		
SD:	15.00(381)	15.00(381)		
T:	4.88(124)	4.88(124)		
XY:	19.25(489)	23.50(597)		
Weight:	235(106.6)	309(140.2)		


Dimensions - inch (mm) Weight - lbs (kg)











TORONTO +1 416 755 2291

#### BUFFALO

+1 716 693 8813

#### BIRMINGHAM

+44 (0) 8444 145 145

#### MANCHESTER

+44 (0) 8444 145 145

#### BANGALORE

+91 (0) 80 4906 3555

### SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM