

DESIGN ENVELOPE 4380 VIL | 0308-001.5 | SUBMITTAL

File No: 100.4337 Date: JANUARY 14, 2016 Supersedes: NEW Date: NEW

Job:	Representative:		
	Order No:	Date:	
Engineer:	Submitted by:	Date:	
Contractor:	_ Approved by:	Date:	
PUMP DESIGN DATA	CONTROLS DATA		

No. of pumps:	Tag:
Capacity:USgpm (L/s)	Head:ft (m
Liquid:	Viscosity:
Temperature:°F (°C)	Specific gravity:
Suction: 3" (75mm)	Discharge: 3" (75mm)
ознро Seismic Certification os	P-0422-10
UL STD 778 & CSA STD C22.2 NO	0.108 certified

MOTOR DESIGN DATA

hp: rpm:	Frame size:	_ Enclosure:	
Volts:	Hertz: 60 Hz	Phase: 3	
Efficiency: NEMA	A premium 12.12		

MAXIMUM PUMP OPERATING CONDITIONS

ANSI 125

175 psig at 150°F (12 bars at 65°C) 140 psig at 250°F (10 bars at 121°C)

ANSI 250

300 psig at 150°F (20 bars at 65°C) 250 psig at 250°F (17 bars at 121°C)

- Tolerance of ±0.125" (±3 mm) should be used
- For exact installation, data please write factory for certified dimensions

MECHANICAL SEAL DATA

Seal type: 2A Secondary seal: EPDM Spring: Stainless steel

Stationary seat: Silicone carbide Rotating hardware: Stainless steel

Sensorless control: Standard Minimum system pressure to be maintained: _ _____ ft (m)* Orientation: ☐ L1 (default) ☐ L2 ☐ L3 ☐ L4 **Protocol (standard):** ☐ Modbus RTU ☐ BACnetTM MS/TP ☐ Johnson® N2 ☐ Siemens® FLN **Protocol (optional):** ☐ LonWorks® **Enclosure:** ☐ Indoor – UL TYPE 12 ☐ Outdoor - UL TYPE 4X with weather shield ☐ Outdoor - UL TYPE 4X less weather shield Fused disconnect switch: □ EMI/RFI control: Integrated filter designed to meet

EN61800-3

Harmonic suppression: Dual Dc-link reactors (equivalent: 5%

AC line reactor) supporting IEEE 519-1992 requirements**

Cooling: Fan-cooled through back channel

Ambient temperature: -10°C to +45°C up to 1000 meters above

sea level (-14°F to +113°F, 3300 ft)

Analog I/o: Two current or voltage inputs,

one current output

Digital I/o: Six programmable inputs (two can be


configured as outputs)

Pulse inputs: Two programmable Relay outputs: Two programmable

Communication port: 1-RS485, 1-USB

*If minimum maintained system pressure is not known: Default to 40% of design head ** The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

FLUID TYPE	ALL GLYCOLS >	30% WT CONC	ALL OTHER NO	N-POTABLE FLUIDS	POTABLE (DRIN	IKING) WATER
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating face	Silicone	carbide	Resin bonded carbon	Antimony loaded carbon	Resin bond	ed carbon
Seat elastomer	EPDM (L-cup)	EPDM (O-ring)	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (O-ring)
Material code	SCSC L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A




Performance curves are for reference only.

 $Confirm\ current\ performance\ data\ with\ Armstrong\ ACE\ Online\ selection\ software.$

DIMENSION DATA

	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)
Frame size:	182	184
Size:	3×3×8	3×3×8
HP:	1.5	1.5
RPM:	1500	1500
AB:	21.87(555)	21.87(555)
в:	6.75(171)	6.75(171)
c:	5.80(147)	5.80(147)
D:	10.00(254)	10.00(254)
E:	12.75(324)	12.75(324)
F:	12.75(324)	12.75(324)
P:	9.50(241)	9.50(241)
s:	12.00(305)	12.00(305)
SD:	22.00(559)	22.00(559)
T:	6.31(160)	6.31(160)
XY:	20.01(508)	20.01(508)
Weight:	320(145.1)	336(152.4)

Dimensions - inch (mm) Weight - lbs (kg)



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER


+44 (0) 8444 145 145


BANGALORE


+91 (0) 80 4906 3555


SHANGHAI

+86 21 3756 6696









ARMSTRONG FLUID TECHNOLOGY

ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM