

DESIGN ENVELOPE 4302 DUALARM | 2025-055.0 | SUBMITTAL

Armstrong seal reference number

☐ Others:

□ c1 (a)

File No: 100.4504IN **Date:** AUGUST 14, 2015 Supersedes: 100.4504IN **Date:** JUNE 15, 2015


Job:		Representative:	
		Order No:	Date:
Engineer:		Submitted by:	Date:
Contractor:		Approved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	
No. of pumps:	Tag:	: Sensorless Control:	Standard
Capacity: m³/h(USgpm) Liquid:		Minimum system pressure to be maintained:	m (ft)*
Temperature:°C (°F) Suction: 200mm (8")	Specific gravity:	Protocol (standard):	☐ Modbus rtu ☐ BACnet™ MS/T☐ Johnson® N2 ☐ Siemens® FLN
		Protocol (optional):	☐ LonWorks®
		Enclosure:	☐ Indoor - IP55 ☐ Outdoor - IP66
MOTOR DESIGN DATA		Fused disconnect switch:	
kW: RPM:	Enclosure:	: Duty/standby	
Volts: Hertz: 50 Hz Phase: 3		pre-wired bridge:	
Efficiency: ☐ IE2 ☐ IE3 ☐ EFF2 Frame size:		EMI/RFI control:	Integrated filter designed to meet EN61800-3
MAXIMUM PUMP OPERAT	TING CONDITIONS	Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
PN 16		Cooling:	Fan-cooled through back channel
16 bars at 149°C (232 psig at 300°F) 7 bars at 150°C (100 psig at 300°F)		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
PN 25 25 bars at 149°C (375 psig at 300°F) 21 bars at 150°C (260 psig at 300°F)		Analog 1/0:	Two current or voltage inputs, one current output
		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
 Tolerance of ±3 mm (±0.125") should be used For exact installation, data please write factory for certified dimensions 		Pulse inputs:	Two programmable
			Two programmable
		Communication port:	
MECHANICAL SEAL DESIG	GN DATA	*If minimum maintained system press	ure is not known: Default to 40% of design hea
See file no. 43.50 for standard mechanical seal details as indicated below		guaranty performance to any system	drive via built-in pc line reactors. This does not in wide harmonic specification or the costs to i supplied with the system electrical details,

Armstrong will run a computer simulation of the system wide harmonics. If system

harmonic levels are exceeded Armstrong can also recommend additional harmonic

mitigation and the costs for such mitigation.

2



Performance curves are for reference only.


Confirm current performance data with Armstrong ACE Online selection software.

DIMENSION DATA

	INDOOR
	IP55
Frame size:	250M
Size:	2025-055.0
kW:	55
RPM:	3000
AB:	1164(45.82)
B1:	305(12.00)
B2:	292(11.58)
C1:	522(20.64)
C2:	533(21.07)
D1:	533(21.07)
D2:	635(25.08)
E:	418(16.54)
F:	572(22.51)
P:	510(20.16)
SD:	1168(46.07)
T:	225(08.94)
XY:	1212(47.71)
Weight:	1568.90(3458)

Dimensions - mm (inch) Weight - kg (lbs)

INDOOR



AB XY

TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM