

DESIGN ENVELOPE 4312 TWIN | 1015-001.1 | SUBMITTAL

File No: 100.4728IN

Date: AUGUST 14, 2015

Supersedes: 100.4728IN

Date: MAY 27, 2015

Job:		Representative:	
		Order No:	Date:
Engineer:		Submitted by:	Date:
Contractor:		Approved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	
No. of pumps:	Tag:	Sensorless control:	Standard
Capacity: m³/h(USgpm) Liquid:		Minimum system pressure to be maintained:	m (ft)*
Temperature:°C (°F)	Specific gravity:	Protocol (standard):	☐ Modbus RTU ☐ BACnet™ MS/TP☐ Johnson® N2 ☐ Siemens® FLN
Suction: 100mm (4")	Discharge: 100mm (4")	Protocol (optional):	\square LonWorks $^{\circledR}$
		Enclosure:	□ Indoor - IP55 □ Outdoor - IP66
MOTOR DESIGN DATA		: Fused disconnect switch:	
kW: RPM:	Enclosure:	Duty/standby	
Volts: Hertz: 50	Hz Phase: 3	pre-wired bridge:	
Efficiency: \square IE2 Frame size:		EMI/RFI control:	Integrated filter designed to meet EN61800-3
MAXIMUM PUMP OPERATI	NG CONDITIONS	Harmonic suppression:	Dual Dc-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
PN 16		Cooling:	Fan-cooled through back channel
16 bars at 149°C (232 psig at 300°F) 7 bars at 150°C (100 psig at 300°F)		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
PN 25 25 bars at 149°C (375 psig at 300°F)		Analog ı/o:	Two current or voltage inputs,
21 bars at 150°C (260 psig at 300°F)		5	one current output
		Digital i/o:	Six programmable inputs (two can be configured as outputs)
 Tolerance of ±3 mm (±0.125") should be used For exact installation, data please write factory for certified dimensions 		Pulse inputs:	Two programmable
		Relay outputs:	Two programmable
		Communication port: 1-RS485, 1-USB	
MECHANICAL SEAL DESIGN DATA		*If minimum maintained system pressure is not known: Default to 40% of design head **The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not	
See file no. 43.50 for standard mechanical seal details as indicated below		meet a system wide specification. If Armstrong will run a computer simu	n wide harmonic specification or the costs to supplied with the system electrical details, plation of the system wide harmonics. If system


 $\label{eq:mitigation} \mbox{mitigation and the costs for such mitigation.}$

Armstrong seal reference number

☐ Others:

□ c1 (a)

2



Performance curves are for reference only.


Confirm current performance data with Armstrong ACE Online selection software.

DIMENSION DATA

	INDOOR IP55	
Frame size:	90S	
Size:	1015-001.1	
kW:	1.1	
RPM:	1500	
AB:	536(21.10)	
B1:	245(09.64)	
B2:	245(09.64)	
C1:	400(15.74)	
C2:	409(16.10)	
D1:	290(11.41)	
D2:	290(11.41)	
E:	133(05.23)	
F:	150(05.90)	
P:	190(07.57)	
SD:	490(13.08)	
T:	178(05.31)	
XY:	551(21.78)	
Weight:	101.61(224)	

Dimensions - mm (inch) Weight - kg (lbs)

INDOOR



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM