


## **DESIGN ENVELOPE** 4312 TWIN 1015-005.5 SUBMITTAL

File No: 100.4736IN Date: AUGUST 14, 2015 Supersedes: 100.4736IN Date: MAY 27, 2015

Job:	Representative:		
	Order No:	Date:	
Engineer:	Submitted by:	Date:	
Contractor:	Approved by:	Date:	
PUMP DESIGN DATA	CONTROLS DATA		
No. of pumps: Tag:	Sensorless control: Star	Sensorless control: Standard	
Capacity: m <sup>3</sup> /h(USgpm) Head: r Liquid: Viscosity:	to be maintained.	m (ft)*	
Temperature:°C (°F) Specific gravity:	Protocol (standard):	Λodbus rtu □ bacnet™ ms/tp ohnson® n2 □ Siemens® fln	
Suction: 100mm (4") Discharge: 100mm	Protocol (optional):	onWorks®	
	Enclosure:	ndoor – 1P55 Dutdoor – 1P66	
MOTOR DESIGN DATA	Fused disconnect switch: $\Box$		
kW: RPM: Enclosure: Volts: Hertz: 50 Hz Phase: 3	Duty∕standby pre-wired bridge: □		
Efficiency:  IE2 Frame size:		grated filter designed to meet 1800-3	
MAXIMUM PUMP OPERATING CONDITION	5% /	al DC-link reactors (Equivalent: AC line reactor) Supporting 519-1992 requirements**	
PN 16	Cooling: Fan	-cooled through back channel	
16 bars at 149°C (232 psig at 300°F) 7 bars at 150°C (100 psig at 300°F)		C to +45°C up to 1000 ers above sea level °F to +113°F, 3300 ft)	
<b>PN 25</b> 25 bars at 149°C (375 psig at 300°F)	Analog I/o: Two one	o current or voltage inputs, current output	
21 bars at 150°C (260 psig at 300°F)		programmable inputs (two be configured as outputs)	
<ul> <li>Tolerance of ±3 mm (±0.125") should be used</li> <li>For exact installation, data please write factory for</li> </ul>	Pulse inputs: Two	programmable	
certified dimensions	Relay outputs: Two	programmable	
	Communication port: 1-RS	485, 1-USB	
<b>MECHANICAL SEAL DESIGN DATA</b> See file no. 43.50 for standard mechanical seal detai indicated below	*If minimum maintained system pressure is r **The IVS 102 drive is a low harmonic drive vi guaranty performance to any system wide meet a system wide specification. If suppli Armstrong will run a computer simulation harmonic levels are exceeded Armstrong of	ia built-in DC line reactors. This does not harmonic specification or the costs to ied with the system electrical details, of the system wide harmonics. If system	
Armstrong seal reference number	mitigation and the costs for such mitigatio		
□ c1 (a) □ Others:	:		



Design Envelope 4312 twin



DIMENSION DATA

	INDOOR IP55	
Frame size:	1325	
Size:	1015-005.5	
kW:	5.5	
RPM:	3000	
AB:	704(27.71)	
B1:	245(09.64)	
B2:	245(09.64)	
C1:	400(15.74)	
C2:	409(16.10)	
D1:	290(11.41)	
D2:	290(11.41)	
E:	175(06.97)	
F:	212(08.34)	
Ρ:	280(11.02)	
SD:	490(13.08)	
т:	178(05.31)	
XY:	719(28.30)	
Weight:	142.43(314)	


Dimensions – mm (inch) Weight – kg (lbs)

:


Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.

INDOOR



L



**TORONTO** +1 416 755 2291

**BUFFALO** +1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

## BANGALORE

+91 (0) 80 4906 3555

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

+86 21 3756 6696

SHANGHAI