

HORIZONTAL SPLIT CASE PUMP | SERIES 4600F |
DIESEL DRIVEN | 10x8x20F | SUBMITTAL

File No: F46.568
Date: JUNE 21, 2021
Supersedes: NEW
Date: NEW

Job: _____ Representative: _____

Order no.: _____ Date: _____

Engineer: _____ Submitted by: _____ Date: _____

Contractor: _____ Approved by: _____ Date: _____

PUMP DESIGN DATA

Flow: _____

Head: _____

ENGINE DESIGN DATA

HP: _____ RPM: _____

Bat. Voltage: _____ Tank size: _____

Other: _____

NOTES

- 1 Std. Discharge flange thickness ANSI 250#.
- 2 Coupling guard not shown.
- 3 All dimensions for engine connections are with reference to engine manufacturer's installation drawings.
- 4 Do not use for construction unless certified.
- 5 Right hand rotation only.

FLANGE RATING

- ANSI 125# STD¹
- ANSI 125# Suction
250# Discharge
- ANSI 250#
- PN 16

FIRE PUMP LISTING

- UL
- ULC
- FM

ACCESSORIES

- Exhaust system
- Fuel system
- Cooling system (mounted on engine)
- Battery system

10x8x20F	HORIZONTAL SPLIT CASE DIESEL DRIVEN	DIMENSIONS inches (mm)							WEIGHT lbs (kg)
		C	HA	HB	HE	HF	HM	Z	
Clarke	JU6H series	105.65 (2684)	35.43 (900)	106.30 (2700)	34.09 (866)	49.21 (1250)	75.97 (1930)	15.04 (382)	3342 (1516)
	JW6H series	110.48 (2806)	37.40 (950)	112.20 (2850)	34.09 (866)	52.17 (1325)	80.79 (2052)	15.04 (382)	3743 (1698)
	DP6H series	111.78 (2839)	37.40 (950)	114.17 (2900)	34.09 (866)	53.15 (1350)	76.71 (1948)	15.04 (382)	3899 (1768.6)
	DQ6H series	110.78 (2814)	38.19 (970)	114.17 (2900)	34.80 (884)	53.15 (1350)	78.72 (1999)	15.04 (382)	4149 (1882.0)
	DSOH series	114.46 (2907)	37.40 (950)	118.11 (3000)	34.45 (875)	55.12 (1400)	79.81 (2027)	15.04 (382)	4849 (2199.0)
	c18H0 series	123.22 (3130)	35.43 (900)	125.98 (3200)	32.12 (816)	59.06 (1500)	78.76 (2001)	15.04 (382)	5749 (2607.7)
Cummins	CFP5E series	85.99 (2184)	32.00 (813)	95.00 (2413)	30.00 (762)	45.50 (1156)	47.53 (1207)	15.04 (382)	3545 (1608.0)
	CFP7E series	96.94 (2462)	32.00 (813)	100.00 (2540)	30.00 (762)	32.00 (813)	47.53 (1207)	15.04 (382)	3545 (1608.0)
	CFP9E series	98.73 (2508)	32.00 (813)	100.00 (2540)	30.00 (762)	32.00 (813)	49.63 (1261)	15.04 (382)	5119 (2322.0)
	CFP15E series	111.03 (2820)	40.00 (1016)	105.00 (2667)	38.00 (965)	50.50 (1283)	50.51 (1283)	15.04 (382)	6499 (2948.0)

TORONTO
+1 416 755 2291

BUFFALO
+1 716 693 8813

DROITWICH SPA
+44 8444 145 145

MANCHESTER
+44 8444 145 145

BANGALORE
+91 80 4906 3555

SHANGHAI
+86 21 5237 0909

SÃO PAULO
+55 11 4785 1330

LYON
+33 4 26 83 78 74

DUBAI
+971 4 887 6775

MANNHEIM
+49 621 3999 9858

JIMBOLIA
+40 256 360 030

