

DESIGN ENVELOPE 4312 TWIN | 1015-011.0 SUBMITTAL

File No: 100.4740IN **Date:** AUGUST 14, 2015 Supersedes: 100.4740IN Date: MAY 27, 2015

Job:		Representative:	
		Order No:	Date:
Engineer:		Submitted by:	Date:
Contractor:		Approved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	
No. of pumps:	Tag:	Sensorless control:	Standard
Capacity: m³/h(USgpm) Liquid:		Minimum system pressure to be maintained:	m (ft)*
Temperature:°C (°F)	Specific gravity:	Protocol (standard):	☐ Modbus RTU ☐ BACnet™ MS/TP☐ Johnson® N2 ☐ Siemens® FLN
Suction: 100mm (4")	Discharge: 100mm (4")	Protocol (optional):	☐ LonWorks®
		Enclosure:	☐ Indoor - IP55 ☐ Outdoor - IP66
MOTOR DESIGN DATA		: Fused disconnect switch:	
kW: RPM: Volts: Hertz: 5		Duty/standby pre-wired bridge:	
Efficiency: Frame size:		:	Integrated filter designed to meet
Efficiency. Truine 3.			EN61800-3
MAXIMUM PUMP OPERATING CONDITIONS		Harmonic suppression:	Dual pc-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
PN 16		Cooling:	Fan-cooled through back channel
16 bars at 149°C (232 psig at 300°F) 7 bars at 150°C (100 psig at 300°F)		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
PN 25 25 bars at 149°C (375 psig at 300°F) 21 bars at 150°C (260 psig at 300°F)		Analog I/0:	Two current or voltage inputs, one current output
		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
 Tolerance of ±3 mm (±0.125") should be used For exact installation, data please write factory for certified dimensions 		Pulse inputs:	Two programmable
		Relay outputs:	Two programmable
		Communication port:	1-RS485, 1-USB
MECHANICAL SEAL DESIGN DATA		*If minimum maintained system pressure is not known: Default to 40% of design head **The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not	
See file no. 43.50 for standard mechanical seal details as indicated below		meet a system wide specification. If Armstrong will run a computer simu	n wide harmonic specification or the costs to supplied with the system electrical details, llation of the system wide harmonics. If system trong can also recommend additional harmonic

 $mitigation\ and\ the\ costs\ for\ such\ mitigation.$


Armstrong seal reference number

☐ Others:

□ c1 (a)

1015-011.0

2




Performance curves are for reference only. Confirm current performance data with Armstrong ACE Online selection software.

DIMENSION DATA

INDOOR IP55	
160M	
1015-011.0	
11	
3600	
847(33.34)	
245(09.64)	
245(09.64)	
400(15.74)	
409(16.10)	
290(11.41)	
290(11.41)	
208(08.27)	
430(16.92)	
315(12.40)	
490(13.08)	
178(05.31)	
806(31.73)	
213.19(470)	

Dimensions - mm (inch) Weight - kg (lbs)

INDOOR



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM