

DESIGN ENVELOPE 4372 TANGO

Seal type: 2A

Secondary seal: EPDM

Rotating hardware: Stainless steel

1.25×1.25×5 (32-125) | 1205-001.5 | SUBMITTAL

File No: 102.5186 Date: NOVEMBER 08, 2021 Supersedes: NEW Date: NEW

Job:	Representative:	
	Order No:	Date:
Engineer:	Submitted by:	Date:
Contractor:	Approved by:	Date:
PUMP DESIGN DATA	DEPM MOTOR	AND CONTROL DATA
No. of pumps: Tag:		HP: 1.5
Total system design flow:	USgpm(L/s) :	RPM: 3000
Head:ft(m) Capacity split	%	nclosure: TEFC
Flow per pump head:	: Volts	s/Phase: 200-240V/1ph 380-480V/3ph
Parallel flow:	•	For 200-240V/3ph or 575V/3ph, see File #:102.5163
	•	fficiency: IE5
Liquid: Viscosity:	Ori	ientation: Standard
Temperature: °F (°C) Specific gravity:	. FIULUCUI (SI	tandard): □ BACnet™ мs/тр □ BACnet™ тср/іғ
Suction: 1.25" (32 mm) Discharge: 1.25"	' (32 mm)	☐ Modbus RTU
UL STD 778 & CSA STD C22.2 NO.108 certified	Control e	nclosure: Indoor – UL TYPE 12
Test report is supplied with each pump	<u>:</u>	Outdoor - UL TYPE 12,
	Eusad disconne	tested to TYPE 4X ct switch: See File 100.8131
MATERIALS OF CONSTRUCTION	•	crossites. See the 100.8131
☐ ANSI 125	EWIJ KI	EN61800-3
CONSTRUCTION: LPDESF	Harmonic sup	pression: Equivalent: 5% AC line reactor - Sup-
E-coated ductile iron A536 Gr 65-45-12, st	ainless fitted :	porting IEEE 519-1992 requirements**
☐ ANSI 250		Cooling: Fan-cooled, surface cooling
CONSTRUCTION: HPDESF E-coated ductile iron A536 Gr120-90-2, si		perature: -10°C to +40°C up to 1000 meters above
E-coated ductile from A530 dr 120-90-2, si	•	sea level (+14°F to +104°F, 3300 ft)
MAXIMUM PUMP OPERATING CONDIT	IONS	nalog I/o: Two inputs, one output. Output can be configured for voltage or current
☐ ANSI 125	. D	igital I/o: Two inputs, two outputs. Outputs can
175 psig at 150°F (12 bar at 65°C)		be configured as inputs
100 psig at 250°F (7 bar at 121°C)	Relay	outputs: Two programmable
☐ ANSI 250	Communication	tion port: 1-RS485
300 psig at 150°F (20 bar at 65°C)	•	stem electrical details, Armstrong will run a computer simulation
250 psig at 250°F (17 bar at 121°C)	•	rmonics. If system harmonic levels are exceeded Armstrong can tional harmonic mitigation and the costs for such mitigation.
MECHANICAL SEAL DESIGN DATA	. FLOW PEADOL	

FLOW READOUT ACCURACY

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMS. The model readout will be factory tested to ensure ±5% accuracy.

FLUID TYPE	ALL GLYCOLS >	30% WT CONC	ALL OTHER NO	N-POTABLE FLUIDS	POTABLE (DRI	NKING) WATER
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating face	Silicone carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat elastomer	EPDM (L-cup)	EPDM (o-ring)	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (O-ring)
Material code	SCsc L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

Stationary seat: Silicone carbide

Spring: Stainless steel

OPTIONS

SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- · Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Cooling		
Duty point	gpm (L/s) at	ft (m)
Minimum system	m pressure to be maint	ained
	ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum system	m pressure to be maint	ained
	ft (m)	

OPTIONAL SERVICES

ON-SITE PUMP COMMISSIONING



PUMP MANAGER



Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- * Requires an internet connection to be provided by building
- * Includes an extended warranty for parts and labour (wearable parts excluded)


^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only

^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only

3




Performance curves are for reference only.


Confirm current performance data with Armstrong ADEPT Quote or ADEPT Select selection software.


INDOOR

B1 B2 C2









DIMENSION DATA

INDOOR (UL TYPE 12/TEFC)		OUTDOOR (UL TYPE 12, TESTED TO TYPE 4X)	
Size:	1.25×1.25×5	1.25×1.25×5	
HP:	1.5	1.5	
RPM:	3000	3000	
Frame:	71	71	
AB:	14.66 (372)	15.79 (401)	
B1:	5.83 (148)	5.83 (148)	
B2:	5.83 (148)	5.83 (148)	
C1:	11.00 (279)	11.00 (279)	
C2:	11.00 (279)	11.00 (279)	
CI:	_	2.80 (71)	
D:	5.17 (131)	5.17 (131)	
E:	5.99 (152)	6.40 (163)	
s:	7.02 (178)	7.02 (178)	
SD:	11.02 (280)	11.02 (280)	
T:	3.52 (89)	3.52 (89)	
Weight:	107 (48.5)	107 (48.5)	

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of ± 0.125 " (± 3 mm) should be used
- For exact installation, data please write factory for certified dimensions

TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS BUSINESS PARK DROITWICH SPA, WORCESTERSHIRE UNITED KINGDOM, WR9 OLW +44 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

JIMBOLIA

STR CALEA MOTILOR NR. 2C JIMBOLIA 305400, JUD.TIMIS ROMANIA +40 256 360 030

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934