

VERTICAL IN-LINE FIRE PUMP 43PF | 6 × 5 × 10 PF | SUBMITTAL

File No: F43.103V
Date: JANUARY 05, 2026
Supersedes: NEW
Date: NEW

Job: _____ Representative: _____
Order no.: _____ Date: _____
Engineer: _____ Submitted by: _____ Date: _____
Contractor: _____ Approved by: _____ Date: _____

PUMP DESIGN DATA

Flow: _____
Head: _____

ENCLOSURE: _____

FIRE PUMP LISTING

- ☐ UL
☐ ULC
☐ FM


FLANGE RATING

- ☐ ANSI 125# STD
☐ ANSI 250# STD

- Dimensions are not to be used for construction purposes unless certified.
- Data subject to change without notice.

MOTOR DATA

HP: _____ RPM: _____
Volt: _____ ph: _____ Hz: _____



PUMP DATA

PUMP	DIMENSIONS inches (mm)						WEIGHT
MODEL	A	B	C	D	E	X	lbs (kg)
43PF 6×5×10PF	6.00 (152)	5.00 (127)	18.50 (470)	13.94 (354)	9.13 (231)	13.50 (342)	446 (202.0)

UL LISTED MOTOR DATA

MOTOR	DIMENSIONS inches (mm)			WEIGHT
FRAME	F MAX	AG MAX	H MAX	lbs (kg)
324TSC/326TSC	15.40 (392)	38.80 (986)	11.10 (282)	460 (208.7)
364TSC/365TSC	17.90 (454)	40.30 (1024)	16.40 (416)	651 (295.3)
404TSC/405TSC	19.50 (495)	48.80 (1242)	16.40 (416)	750 (340.0)

TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

DROITWICH SPA

+44 8444 145 145

MANCHESTER

+44 8444 145 145

BANGALORE

+91 80 6510 3555

SHANGHAI

+86 21 5237 0909

BEIJING

+86 21 5237 0909

SÃO PAULO

+55 11 4785 1330

LYON

+33 4 20 10 26 21

DUBAI

+971 4 887 6775

JIMBOLIA

+40 256 360 030

FRANKFURT

+49 6173 999 77 55