

DESIGN ENVELOPE 4372 TANGO | 2×2×5 (50–125) |

_____ Representative: ___

0205-002.0 | SUBMITTAL

MECHANICAL SEAL DESIGN DATA

Stationary seat: Silicone carbide

Spring: Stainless steel

Seal type: 2A

Secondary seal: EPDM

Rotating hardware: Stainless steel

Job:

File No: 102.5194 **Date:** NOVEMBER 08, 2021 Supersedes: NEW Date: NEW

		Order	· No:	Date:	
Engineer: Sub Contractor: App		Subm	itted by:		
		Appro	oved by:		
PUMP DESIGN DATA			DEPM MOTOR AND CO	ONTROL DATA	
No. of pumps:	Tag:		HP:	2	
Total system design flow:ft(m) Flow per pump head:	USg Capacity splitUSg	pm(L/s) % pm(L/s)	Motor enclosure:	☐ 200-240V/1ph ☐ 380-480V/3ph For 200-240V/3ph or 575V/3ph,	
Parallel flow: Liquid:	Viscosity:		Efficiency: Orientation:	_	
Temperature: °F (°C) Suction: 2" (50 mm)				□ BACnet™ MS/TP □ BACnet™ TCP/IP □ Modbus RTU	
UL STD 778 & CSA STD C22.2 NO.108 certified Test report is supplied with each pump			Control enclosure:	☐ Indoor - UL TYPE 12 ☐ Outdoor - UL TYPE 12, tested to TYPE 4X	
MATERIALS OF CONSTRU	JCTION		Fused disconnect switch:	_	
□ ANSI 125 CONSTRUCTION: LPDESF E-coated ductile iron A536	Gr 65-45-12, stainles	ss fitted		Integrated filter designed to meet EN61800-3 Equivalent: 5% AC line reactor - Sup- porting IEEE 519-1992 requirements**	
☐ ANSI 250			Cooling:	Fan-cooled, surface cooling	
CONSTRUCTION: HPDESF E-coated ductile iron A536	Gr 120-90-2, stainle	ss fitted	Ambient temperature:	-10°C to +40°C up to 1000 meters above sea level (+14°F to +104°F, 3300 ft)	
MAXIMUM PUMP OPERA	TING CONDITION:	s	Analog ı/o:	Two inputs, one output. Output can	
□ ANSI 125 175 psig at 150°F (12 bar at 6) 100 psig at 250°F (7 bar at 12) □ ANSI 250	5°C)		_	be configured for voltage or current Two inputs, two outputs. Outputs can be configured as inputs Two programmable	
300 psig at 150°F (20 bar at 1250°F) (17 bar at 1	-		** If supplied with the system electric of the system wide harmonics. If sy	al details, Armstrong will run a computer simulation stem harmonic levels are exceeded Armstrong can nic mitigation and the costs for such mitigation.	

FLOW READOUT ACCURACY

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMS. The model readout will be factory tested to ensure ±5% accuracy.

·						
FLUID TYPE	ALL GLYCOLS > 30% WT CONC		ALL OTHER NON-POTABLE FLUIDS		POTABLE (DRINKING) WATER	
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating face	Silicone carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat elastomer	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (o-ring)
Material code	SCsc L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

2

OPTIONS

SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

□ PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

☐ PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

□ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Cooling

Cooling		
Duty point	gpm (L/s) at	ft (m)
Minimum system	m pressure to be maint	ained
	ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum system	m pressure to be maint	ained
	ft (m)	

OPTIONAL SERVICES

ON-SITE PUMP COMMISSIONING



PUMP MANAGER



Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- * Requires an internet connection to be provided by building
- * Includes an extended warranty for parts and labour (wearable parts excluded)


^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only

^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only

3




Performance curves are for reference only.


Confirm current performance data with Armstrong ADEPT Quote or ADEPT Select selection software.


INDOOR

B1 B2 C2









DIMENSION DATA

	INDOOR (UL TYPE 12/TEFC)	OUTDOOR (UL TYPE 12, TESTED TO TYPE 4X)
Size:	2×2×5	2×2×5
HP:	2	2
RPM:	3000	3000
Frame:	71	71
AB:	14.48 (368)	15.61 (397)
B1:	5.50 (140)	5.50 (140)
B2:	5.50 (140)	5.50 (140)
C1:	11.80 (300)	11.80 (300)
C2:	11.80 (300)	11.80 (300)
CI:	-	2.80 (71)
D:	6.30 (160)	6.30 (160)
E:	5.99 (152)	6.40 (163)
s:	7.83 (199)	7.83 (199)
SD:	13.02 (331)	13.02 (331)
T:	4.30 (109)	4.30 (109)
Weight:	127 (57.6)	127 (57.6)

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of ±0.125" (±3 mm) should be used
- For exact installation, data please write factory for certified dimensions

TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS BUSINESS PARK DROITWICH SPA, WORCESTERSHIRE UNITED KINGDOM, WR9 OLW +44 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

JIMBOLIA

STR CALEA MOTILOR NR. 2C JIMBOLIA 305400, JUD.TIMIS ROMANIA +40 256 360 030

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934