

Date: \_\_\_\_\_

\_\_\_\_\_ Date: \_\_\_\_

# DESIGN ENVELOPE 4372 TANGO

Job:

Seal type: 2A

Secondary seal: EPDM

Rotating hardware: Stainless steel

1×1×3 (25-80) | 0103-000.5 | SUBMITTAL

File No: 102.5153 Date: MARCH 25, 2021 Supersedes: 102.5153 **Date:** OCTOBER 18, 2019

		·		
		Ord	der No:	
Engineer: Su  Contractor: Ap		Sub	•	
		Арן		
PUMP DESIGN DATA			DEPM MOTOR AN	
No. of pumps:	Tag:		:	
Total system design flow:				
Head:ft(m)	Capacity split _	%	Motor enclos	
Flow per pump head:		USgpm(L/s)	V	
Parallel flow:		USgpm(L/s)	Ph Efficie	
Liquid:	Viscosity:		Orienta	
Temperature: °F (°C)	Specific gravity	:	Protocol (stand	
Suction: 1.5"MNPT	Discharge: 1.5"	MNPT	•	
UL STD 778 & CSA STD C22.2 N	o.108 certified		Control enclos	
Test report is supplied with eac	h pump		Fused disconnect sw	
MATERIALS OF CONSTR	UCTION		EMI/RFI COT	
☐ ANSI 125	OCTION		:	
CONSTRUCTION: LPDESF			Harmonic suppres	
E-coated ductile iron A536	Gr 65-45-12, s	tainless fitted	Coo	
☐ ANSI 250			Ambient tempera	
CONSTRUCTION: HPDESF	C*122 22 2	atainlaga fittad	Anala	
E-coated ductile iron A536	o Gr 120-90-2, s	stainiess nitteu	Analog	
MAXIMUM PUMP OPERA	TING CONDI	TIONS	Digita	
☐ ANSI 125				
175 psig at 150°F (12 bar at 6	-		Relay out	
100 psig at 250°F (7 bar at 1:	21°C)		* Maximum power draw = 0.5 h	
300 psig at 150°F (20 bar at	65°C)		* ** If supplied with the system e	
250 psig at 250°F (17 bar at	_		of the system wide harmonic also recommend additional	
MECHANICAL SEAL DES	IGN DATA		: FLOW READOUT A	

Stationary seat: Silicone carbide

**Spring:** Stainless steel

#### **DEPM MOTOR AND CONTROL DATA**

Representative: \_\_\_

**HP:** 1\* **RPM:** 3600 Motor enclosure: TEFC Volts: Phase: 3 Efficiency: IE5 Orientation: Standard **Protocol (standard):** □ BACnet<sup>™</sup> MS/TP □ BACnet<sup>™</sup> TCP/IP ☐ Modbus RTU

No: Date:

Control enclosure: ☐ Indoor - UL TYPE 12 ☐ Outdoor - UL TYPE 4X

Fused disconnect switch: Consult factory

**EMI/RFI control:** Integrated filter designed to meet

EN61800-3

Harmonic suppression: Equivalent: 5% Ac line reactor - Sup-

porting IEEE 519-1992 requirements\*\*

Cooling: Fan-cooled, surface cooling

**Ambient temperature:** -10°C to +45°C up to 1000 meters above

sea level (+14°F to +113°F, 3300 ft)

Analog I/o: Two inputs, one output. Output can

be configured for voltage or current

Digital I/o: Two inputs, two outputs. Outputs can

be configured as inputs

Relay outputs: Two programmable

Communication port: 1-RS485

- \* Maximum power draw = 0.5 hp
- $^{\star\star}\,$  If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

### FLOW READOUT ACCURACY

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMS. The model readout will be factory tested to ensure ±5% accuracy.

FLUID TYPE	ALL GLYCOLS >	30% WT CONC	ALL OTHER NO	N-POTABLE FLUIDS	POTABLE (DRI	NKING) WATER
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating face	Silicone	carbide	Resin bonded carbon	Antimony loaded carbon	Resin bond	led carbon
Seat elastomer	EPDM (L-cup)	EPDM (o-ring)	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (0-ring)
Material code	SCsc L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

2

# **OPTIONS**

# SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- · Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

# □ PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

# ☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

# □ PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum	flow rate	gpm	(L/	/s

# □ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

#### Cooling

Cooling		
Duty point	gpm (L/s) at	ft (m)
Minimum syster	n pressure to be maint	ained
	ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum syster	m pressure to be maint	ained
	_ ft (m)	

# **OPTIONAL SERVICES**

# **ON-SITE PUMP COMMISSIONING**



# PUMP MANAGER



Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- \* Requires an internet connection to be provided by building
- \* Includes an extended warranty for parts and labour (wearable parts excluded)


<sup>\*</sup>Only available if sensorless bundle is enabled

<sup>\*</sup>Available in single pump operation only

<sup>\*</sup>Only available if sensorless bundle is enabled

<sup>\*</sup>Available in single pump operation only


3




Performance curves are for reference only.


Confirm current performance data with Armstrong ADEPT Quote or ADEPT Select selection software.

# INDOOR



# OUTDOOR





# **DIMENSION DATA**

	INDOOR	OUTDOOR	
	(UL TYPE 12/TEFC)	(UL TYPE 4X/TEFC)	
Size:	1×1×3	1×1×3	
HP:	0.5	0.5	
RPM:	3600	3600	
Frame:	90S	90S	
AB:	17.21 (437)	19.42 (493)	
B1:	5.12 (130)	5.12 (130)	
B2:	5.12 (130)	5.12 (130)	
C1:	10.28 (261)	10.28 (261)	
C2:	10.28 (261)	10.28 (261)	
CI:	-	5.00 (127)	
D:	3.97 (101)	3.97 (101)	
E:	8.20 (208)	8.62 (219)	
s:	4.75 (121)	4.75 (121)	
SD:	8.66 (220)	8.66 (220)	
T:	2.83 (72)	2.83 (72)	
Weight:	110 (49.9)	110 (49.9)	

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of  $\pm 0.125$ " ( $\pm 3$  mm) should be used
- For exact installation, data please write factory for certified dimensions

#### TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

#### BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

#### DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS BUSINESS PARK DROITWICH SPA, WORCESTERSHIRE UNITED KINGDOM, WR9 OLW +44 8444 145 145

#### MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

#### BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

# SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

#### SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

#### LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

#### DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

# MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

# JIMBOLIA

STR CALEA MOTILOR NR. 2C JIMBOLIA 305400, JUD.TIMIS ROMANIA +40 256 360 030

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934