

# VERTICAL TURBINE DIESEL FIRE PUMP | 1000 GPM WITH 8×20 FABRICATED STEEL HEAD | SUBMITTAL

File No: F51.616

Date: JULY 15, 2013

Supersedes: F51.616

Date: AUGUST 15, 2005

Job:		Representative:					
Engineer:		Order no.:	Date:				
		Submitted by:	Date:				
		Approved by:	Date:				
Model: 8×14M VTF	<b>Discharge head:</b> 8×20 F	NOTES					
<b>RPM:</b> 1770 Water lube <b>1000 GPM:</b> T.D.H		•	Dimension based on randolph gear drive. May vary when driver adaptor is required.				
☐ FM ☐ UL	☐ NFPA-20 only	Dimensions are in in	Dimensions are in inches unless otherwise indicated.				
☐ Approval ☐ Construc	tion	• =	nting and cooling loop to be field				
☐ Engine model:		installed and plumbe					
☐ Ragd model:		:	<ul> <li>Engine oil &amp; anti freeze/coolant may not be included.</li> <li>Gear shipped filled with oil. Check level before installation</li> <li>Refer dwg. no</li></ul>				
☐ Shaft model:		•					
☐ Controller model:		• Not to be used for co	Not to be used for construction unless certified.				
		· · · · · · · · · · · · · · · · · · ·					
PRESS DISCHARGE FLAN	GE INCH (mm)	FM>	ر (Uı ),,,				

NO OF	DISCHARGE SIZE	RATING	RAGD	AG*	В	с	н*	I*	L	AA
	INCH (mm)		НР	ıncн (mm)						
8	8.00 (203)	300	350	36.00 (914)	105.00 (2667)	1.94 (49)	13.75 (349)	21.75 (553)	_	_
9	8.00 (203)	300	350-400	36.00 (914)	114.88 (2896)	1.94 (49)	13.75 (349)	21.75 (553)	_	_

**Approved** 

15.00

300 #

13.00

(330)

13.00

(330)


8.00

1.00

1.63

(41)

<sup>\*</sup> Dimension based on randolph gear drive. May vary when driver adaptor is required.



## TORONTO

+1 416 755 2291

#### BUFFALO

+1 716 693 8813

## BIRMINGHAM

+44 (0) 8444 145 145

#### MANCHESTER

+44 (0) 8444 145 145

#### BANGALORE

+91 (0) 80 4906 3555

## SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM