

# DESIGN ENVELOPE 4372 TANGO

# 1.25×1.25×5 (32-125) | 1205-002.0 | SUBMITTAL

File No: 102.5165 Date: MARCH 25, 2021 Supersedes: 102.5165 Date: SEPTEMBER 30, 2019

Job:	Representative:			
	Order No: Date:			
Engineer:	Submitted by: Date:			
Contractor:	Approved by: Date:			
PUMP DESIGN DATA	DEPM MOTOR AND CONTROL DATA			
No. of pumps: Tag:	HP: 2			
Total system design flow:USgpm0	:			
Head:ft(m) Capacity split				
Flow per pump head:USgpm0	: Volts:			
	Phase: 2			
Parallel flow:USgpm(	: Efficiency. 165			
Liquid: Viscosity:				
Temperature:of (oc) Specific gravity:	•			
Suction: 1.25" (32 mm) Discharge: 1.25" (32 mm)	☐ Modbus RTU  Control enclosure: ☐ Indoor - UL TYPE 12			
UL STD 778 & CSA STD C22.2 NO.108 certified	Outdoor - UL TYPE 12			
Test report is supplied with each pump	Fused disconnect switch: Consult factory			
MATERIALS OF CONSTRUCTION	EMI/RFI control: Integrated filter designed to meet EN61800-3			
☐ ANSI 125 CONSTRUCTION: LPDESF	Harmonic suppression: Equivalent: 5% Ac line reactor - Supporting IEEE 519-1992 requirements*			
E-coated ductile iron A536 Gr 65-45-12, stainless fi	ted <b>Cooling:</b> Fan-cooled, surface cooling			
CONSTRUCTION: HPDESF	Ambient temperature: -10°C to +45°C up to 1000 meters abore sea level (+14°F to +113°F, 3300 ft)			
E-coated ductile iron A536 Gr 120-90-2, stainless f	tted : Analog I/o: Two inputs, one output. Output can be configured for voltage or current			
MAXIMUM PUMP OPERATING CONDITIONS	Digital I/o: Two inputs, two outputs. Outputs ca			
☐ ANSI 125	be configured as inputs			
175 psig at 150°F (12 bar at 65°C)	Relay outputs: Two programmable			
100 psig at 250°F (7 bar at 121°C)	Communication port: 1-RS485			
☐ ANSI 250				
300 psig at 150°F (20 bar at 65°C) 250 psig at 250°F (17 bar at 121°C)	** If supplied with the system electrical details, Armstrong will run a computer simulat of the system wide harmonics. If system harmonic levels are exceeded Armstrong c			
250 paig at 250 1 (1/ bai at 121 c)	• • • • • • • • • • • • • • • • • • • •			

Seal type: 2A Stationary seat: Silicone carbide

Secondary seal: EPDM **Spring:** Stainless steel

MECHANICAL SEAL DESIGN DATA

Rotating hardware: Stainless steel

### **DEPM MOTOR AND CONTROL DATA**

\*\* If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

### FLOW READOUT ACCURACY

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMS. The model readout will be factory tested to ensure ±5% accuracy.

FLUID TYPE	ALL GLYCOLS > 30% WT CONC		ALL OTHER NON-POTABLE FLUIDS		POTABLE (DRINKING) WATER	
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating face	Silicone carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat elastomer	EPDM (L-cup)	EPDM (o-ring)	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (O-ring)
Material code	SCsc L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

2

## **OPTIONS**

### SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

### □ PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

### ☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

### □ PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

### □ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

### Cooling

Cooling		
Duty point	gpm (L/s) at	ft (m)
Minimum system	m pressure to be maint	ained
	ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum system	m pressure to be maint	ained
	ft (m)	

### **OPTIONAL SERVICES**

### **ON-SITE PUMP COMMISSIONING**



### **PUMP MANAGER**



Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- \* Requires an internet connection to be provided by building
- \* Includes an extended warranty for parts and labour (wearable parts excluded)


<sup>\*</sup>Only available if sensorless bundle is enabled

<sup>\*</sup>Available in single pump operation only

<sup>\*</sup>Only available if sensorless bundle is enabled

<sup>\*</sup>Available in single pump operation only

3



Performance curves are for reference only.


Confirm current performance data with Armstrong ADEPT Quote or ADEPT Select selection software.


### INDOOR


# B1 B2 C2



OUTDOOR







### **DIMENSION DATA**

INDOOR		OUTDOOR
	(UL TYPE 12/TEFC)	(UL TYPE 4X/TEFC)
Size:	1.25×1.25×5	1.25×1.25×5
HP:	2	2
RPM:	3600	3600
Frame:	905	905
AB:	18.40 (467)	20.61 (523)
В1:	5.83 (148)	5.83 (148)
B2:	5.83 (148)	5.83 (148)
C1:	11.00 (279)	11.00 (279)
C2:	11.00 (279)	11.00 (279)
CI:	_	5.00 (127)
D:	4.00 (102)	4.00 (102)
E:	8.20 (208)	8.62 (219)
s:	7.02 (178)	7.02 (178)
SD:	11.02 (280)	11.02 (280)
T:	3.52 (89)	3.52 (89)
Weight:	110 (49.9)	110 (49.9)

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of  $\pm 0.125$ " ( $\pm 3$  mm) should be used
- For exact installation, data please write factory for certified dimensions

### TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

### BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

### DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS BUSINESS PARK DROITWICH SPA, WORCESTERSHIRE UNITED KINGDOM, WR9 OLW +44 8444 145 145

### MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

### BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

### SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

### SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

### LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

### DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

### MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

### JIMBOLIA

STR CALEA MOTILOR NR. 2C JIMBOLIA 305400, JUD.TIMIS ROMANIA +40 256 360 030

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934