

VERTICAL TURBINE DIESEL FIRE PUMP | 4000 GPM WITH 12×20 CAST STEEL HEAD | SUBMITTAL

File No: F51.640

Date: JULY 15, 2013

Supersedes: F51.640

Date: AUGUST 15, 2005

Job:		Representative:					
Engineer:		Order no.:		Date:			
		Submitted by:	Date:				
		Approved by:		Date:			
Model: 12×18H VTF	Discharge head: 12×20 A	NOT	ES				
RPM: 1770 Water lube 4000 GPM:	T.D.H	•	nension based on ra ver adaptor is requir	on randolph gear drive. May vary when equired.			
□ FM □ UL □ Approval □ Constructi □ Engine model: □ Ragd model: □ Shaft model: □ Controller model: □	□ NFPA-20 only on	Eng instEngGeaRef	 Dimensions are in inches unless otherwise indicated. Engine to base mounting and cooling loop to be field installed and plumbed. Engine oil & anti freeze/coolant may not be included. Gear shipped filled with oil. Check level before installation Refer dwg. no for Engine dimensions. Not to be used for construction unless certified. 				
PRESS DISCHARGE FLANG	E INCH (mm)	— <u> </u>					


PRESS	DISCHARGE FLANGE INCH (MM)							
RATE	DA	DC	DD	DF	DG	DK		
125 #	19.00 (483)	17.00 (432)	16.50 (419)		1.00 (25)	1.25 (32)		





STG'S	DISCHARGE SIZE	RATING	RAGD	AG*	В	С	н*	I*	L	AA
	INCH (mm)		НР	INCH (mm)						
2	12.00 (305)	125	400						_	_
2	12.00 (305)	125	500	45.44 (1154)	54.00 (1372)	1.94 (49)	18.75 (476)	28.00 (711)	_	_

^{*} Dimension based on randolph gear drive. May vary when driver adaptor is required.



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM