

## FLO-TREX VALVES - MODEL FSA

## SUBMITTAL

JOB:	REPRESENTATIVE:		
	ORDER NO:	DATE:	
ENGINEER:	SUBMITTED BY:	DATE:	
CONTRACTOR:	APPROVED BY:	DATE:	

	CONNECTION SIZES		QUANTITY	IDENTIFICATION
MODEL NUMBER	INLET FROM PUMP	OUTLET TO SYSTEM	REQUIRED	IDENTIFICATION

**DIMENSIONS** in inches (mm)

6.88 (175) 9.13 (232) 4.63 (118) 4.00 (102) 2.63 (67) 2.75 (70)

8.38 (213) 11.50 (292) 6.00 (152) 5.00 (127) 3.50 (89) 3.75 (95)

9.00 (229) 11.75 (298) 6.00 (152) 5.25 (133) 3.75 (95) 3.75 (95)

Pressure Drop in Feet of Water

Line Velocity in Feet Per Second

5 Ft/sec.

3.5 ft

2.7 ft

(32 GPM)

7.3 ft

5.0 ft

(54 GPM)

5.1 ft

3.5 ft

(75 GPM)

5.5 ft

4.2 ft

(115 GPM)

D

Е

2.50 (63) 2.25 (57) 2.75 (70)

6 Ft/sec.

4.8 ft

3.5 ft

(38 GPM)

10.2 ft

7.0 ft

(64 GPM)

7.2 ft

4.7 ft

(90 GPM)

8.2 ft

6.3 ft

(138 GPM)

С

3.00 (76)

MATERIALS OF CONSTRUCTION		
Body	Cast Iron	
Disc and Seat	Bronze	
Stem	Stainless Steel	
Packing	John Crane Kevlar (non-asbestos)	
Max. Working Pressure	125 psig (9 bars)	
Max. Operating Temperature	250°F (121°C)	

Α

3 Ft/sec.

1.2 ft

1.0 ft

(19 GPM)

2.7 ft

1.5 ft

(32 GPM)

1.6 ft

1.3 ft

(45 GPM)

2.1 ft

1.6 ft

(70 GPM)

В

4 Ft/sec.

2.2 ft

1.8 ft

(25 GPM)

4.7 ft

3.2 ft

(43 GPM)

3.2 ft

2.2 ft

(60 GPM)

3.6 ft

2.7 ft

(92 GPM)

5.00 (127) 8.38 (213)

## FSA valves must be installed with stem in vertical upright position.

Weight

lbs. (kg)

9 (4.1)

13 (5.9)

24 (10.9)

26 (11.8)

8 Ft/sec.

12.5 ft


8.2 ft


(120 GPM)

14.4 ft

11.2 ft

(185 GPM)





Notes: 1. Dimensions given are for reference only. For exact installation data, contact Factory. 2. Connections are threaded NPT or 125 lb. flanged as indicated 3. Companion flanges provided on flanged connections.

© S.A. Armstrong Limited 2010

S. A. Armstrona Limited 23 Bertrand Avenue Toronto, Ontario Canada, M1L 2P3 T: (416) 755-2291 F (Main): (416) 759-9101

**DIMENSIONAL DATA** 

PUMP

1½ NPT

2 NPT

21/2 NPT

3 NPT

PERFORMANCE DATA

MODEL

1½ FSA

2 FSA

21/2 FSA

3 FSA

MODEL

11/2 FSA

2 FSA

21/2 FSA

3 FSA

CONNECTION SIZE

**POSITION IN** 

PIPE LINE

Straight

Angle

Straight

Angle

Straight

Angle

Straight

Angle

OUTLET

1½ NPT

2 Flg'd

21/2 Flg'd

3 Flg'd

Armstrong Pumps Inc. 93 East Avenue North Tonawanda, New York U.S.A. 14120-6594 T: (716) 693-8813 F: (716) 693-8970

Armstrong Integrated Limited Wenlock Way Manchester United Kingdom, M12 5JL T: +44 (0) 8444 145 145 **F**: +44 (0) 8444 145 146