

DESIGN ENVELOPE 4380 VIL | 0208-003.0 | SUBMITTAL

File No: 100.4334

Date: JANUARY 14, 2016

Supersedes: 100.4334

Date: AUGUST 14, 2015

Job:	Representative:	depresentative:			
	Order No:	Date:			
Engineer:	Submitted by:	Date:			
Contractor:	Approved by:	Date:			
PUMP DESIGN DATA	CONTROLS DATA				
No. of pumps: Tag:	Sensorless control:	Standard			
Capacity:USgpm (L/s) Head:ft (i	to be maintained:	ft (m)*			
_iquid: Viscosity:	: Orientation:	□ L1 (default) □ L2 □ L3 □ L4			
Temperature:°F (°C) Specific gravity: Suction: 2" (50mm) Discharge: 2" (50mm	•	 ☐ Modbus RTU ☐ BACnet[™] MS/TP ☐ Johnson[®] N2 ☐ Siemens[®] FLN 			
DSHPD Seismic Certification OSP-0422-10	Protocol (optional):	\square LonWorks $^{\circledR}$			
JL STD 778 & CSA STD C22.2 NO.108 certified	Enclosure:	☐ Indoor - UL TYPE 12 ☐ Outdoor - UL TYPE 4X with weather shield			
MOTOR DESIGN DATA		Outdoor - UL TYPE 4X less weather shield			
np: rpm:Frame size: Enclosure:	Fused disconnect switch:				
Volts: Hertz: 60 Hz Phase: 3	EMI/RFI control:	Integrated filter designed to meet EN61800-3			
Efficiency: NEMA premium 12.12 MAXIMUM PUMP OPERATING CONDITION		Dual DC-link reactors (equivalent: 5% Ac line reactor) supporting IEEE 519-1992 requirements**			
ANSI 125		Fan-cooled through back channel			
175 psig at 150°F (12 bars at 65°C)	Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)			
140 psig at 250°F (10 bars at 121°C) ANSI 250	Analog ı/o:	Two current or voltage inputs, one current output			
300 psig at 150°F (20 bars at 65°C)	Digital ı/o:	Six programmable inputs (two can be configured as outputs)			
250 psig at 250°F (17 bars at 121°C)	Pulse inputs:	Two programmable			
• Tolerance of ±0.125" (±3 mm) should be used	:	Two programmable			
 For exact installation, data please write factory for certified dimensions 	Communication port:	1-RS485, 1-USB			

^{*}If minimum maintained system pressure is not known: Default to 40% of design head

**The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not
guaranty performance to any system wide harmonic specification or the costs to meet
a system wide specification. If supplied with the system electrical details, Armstrong
will run a computer simulation of the system wide harmonics. If system harmonic
levels are exceeded Armstrong can also recommend additional harmonic mitigation
and the costs for such mitigation.

FLUID TYPE	ALL GLYCOLS > 30% WT CONC		ALL OTHER NON-POTABLE FLUIDS		POTABLE (DRINKING) WATER	
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating face	Silicone carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat elastomer	EPDM (L-cup)	EPDM (O-ring)	EPDM (L-cup)	EPDM (O-ring)	EPDM (L-cup)	EPDM (0-ring)
Material code	SCsc L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

MECHANICAL SEAL DATA


Seal type: 2A

Secondary seal: EPDM

Spring: Stainless steel

Stationary seat: Silicone carbide

Rotating hardware: Stainless steel




Performance curves are for reference only.


 $Confirm\ current\ performance\ data\ with\ Armstrong\ ACE\ Online\ selection\ software.$


DIMENSION DATA


	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)		
Frame size: 182		182		
Size:	2×2×8	2×2×8		
HP:	3	3		
RPM:	1800	1800		
AB: B: C: D: E: P:	21.86(555)	27.82(707)		
	5.72(145)	5.72(145)		
	5.72(145)	5.72(145)		
	8.50(216)	8.50(216)		
	12.56(319)	17.83(453)		
	10.38(264)	9.50(241)		
	22.06(560)	27.33(694)		
s:	9.50(241)	9.50(241)		
SD:	18.00(457)	18.00(457)		
T:	5.09(129)	5.09(129)		
XY:	19.26(489)	20.01(508)		
Weight:	249(112.9)	288(130.6)		


Dimensions - inch (mm) Weight - lbs (kg)











TORONTO +1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM