



EXCHANGER SIZE	DIMENSIONS											
	A		B		C		D		N1		N2	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WSX-163-2-2	52 3/4	1340	19 3/4	502	6	152	40	1016	8	203	2 1/2	64
WSX-164-2-2	64 3/4	1645	31 3/4	806	18	457	52	1321	8	203	2 1/2	64
WSX-165-2-2	76 3/4	1949	43 3/4	1111	30	762	64	1626	8	203	2 1/2	64
WSX-166-2-2	88 3/4	2254	55 3/4	1416	42	1067	76	1930	8	203	2 1/2	64
WSX-167-2-2	100 3/4	2559	67 3/4	1721	54	1372	88	2235	8	203	2 1/2	64

NOZZLE SCHEDULE				
SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	(N1)	AS PER TABLE	(N5)	6 (152) FLG
OUTLET	(N2)	AS PER TABLE	(N6)	6 (152) FLG
DRAIN	(N3)	1/2 (13) NPT		
VENT	(N4)	3/4 (19) NPT		

NOTES: 1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.  
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.  
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.  
 4. DRAWING IS NOT TO SCALE.  
 5. ALL DIM'S ±1/8 (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS				
	SHELL		TUBES	
DESIGN PRESSURE	150 PSIG	1034 KPa	150 PSIG	1034 KPa
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	40 °F	4.4 °C	40 °F	4.4 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KPa	300 PSIG	2068 KPa
CONTENTS	STEAM		WATER	

CUSTOMER:  
 LOCATION:  
 ENGINEER:  
 ORDER No.:  
 PROJECT/JOB:  
 LOCATION:  
 TAG: (QUOTE # )

TITLE	A R M S T R O N G				NUMBER	REV.
G.A. 150 LB. WSX SERIES HEAT EXCHANGERS	TORONTO - CANADA	MONTREAL - CANADA	BUFFALO - N. Y.	COLCHESTER - U.K.	WSX-16-2P-2-(8)	
DATE: 12 / 01 / 94	BY: D.C.R.	TEL : (416) 755-2291	TEL : (514) 421-2424	TEL: (716) 693-8813	TEL: (44) 120-657-9491	