

DESIGN ENVELOPE 4380 VIL | 1.5×1.5×3 (40-80) |

1503-001.0 | SUBMITTAL

Supersedes: 101.5501 Date: AUGUST 29, 2018

Job: Re		epresentative:		
	Order	No:	Date:	
Engineer:	Submit	ted by:	Date:	
Contractor:	Approv	ved by:	Date:	
PUMP DESIGN DATA	:	DEPM MOTOR AND CO	ONTROL DATA	
No. of pumps: Tag:		HP:	1	
Capacity:USgpm (L/s) Head:	:	RPM:	3600	
	:	Motor enclosure:	TEFC	
Liquid: Viscosity:	:	Volts:		
Temperature: °F (°C) Specific grav	•	Phase:	3	
Suction: 1.5" (40 mm) Discharge: 1.	5" (40 mm)	Efficiency:	=	
UL STD 778 & CSA STD C22.2 NO.108 certified			□ L5 (default) □ L6	
NSF/ANSI 61 & 372 certified for stainless steel units		Protocol (standard):	□ BACnet [™] MS/TP □ BACnet [™] TCP/IP	
Test report is supplied with each pump			☐ Modbus RTU	
		Control enclosure:	☐ Indoor – UL TYPE 12	
MATERIALS OF CONSTRUCTION	:		Outdoor - UL TYPE 4X	
☐ ANSI 125		Fused disconnect switch:	•	
CONSTRUCTION: LPDESF	:	EMI/RFI control:	Integrated filter designed to meet	
E-coated ductile iron A536 Gr 65-45-12, stain	less fitted		EN61800-3	
CONSTRUCTION: SS	:	Harmonic suppression:	Equivalent: 5% Ac line reactor - Sup-	
Cast Stainless Steel ASTM A743 CF8M Type 31	6	Caalina	porting IEEE 519-1992 requirements** Fan-cooled, surface cooling	
☐ ANSI 250		_	-10°C to +45°C up to 1000 meters above	
CONSTRUCTION: HPDESF		Ambient temperature:	sea level (+14°F to +113°F, 3300 ft)	
E-coated ductile iron A536 Gr 120 - 90 - 2, stain	less fitted :	Analog I/O:	Two inputs, one output. Output can	
	:	Allalog I/ O.	be configured for voltage or current	
MAXIMUM PUMP OPERATING CONDITI	ONS	Digital 1/0:	Two inputs, two outputs. Outputs can	
☐ ANSI 125	:	2 . g , 0 .	be configured as inputs	
175 psig at 150°F (12 bar at 65°C)	:	Relay outputs:	Two programmable	
140 psig at 250°F (10 bar at 121°C)		Communication port:		
□ ANSI 250	:	•	al details, Armstrong will run a computer simulation	
300 psig at 150°F (20 bar at 65°C) 250 psig at 250°F (17 bar at 121°C)			stem harmonic levels are exceeded Armstrong can nic mitigation and the costs for such mitigation.	
MECHANICAL SEAL DESIGN DATA	:	FLOW READOUT ACCUI		

FLOW READOUT ACCURACY

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMS. The model readout will be factory tested to ensure ±5% accuracy.

FLUID TYPE	ALL GLYCOLS > 30% WT CONC		ALL OTHER NON-POTABLE FLUIDS		POTABLE (DRINKING) WATER	
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating face	Silicone carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat elastomer	EPDM (L-cup)	EPDM (o-ring)	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (o-ring)
Material code	SCsc L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

Stationary seat: Silicone carbide

Spring: Stainless steel

Seal type: 2A

Secondary seal: EPDM

Rotating hardware: Stainless steel

OPTIONS

SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

PARALLEL SENSORLESS



Operation of multiple pumps without a remote

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate qpm (L/s)

PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

gpm (L/s) Minimum flow rate

DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Cooling		
Duty point	gpm (L/s) at	ft (m)
Minimum syster	n pressure to be maint	ained
	ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum syster	m pressure to be maint	ained
	ft (m)	
	ft (m)	

OPTIONAL SERVICES

ON-SITE PUMP COMMISSIONING



PUMP MANAGER



Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- * Requires an internet connection to be provided by building
- * Includes an extended warranty for parts and labour (wearable parts excluded)


^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only

^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only

3



DIMENSION DATA

	INDOOR (UL TYPE 12/TEFC)	OUTDOOR (UL TYPE 4X/TEFC)
Size:	1.5×1.5×3	1.5×1.5×3
HP:	1	1
RPM:	3600	3600
AB:	16.91 (430)	19.12 (486)
в:	3.09 (78)	3.09 (78)
c:	2.27 (58)	2.27 (58)
CI:	-	5.00 (127)
D:	4.59 (116)	4.59 (116)
E:	8.20 (208)	8.62 (219)
s:	5.37 (136)	5.37 (136)
SD:	9.96 (253)	9.96 (253)
T:	2.93 (74)	2.93 (74)
Weight:	63 (28.6)	63 (28.6)


Dimensions - inch (mm) Weight - Ibs (kg)


- Tolerance of ± 0.125 " (± 3 mm) should be used
- For exact installation, data please write factory for certified dimensions

Performance curves are for reference only.


 $Confirm\ current\ performance\ data\ with\ Armstrong\ {\tt ADEPT}\ Quote\ or\ {\tt ADEPT}\ Select\ selection\ software.$


INDOOR






OUTDOOR





CONTROL ORIENTATIONS



TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

DROITWICH SPA

POINTON WAY,
STONEBRIDGE CROSS BUSINESS PARK
DROITWICH SPA, WORCESTERSHIRE
UNITED KINGDOM, WR9 OLW
+44 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

JIMBOLIA

STR CALEA MOTILOR NR 2C PO: 305400, JIMBOLIA ROMANIA +40 256 360 030

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934