
ARMSTRONG®



	DIMENSIONS											
EXCHANGER SIZE	A		В		С		D		N)		N 2	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WSX-168-2-4	116 1/4	2953	79 3/4	2026	66	1676	100	2540	10	254	3	76
WSX-169-2-4	128 1/4	3258	91 3/4	2330	78	1981	112	2845	10	254	3	76
WSX-1610-2-4	140 1/4	3562	103 3/4	2635	90	2286	124	3150	10	254	3	76
WSX-1611-2-4	152 1/4	3867	115 3/4	2940	102	2591	136	3454	10	254	3	76
WSX-1612-2-4	164 1/4	4172	127 3/4	3245	114	2896	148	3759	10	254	3	76
WSX-1613-2-4	176 1/4	4477	139 3/4	3550	126	3200	160	4064	10	254	3	76
WSX-1614-2-4	188 1/4	4782	151 3/4	3854	138	3505	172	4369	10	254	3	76
WSX-1615-2-4	200 1/4	5086	163 3/4	4159	150	3810	184	4674	10	254	3	76

NOZZLE SCHEDULE							
SERVICE	MARK	SHELL SIDE	MARK	Tube Side			
INLET	(N)	as per table	N5)	6 (152) FLG			
OUTLET	8	as per table	(6)	6 (152) FLG			
DRAIN	3	1/2 (13) NPT					
VENT	N 4	3/4 (19) NPT					

NOTES: 1, SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.

- 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.
- FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA,
- 4. DRAWING IS NOT TO SCALE.
- 5. ALL DIMN'S ±1/8 (3) UNLESS OTHERWISE SHOWN.

DES	SIGN COND	ITIONS		CUSTOMER:			
	SH	ELL	TUI	BES	LOCATION:		
DESIGN PRESSURE	150 PSIG	1034 KPa	150 PSIG	1034 KPa	ENGINEER:		
DESIGN TEMPERATURE 375		191 °C	375 °F	191 °C	ORDER No.:		
MIN. DESIGN METAL TEMP.	40 °F	4.4 °C	40 °F	4.4 °C	PROJECT/JOB:		
HYDRO, TEST PRESSURE	225 PSIG	1551 KPa	225 PSIG	1551 KPa	LOCATION:		
CONTENTS	STEAM		WATER		TAG:	(QUOTE #	
TITLE G.A. 150 LB. WSX SERIES		A R	. M	S T	R O N G	NUMBER	REV,

HEAT EXCHANGERS

TORONTO - CANADA MONTREAL - CANADA BUFFALO - N. Y. COLCHESTER - U.K.

DATE: 12 / 01 / 94 BY: D.C.R. TEL: (416) 755-2291 TEL; (514) 421-2424 TEL: (716) 693-8813 TEL: (44) 120-657-9491

WSX-16-2P-4-(10)