

DESIGN ENVELOPE 4380 VIL | 2×2×5 (50–125)

0205-005.0 | SUBMITTAL

MECHANICAL SEAL DESIGN DATA

Seal type: 2A

Secondary seal: EPDM

Rotating hardware: Stainless steel

Stationary seat: Silicone carbide

Spring: Stainless steel

File No: 101.5511

Date: MARCH 25, 2021

Supersedes: 101.5511

Date: APRIL 18, 2018

Job:		Representative:			
	Orde	r No:	Date:		
Engineer:		nitted by:			
		oved by:			
PUMP DESIGN DATA		DEPM MOTOR AND CO	ONTROL DATA		
No. of pumps: Tag:		нр:	5		
Capacity:USgpm (L/s) Head:	ft (m)	RPM:	3600		
Liquid: Viscosity:		Motor enclosure:			
Temperature: °F (°C) Specific gravity:					
Suction: 2" (50 mm) Discharge: 2" (5		Phase:	-		
	0 111111)	Efficiency:	□ L5 (default) □ L6		
UL STD 778 & CSA STD C22.2 NO.108 certified		•	☐ BACnet TM MS/TP ☐ BACnet TM TCP/IP		
Test report is supplied with each pump			☐ Modbus RTU		
		Control enclosure:	☐ Indoor - UL TYPE 12		
MATERIALS OF CONSTRUCTION		•	☐ Outdoor - UL TYPE 4X		
		Fused disconnect switch:	Consult factory		
☐ ANSI 125		ЕМІ/RFI control:	Integrated filter designed to meet		
CONSTRUCTION: LPDESF	aa fittad		EN61800-3		
E-coated ductile iron A536 Gr 65-45-12, stainle ☐ ANSI 250	ssiittea	Harmonic suppression: Equivalent: 5% AC line reactor - Sup			
CONSTRUCTION: HPDESF		Cooling	porting IEEE 519-1992 requirements** Fan-cooled, surface cooling		
E-coated ductile iron A536 Gr 120-90-2, stainless fit			-10°C to +45°C up to 1000 meters above		
		Ambient temperature.	sea level (+14°F to +113°F, 3300 ft)		
		: Analog ı/o:	Two inputs, one output. Output can		
MAXIMUM PUMP OPERATING CONDITION	S		be configured for voltage or current		
☐ ANSI 125		Digital ı/o:	Two inputs, two outputs. Outputs can		
175 psig at 150°F (12 bar at 65°C)		•	be configured as inputs		
140 psig at 250°F (10 bar at 121°C)			Two programmable		
□ ANSI 250		Communication port:			
300 psig at 150°F (20 bar at 65°C) 250 psig at 250°F (17 bar at 121°C)			al details, Armstrong will run a computer simulation estem harmonic levels are exceeded Armstrong can		
		•	nic mitigation and the costs for such mitigation.		
		•			

FLOW READOUT ACCURACY

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMs. The model readout will be factory tested to ensure $\pm 5\%$ accuracy.

FLUID TYPE	ALL GLYCOLS > 30% WT CONC		ALL OTHER NO	N-POTABLE FLUIDS	POTABLE (DRINKING) WATER	
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating face	Silicone carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat elastomer	EPDM (L-cup)	EPDM (o-ring)	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (o-ring)
Material code	SCsc L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

2

OPTIONS

SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

 If minimum maintained system pressure is not known: Default to 40% of design head

☐ PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

□ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Cooling

Cooling		
Duty point	gpm (L/s) at	ft (m)
Minimum system	m pressure to be maint	ained
	ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum system	m pressure to be maint	ained
	ft (m)	

OPTIONAL SERVICES

ON-SITE PUMP COMMISSIONING



PUMP MANAGER



Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- * Requires an internet connection to be provided by building
- * Includes an extended warranty for parts and labour (wearable parts excluded)


^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only

 $^{^\}star Only$ available if sensorless bundle is enabled

^{*}Available in single pump operation only


3




Performance curves are for reference only.

Confirm current performance data with Armstrong ADEPT Quote or ADEPT Select selection software.


INDOOR



-SD



OUTDOOR




DIMENSION DATA

	INDOOR	OUTDOOR	
	(UL TYPE 12/TEFC)	(UL TYPE 4X/TEFC)	
Size:	2×2×5	2×2×5	
HP:	5	5	
RPM:	3600	3600	
AB:	18.10 (460)	20.31 (516)	
в:	4.31 (109)	4.31 (109)	
c:	3.46 (88)	3.46 (88)	
CI:	-	5.00 (127)	
D:	6.01 (153)	6.01 (153)	
E:	8.20 (208)	8.62 (219)	
s:	7.01 (178)	7.01 (178)	
SD:	13.02 (331)	13.02 (331)	
T:	3.12 (79)	3.12 (79)	
Weight:	101 (45.8)	101 (45.8)	

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of ± 0.125 " (± 3 mm) should be used
- For exact installation, data please write factory for certified dimensions

CONTROL ORIENTATIONS



TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

DROITWICH SPA

POINTON WAY,
STONEBRIDGE CROSS BUSINESS PARK
DROITWICH SPA, WORCESTERSHIRE
UNITED KINGDOM, WR9 OLW
+44 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

JIMBOLIA

STR CALEA MOTILOR NR 2C PO: 305400, JIMBOLIA ROMANIA +40 256 360 030

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934