

DESIGN ENVELOPE 4380 VIL | 2.5×2.5×5 (65–125)

2505-007.5 | SUBMITTAL

Seal type: 2A

Secondary seal: EPDM

Rotating hardware: Stainless steel

Date: MAY 04, 2018

Job:		Representative:		
	Or	der No:	Date:	
Engineer:	Sul	bmitted by:	Date:	
Contractor:		proved by:	Date:	
PUMP DESIGN DATA		DEPM MOTOR AND CO	ONTROL DATA	
No. of pumps:	Tag:	нр:	7.5	
Capacity:USgpm (L/s)	Head:ft (m)	RPM:	3600	
Liquid:	Viscosity:	Motor enclosure:		
Temperature: °F (°C)		Volts:		
•	Discharge: 2.5" (65 mm)	Phase: Efficiency:		
		•	□ L5 (default) □ L6	
UL STD 778 & CSA STD C22.2 NO.1		•	☐ BACnet™ MS/TP ☐ BACnet™ TCP/IP	
Test report is supplied with each p	oump		☐ Modbus rtu	
		Control enclosure:	☐ Indoor – UL TYPE 12	
MATERIALS OF CONSTRUCT	TON		☐ Outdoor - UL TYPE 4X	
☐ ANSI 125		Fused disconnect switch:	•	
CONSTRUCTION: LPDESF		EMI/RFI CONTROI:	Integrated filter designed to meet EN61800-3	
E-coated ductile iron A536 Gr	65-45-12, stainless fitted	: Harmonic suppression:	Equivalent: 5% Ac line reactor - Sup-	
☐ ANSI 250		i i i i i i i i i i i i i i i i i i i	porting IEEE 519-1992 requirements**	
CONSTRUCTION: HPDESF		Cooling:	Fan-cooled, surface cooling	
E-coated ductile iron A536 Gr	120-90-2, stainless fitted	Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (+14°F to +113°F, 3300 ft)	
MAXIMUM PUMP OPERATIN	AG CONDITIONS	Analog ı/o:	Two inputs, one output. Output can	
☐ ANSI 125	to conditions		be configured for voltage or current	
175 psig at 150°F (12 bar at 65°C)	1	: Digital i/o:	Two inputs, two outputs. Outputs can be configured as inputs	
140 psig at 250°F (10 bar at 121°C		: Relay outnuts:	Two programmable	
□ ANSI 250		Communication port:		
300 psig at 150°F (20 bar at 65°C) 250 psig at 250°F (17 bar at 121°C)		* ** If supplied with the system electric	cal details, Armstrong will run a computer simulation	
		•	ystem harmonic levels are exceeded Armstrong can nic mitigation and the costs for such mitigation.	
MECHANICAL SEAL DESIGN	DATA	FLOW READOUT ACCU	RACY	

FLOW READOUT ACCURACY

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMS. The model readout will be factory tested to ensure ±5% accuracy.

FLUID TYPE	ALL GLYCOLS >	30% WT CONC	ALL OTHER NO	N-POTABLE FLUIDS	POTABLE (DRII	NKING) WATER
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating face	Silicone	carbide	Resin bonded carbon	Antimony loaded carbon	Resin bond	led carbon
Seat elastomer	EPDM (L-cup)	EPDM (o-ring)	EPDM (L-cup)	EPDM (O-ring)	EPDM (L-cup)	EPDM (0-ring)
Material code	SCsc L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2a	C-SC L EPSS 2A	C-SC O EPSS 2A

Stationary seat: Silicone carbide

Spring: Stainless steel

OPTIONS

SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

PARALLEL SENSORLESS



Operation of multiple pumps without a remote

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate qpm (L/s)

PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

gpm (L/s) Minimum flow rate

DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Cooling		
Duty point	gpm (L/s) at	ft (m)
Minimum system	n pressure to be maint	ained
-	ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum system	m pressure to be maint	ained
	ft (m)	

OPTIONAL SERVICES

ON-SITE PUMP COMMISSIONING



PUMP MANAGER



Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- * Requires an internet connection to be provided by building
- * Includes an extended warranty for parts and labour (wearable parts excluded)


^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only

^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only


3



Performance curves are for reference only.


Confirm current performance data with Armstrong ADEPT Quote or ADEPT Select selection software.

INDOOR



-SD

OUTDOOR




DIMENSION DATA

	INDOOR	OUTDOOR	
	(UL TYPE 12/TEFC)	(UL TYPE 4X/TEFC)	
Size:	2.5×2.5×5	2.5×2.5×5	
HP:	7.5	7.5	
RPM:	3600	3600	
AB:	18.23 (463)	20.44 (519)	
в:	4.75 (120)	4.75 (120)	
C:	3.65 (93)	3.65 (93)	
CI:	_	5.00 (127)	
D:	7.16 (182)	7.16 (182)	
E:	8.20 (208)	8.20 (208)	
s:	8.16 (207)	8.16 (207)	
SD:	15.32 (389)	15.32 (389)	
T:	3.50 (89)	3.50 (89)	
Weight:	114 (51.7)	114 (51.7)	

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of ± 0.125 " (± 3 mm) should be used
- For exact installation, data please write factory for certified dimensions

CONTROL ORIENTATIONS



TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

DROITWICH SPA

POINTON WAY,
STONEBRIDGE CROSS BUSINESS PARK
DROITWICH SPA, WORCESTERSHIRE
UNITED KINGDOM, WR9 OLW
+44 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

JIMBOLIA

STR CALEA MOTILOR NR 2C PO: 305400, JIMBOLIA ROMANIA +40 256 360 030

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934